


## CATALOG # 2810

V0 MAX SINGLE LOCKING RECEPTACLE  
GROUNDING, 30 AMP 3 PHASE Y,  
120/208V 4-POLE 5-WIRE,  
NEMA L21-30R.

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON®</b>		
<b>TOLERANCES</b>		TITLE: 2810 V0 MAX FR CATALOG DRAWING FOR NEMA L21-30		
<b>INCH</b> .XX ± .01 .XXX ± .005	<b>METRIC</b> .X ± .2 mm .XX ± .1 mm	DWG NO. CATSTD-02810-000-D01		
<b>ANGLES:</b> ± 1/2° THIRD ANGLE PROJECTION 		SIZE <b>B</b>	SCALE:1:1	SHEET 1 OF 1
ALL PRINTED COPIES ARE UNCONTROLLED		Copyright 2019. Unpublished. All Rights Reserved.		REV 1