



UPPER VALUES = INCHES
LOWER VALUES = MM

CATALOG #2820
SINGLE LOCKING RECEPTACLE
GROUNDING, 30 AMP 3 PHASE Y,
277/480V 4-POLE 5-WIRE,
NEMA L22-30R.

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.				
TOLERANCES		TITLE: SINGLE FR NEMA L22-30R CATALOG DRAWING		
INCH .XX ± .01 .XXX ± .005	METRIC .X ± .2 mm .XX ± .1 mm	DWG NO. CATSTD-02820-000-D05		
ANGLES: ± 1/2°		SIZE B	SCALE:1:1	SHEET 1 OF 1
THIRD ANGLE PROJECTION 		Copyright 2019. Unpublished. All Rights Reserved.		REV 1
ALL PRINTED COPIES ARE UNCONTROLLED				