



CATALOG # 15379-C

20 AMP, 125 VOLT, GROUNDING
 FLANGED OUTLET RECEPTACLE
 NEMA 5-20R, 2 POLE, 3 WIRE,
 STRAIGHT BLADE

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		LEVITON		
TOLERANCES		TITLE: 15379-C FLANGED OUTLET 20A NEMA 5-20 CATALOG		
INCH	METRIC	DWG NO. CATSTD-15379-00C-D01		
.XX ± .01 .XXX ± .005	.X ± .2 mm .XX ± .1 mm			
ANGLES: ± 1/2°		SIZE	SCALE: 1:1	SHEET 1 OF 1
THIRD ANGLE PROJECTION		B	Copyright 2020. Unpublished. All Rights Reserved.	REV 2
ALL PRINTED COPIES ARE UNCONTROLLED				