



**CATALOG # 16262**  
 DECORA PLUS DUPLEX RECEPTACLE,  
 2 POLE, 3 WIRE, 15AMP, 125 VOLT  
 SELF-GROUNDING, SPEC GRADE,  
 NEMA 5-15R

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON®</b>										
TOLERANCES		TITLE: <b>16262 15A-125V RECEPTACLE DECORA CATALOG DRAWING</b>										
<b>INCH</b>	<b>METRIC</b>	DWG NO. <b>CATSTD-16262-00X-D01</b>										
.XX ± .01 .XXX ± .005	.X ± .2 mm .XX ± .1 mm											
<b>ANGLES: ± 1/2°</b>		<table border="1"> <tr> <td>SIZE</td> <td>SCALE: 1:1</td> <td>SHEET 1 OF 1</td> <td>REV</td> </tr> <tr> <td><b>B</b></td> <td></td> <td></td> <td><b>1</b></td> </tr> </table>			SIZE	SCALE: 1:1	SHEET 1 OF 1	REV	<b>B</b>			<b>1</b>
SIZE	SCALE: 1:1				SHEET 1 OF 1	REV						
<b>B</b>			<b>1</b>									
THIRD ANGLE PROJECTION		Copyright 2020. Unpublished. All Rights Reserved.										
		<b>ALL PRINTED COPIES ARE UNCONTROLLED</b>										