



UPPER VALUES = INCHES
LOWER VALUES = MM

CATALOG #320R4W
WATERTIGHT RECEPTACLE, IP67 RATED,
2-POLE, 3 WIRE, 20A, 125V, PIN & SLEEVE,
INDUSTRIAL GRADE

UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.



TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

TITLE:
**20A PIN & SLEEVE 3WR
RECEPTACLE CATALOG DWG**

ANGLES: ± 1/2°
THIRD ANGLE PROJECTION

DWG NO.
CATSTD-320R4-00W-D01

ALL PRINTED COPIES
ARE UNCONTROLLED

SIZE B	SCALE:1:1	SHEET 1 OF 1	REV 1
------------------	-----------	--------------	-----------------

Copyright 2020. Unpublished. All Rights Reserved.