

Duplex Receptacles

Heavy-Duty Industrial Specification Grade Isolated Ground

15 A & 20 A, 125 V

Brass self-grounding clip is permanently staked on for secure and reliable performance

Wide receptacle face shelf — provides exceptional support to the wallplate or box cover

Body and face made of — impact-resistant advanced engineering polymer for extreme durability


Common Applications:

- Educational Facilities
- Office Environments
- Hospitality
- Day Care Centers



Oversized brass terminal screw heads provide superior clamping force and electrical conductivity

External wiring — clamps allow for back or side wiring, and provide visual verification of termination and a faster, easier installation



Molded in ribs prevent terminal screws from making contact with wall box

Ordering Information

Ratings		15 A/ 125 V	20 A/ 125 V
NEMA Config.		5-15R	5-20R
Order ID	Orange	5262-IG	5362-IG
	lvory	5262-IGI	5362-IGI
	White	5262-IGW	5362-IGW
	Gray	5262-IGG	5362-IGG
	Red	5262-IGR	5362-IGR
	Brown	5262-IGB	5362-IGB
	Black	5262-IGE	5362-IGE
	Light Almond	_	5362-IGT
	Blue	5262-BIG	5362-BIG


Specifications

Series	5262-IG	5362-IG		
AC Horsepower Rating				
At Rated Voltage	½ HP	1 HP		
Electrical Specifications				
Amperage	15 A	20 A		
NEMA	5-15R	5-20R		
Voltage	125 V			
Grounding	Self-Grounding*			
Pole	2			
Wire	3			
Dielectric Voltage	Withstands 3000 V min			
Temperature Rise	Max 30 °C temperature rise at full rated current			
Environmental Specification	S			
Flammability	UL94 V0			
Operating Temperature	Maximum Continuous 75 °C, minimum -40 °C (w/o impact)			
Material Specifications				
Face	PBT Polyester Blend			
Body	PBT Polyester Blend			
Strap	Steel (Galvanized G60)			
Ground Contact	0.030" Brass			
Ground Screw	#8 Hex Head, Triple-Drive Brass			
Ground Clamp	Brass			
Ground Clip	Brass			
Mounting Screw	Triple-Drive Plated Steel			
Line Contacts	0.030" Phosphor Bronze			
Terminal Clamp	Brass			
Terminal Screws	#8 Triple-Drive Brass			
Mechanical Specifications				
Product ID	Ratings are perman	ent part of devices		
Terminal ID	Brass - Hot, Silver - Ne	eutral, Green - Ground		
Terminal Accommodation	#14 - #1	10 AWG		
Wire Types	Stranded	d or Solid		
Termination	Back and Side Wire			
Standards & Certifications				
NEMA	WD 1 8	& WD 6		
ANSI	C-73			
Certification/Listing	cULus, NOM-ANCE			
Applicable Standards	UL498, Fed Spec W-C-596, CSA C22.2 No.42			
RoHS	RoHS Compliant			
Warranty				
Product Warranty	10 Y	'ears		


^{*} Self-grounding when installed in a properly grounded metallic box

Dimensions

Front View



Side View



Q-1145