



SINGLE LOCKING RECEPTACLE  
2 POLE, 3 WIRE, 15A-125V, GROUNDING.  
NEMA L5-15. SIDE WIRED.

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<div></div> <b>LEVITON®</b>			
TOLERANCES		TITLE:  4710 SINGLE RECEPTACLE NEMA L5-15 CATALOG DWG			
INCH .XX ± .01 .XXX ± .005	METRIC .X ± .2 mm .XX ± .1 mm				
ANGLES: ± 1/2°		DWG NO.  CATSTD-04710-000-D01			
THIRD ANGLE PROJECTION <div></div>					
ALL PRINTED COPIES ARE UNCONTROLLED		SIZE <b>B</b>	SCALE:1:1	SHEET 1 OF 1	REV <b>1</b>
		Copyright 2019. Unpublished. All Rights Reserved.			