

Product Selection Guide

Renoir™ II Architectural Wall Box Dimmers



Load Type	Wattage	Voltage	Control	Heat Sink	No Neutral	Heat Sink Width	Cat. No.
Incandescent	600	120	Preset Slide	Thin	No Neutral	Narrow	AWSMT-IAW
	1000	120	Preset Slide	Thin	No Neutral	Narrow	AWSMT-IBW
	1500	120	Preset Slide	Thin	No Neutral	Wide	AWSMT-ICW
	600	120	Preset Slide	Standard	No Neutral	Narrow	AWSMG-IAW
	1000	120	Preset Slide	Standard	No Neutral	Narrow	AWSMG-IBW
	1500	120	Preset Slide	Standard	No Neutral	Wide	AWSMG-ICW
	1920	120	Preset Slide	Standard	No Neutral	Wide	AWSMG-IDW
	600	120	Rotary	Standard	No Neutral	Narrow	AWRMG-IAW
	1000	120	Rotary	Standard	No Neutral	Narrow	AWRMG-IBW
	1500	120	Rotary	Standard	No Neutral	Wide	AWRMG-ICW
	1920	120	Rotary	Standard	No Neutral	Wide	AWRMG-IDW
Incandescent/ Magnetic Low Voltage	600/1150/1385	120/230/277	Preset Slide	Thin	-	Narrow	AWSMT-MAW
	1000/1917/2308	120/230/277	Preset Slide	Thin	-	Narrow	AWSMT-MBW
	1500/2875/3463	120/230/277	Preset Slide	Thin	-	Wide	AWSMT-MCW
	600/1150/1385	120/230/277	Preset Slide	Standard	-	Narrow	AWSMG-MAW
	1000/1917/2308	120/230/277	Preset Slide	Standard	-	Narrow	AWSMG-MBW
	1500/2875/3463	120/230/277	Preset Slide	Standard	-	Wide	AWSMG-MCW
	1920/3680/4432	120/230/277	Preset Slide	Standard	-	Wide	AWSMG-MDW
	600/1150/1385	120/230/277	Rotary	Standard	-	Narrow	AWRMG-MAW
	1000/1917/2308	120/230/277	Rotary	Standard	-	Narrow	AWRMG-MBW
	1500/2875/3463	120/230/277	Rotary	Standard	-	Wide	AWRMG-MCW
	1920/3680/4432	120/230/277	Rotary	Standard	-	Wide	AWRMG-MDW
Fluorescent 0-10V	1920/3680/4432	120/230/277	Preset Slide	Thin	-	Narrow	AWSMT-7DW
	1920/3680/4432	120/230/277	Preset Slide	Standard	-	Narrow	AWSMG-7DW
	1920/3680/4432	120/230/277	Rotary	Standard	-	Narrow	AWRMG-7DW
Mark 10 or Lutron 2-Wire	600/1150/1385	120/230/277	Preset Slide	Thin	-	Narrow	AWSMT-XAW
	1000/1917/2308	120/230/277	Preset Slide	Thin	-	Narrow	AWSMT-XBW
	1500/2875/3463	120/230/277	Preset Slide	Thin	-	Wide	AWSMT-XCW
	1920/3680/4432	120/230/277	Preset Slide	Thin	-	Wide	AWSMT-XDW
	600/1150/1385	120/230/277	Preset Slide	Standard	-	Narrow	AWSMG-XAW
	1000/1917/2308	120/230/277	Preset Slide	Standard	-	Narrow	AWSMG-XBW
	1500/2875/3463	120/230/277	Preset Slide	Standard	-	Wide	AWSMG-XCW
	1920/3680/4432	120/230/277	Preset Slide	Standard	-	Wide	AWSMG-XDW
	600/1150/1385	120/230/277	Rotary	Standard	-	Narrow	AWRMG-XAW
	1000/1917/2308	120/230/277	Rotary	Standard	-	Narrow	AWRMG-XBW
	1500/2875/3463	120/230/277	Rotary	Standard	-	Wide	AWRMG-XCW
		1920/3680/4432	120/230/277	Rotary	Standard	-	Wide

Easy Product Selection*

1. **Confirm** load type and voltage
2. **Calculate** total load
3. **Identify** control locations
4. **Select** control aesthetics, dimmers, and remotes
5. **Choose** wall plates

*Reference Product Selection Guide and Data Sheets for complete information.

Leviton Manufacturing Co., Inc. Lighting & Energy Solutions

201 N. Service Rd. Melville, NY 11747-3138 Tech Line: 1-800-824-3005 Fax: 1-800-832-9538 www.leviton.com/les

© 2012 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

The Leviton Renoir™ II Advantage

Feature		Competition
Single Multi-Voltage Units, 120-277V	Yes	-
Supports Virtually All Common Load Types	Yes	-
Easy Touch ON/OFF Button	Yes	-
Up to 5-Way Multi-Location Dimming Options	Yes	Limited (up to 4-way only)
Multiple Dimmers/Remotes	Yes	-
Engraving	Yes	Limited (no graphics)
Preset Slide Design	Yes	Yes
Preset Rotary Design	Yes	Yes
Thin Heat Sink	Yes	Yes
No Visible Heat Sink	Yes	Yes
Remote Dimming Option	Yes	Yes
No Neutral Models	Yes	Yes
Automatic Multi-Gang Alignment	Yes	Yes
Power Failure Memory	Yes	Yes
Air-Gap Switch	Yes	Yes
Voltage Compensation	Yes	Yes
RFI Suppression	Yes	Yes
Square Law Dimming	Yes	Yes
Captive Slider	Yes	Yes
Heavy Duty Components	Yes	Yes
Electrostatic Discharge Tested	Yes	Yes
Precise Color Matching Across All Controls	Yes	Yes