

# Sapphire™ Room Controller Customizable lighting, color tuning and scheduling



#### **Description**

Sapphire™ Room Controller provides the flexibility of a fully customizable user interface with the convenience of native controls from Leviton's Commercial Systems products. Integrate room controls, including occupancy/vacancy sensing, partial-ON and partial-OFF from one elegant interface. Sapphire Room Control is Leviton's premier touch screen offering occupancy/photocell sensing, full-range automatic dimming, color tuning and daylighting integration. The scheduler feature allows facility and building managers to schedule holidays and daily lighting schedules from the touch screen.

#### **Applications**

- Color tuning—0-10V, DMX (requires interface hardware)
- Conference room control
- Building supervisor control panel
- Classroom control
- · Executive office control
- Ballroom control
- Anywhere touch-interface is desired

#### **Features**

- 7" capacitive LCD touch screen
- Supports Sapphire User Interface (UI) components and commands
- Supports Sapphire Scheduler
- Supports Sapphire Room Controls
- LumaCAN and analog input connectivity
- Analog input supports photocell, occupancy, and momentary/maintained switch
- Secure password protection administration access
- Offline UI configuration through Sapphire Studio PC Tool
- All software is updated through a front-panel USB memory stick
- Available faceplates—White, Light Almond, & Black

#### Sapphire User Interface Components & Commands

- All UI elements are updated from live network status
- Uses tabs for organization of UI elements into pages
  - Each tab has a custom name
  - Each tab can offer secured access with a PIN
- Buttons
  - · Button operating modes
    - Toggle
    - Press/release
    - Preset group
  - Configurable caption
  - All network commands supported
- Sliders
  - Configurable caption
  - Supports only set channel/group level commands
  - Configurable numeric level display
- Network Commands
  - Administrative functions
    - Network setup
  - Log file import/export
  - Configuration update
  - Snapshot record
  - Snapshot edit
  - Set channel and group level
  - Fade stop
  - · Fade rate or fade time
  - Raise/lower

#### **Room Controls**

- Room controls run independent of UI
- (2) low voltage/analog inputs for connecting of occupancy sensors, photocells, etc.
- Receives input signals for automatic dimming and daylighting within the space
- Single zone occupancy
- Single zone closed loop daylight harvesting
- 8 unique buttons (may be spread across multiple stations)
- All ON through AI, configurable priority

#### Scheduler

- Scheduler runs independent of UI
- 7-day scheduler
- (2) custom, user defined holiday exception calendars
- Astronomical time clock
- Special event calendar

# **Sapphire User Interface Screenshots**

#### **Tabs and Buttons**




#### Scheduler—Daily



#### Tabs, Buttons and Sliders




#### Scheduler-Event



#### Tabs, Buttons and Sliders




#### Scheduler-Holiday







#### **Wiring Diagram**



#### Touch Screen with Connector Annotations—Rear View



#### **Installation Diagram**




| А | Face plate with trim ring           |
|---|-------------------------------------|
| В | Touch screen electronics            |
| С | Normalizing installation & mounting |
| D | 4-gang box                          |


#### Leviton Manufacturing Co., Inc. Lighting & Controls

# **Product Data** TS007-xxx



## **Dimensions Diagram**





## **Specifications**

| op-o-measure.       |   |  |
|---------------------|---|--|
| LCD Panel           | 7" (17.78cm) diagonal, 16.9 form factor ; 800x480 WVGA; 130° x 110° viewing angle; LED backlight; 24 bit color  |  |
| Power Input Voltage | +12-24VDC, Class 2 SELV; current draw: 325mA+connected device to AI, standby current: 200mA;power supply via terminals or LumaCAN network             |  |
| Environmental       | Operating Temperature Range: 14 to 122°F (5 to 50°C)<br>Storage -Temperature: -4 to 158°F (-20 to 70°C)<br>Relative Humidity: 0 to 90° non-condensing |  |
| Enclosure           | Mounting/installation: 4-gang box with a 4-gang raised device cover preferred, 4-gang low voltage rating acceptable, IP30                             |  |
| Listing             | CE, NOM, FCC  |  |

# **Ordering Information**

| Sapphire Room Controller |  |  |
|--------------------------|--|--|
| Cat. No.                 | Description  |  |
| TS007-000                | 7" Touch Screen, capacitive interface, no faceplate included   |  |
| TS007-C0E                | 7" Touch Screen, Color Change Kit, Black Faceplate   |  |
| TS007-C0T                | 7" Touch Screen, Color Change Kit, Light Almond Faceplate  |  |
| TS007C0W                 | 7" Touch Screen, Color Change Kit, White Faceplate   |  |
| TS007-LCE                | 7" Touch Screen Locking Cover, Black   |  |
| BBG04-000                | 4-Gang Box   |  |
| WPG04-DR0                | 4-Gang raised device ring for use with BBG04-000   |  |
| PST24-I10                | +24VDC, 1A, 30W 100-277VAC Input DIN Rail Power Supply. UL, cUL & CE listed, terminals on input and output |  |
| DRC00-0D0                | In-line Power Supply   |  |

#### Leviton Manufacturing Co., Inc. Lighting & Controls

10385 SW Avery Street, Tualatin, OR 97062 tel 800-736-6682 tech line (6:00AM-4:00PM PT Mon-Fri) 800-959-6004

#### Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, MeVille, NY 11747-3138 tel 800-323-8920 tech line (8:00AM-10:00PM ET Mon-Fri, 9:00AM-7:00PM ET Sat, 9:00AM-5:00PM ET Sun) 800-824-3005