

Cat 6A 110-Style Wiring Block

APPLICATION

The Leviton Cat 6A 110-Style Block provides a centralized location to easily terminate 22-26 gauge solid copper wire for telephone, voice, and data applications. The block meets Category 6A component requirements.



SPECIFICATION

The cross-connect shall be Category 6A 110-style wiring bases, available for wall mount. They shall provide 110 terminations supporting voice, data, video, and Category 6A data applications, including high megabit and shared-sheath applications when used with Category 6A rated cabling. The components shall be UL listed and ANSI/TIA-568.2-D compliant. Bases shall support 64-pair densities with provision for ANSI/TIA-606-C compliant labeling. Plastic bases and blocks must be made of fire-retardant plastic rated UL 94V-0.

FEATURES

- Supports high-frequency data signals up to 500 MHz
- Can be used as a consolidation point (CP) in a TIA defined 90 meter permanent link
- Designed to mitigate alien crosstalk (AXT)
- Independently tested and verified to meet all TIA link and channel requirements
- Available in 64-pair wall-mount block

DESIGN CONSIDERATIONS

- · Use where space limitations and low cost are factors
- Includes labels, label holders, and 16 Category 6A C-4 clips
- Port ID options: Use the label strips and holders provided

STANDARDS COMPLIANCE

Meets or exceeds all applicable standards: UL listed components; complies with ANSI/TIA-568.2-D component requirements; and supports emerging PoE standards such as the draft IEEE 802.3bt, including 100 watts

COUNTRY OF ORIGIN

Taiwan

PHYSICAL SPECIFICATIONS

Dimensions: See page two

Materials: 110 wiring bases are made of fire-retardant plastic rated UL 94V-0; C-4 clips are made of fire-retardant plastic rated UL 94V-0 with solder plated IDCs

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

Page 1 of 2

 Leviton Network Solutions
 Asia / Pacific

 2222 - 222nd St. SE
 T +1.631.812

 Bothell, WA 98021-4416
 E infoasean@

tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com T +1.631.812.6228 E infoasean@leviton.com

Europe T +44.0.1592.772124 E customerserviceeu@leviton.com Canada T +1.514.954.1840 E pcservice@leviton. com

India / SAARC T +971.4.886.4722 E infoindia@leviton.com

T +1.954.593.1896 E infocaribbean@leviton.com

T+52.55.5082.1040

E lsamarketing@leviton.com

Caribbean

Mexico

bbean@leviton.com E infochina@leviton.co Middle East & Africa

 China
 Colombia

 T +852.2774.9876
 T +57.1.74

 E infochina@leviton.com
 E infocolor

T +971 4 247 9800

E Imeinfo@leviton.com

T +57.1.743.6045 E infocolombia@leviton.com


South Korea T +82.2.3273.9963 E infokorea@leviton.com

Copyright © 2019 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.



ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



PART NUMBERS	
Description	Part No.
Cat 6A 110-Style Wiring Block Kit, includes 64-port block with legs, labels, and 16 C-4 clips*	41D6A-1F4

*Note: Standoff legs are not removable

Page 2 of 2

tel 1-800-824-3005

tel +1-425-486-2222

appeng@leviton.com

www.leviton.com

Leviton Network SolutionsAs2222 - 222nd St. SETBothell, WA 98021-4416E i

Asia / Pacific
 T +1.631.812.6228
 E infoasean@leviton.com

Europe T +44.0.1592.772124 E customerserviceeu@leviton.com Canada T +1.514.954.1840 E pcservice@leviton. com

India / SAARC T +971.4.886.4722 E infoindia@leviton.com

T +1.954.593.1896 E infocaribbean@leviton.com

Caribbean

Mexico T +52.55.5082.1040 E Isamarketing@leviton.com China T +852.2774.9876 E infochina@leviton.com

A19 7573

Colombia

T +57.1.743.6045

Middle East & Africa T +971.4.247.9800 E Imeinfo@leviton.com South Korea T +82.2.3273.9963 E infokorea@leviton.com

E infocolombia@leviton.com

Copyright © 2019 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

