

# 14" & 21" Structured Media™ Enclosures

#### **APPLICATION**

14- and 21-inch Structured Media Enclosures make running cable and managing media both simple and cost effective. They are designed to provide a central distribution consolidation point, and can be installed and concealed in a closet or behind a flat-screen display. Structured media enclosures are ideal for supporting home, classroom, and small office technologies, enclosures accommodate the distribution of voice, data, video, audio, security, and IT/AV control applications.





# **SPECIFICATION**

Enclosures shall be one-piece (excluding cover) boxes, made of 20-gauge, white powder-coated steel. They shall be flush mountable, with four wood screws (provided) on standard 16-inch center wall studs prior to drywall, or surface mountable after drywall installation. Each enclosure shall have a cutout to accommodate a single-gang J-Box power module, AC power module, or a Mini or Universal DC power supply. The enclosures shall include multiple knockouts on the top and bottom to support conduit up to two inches in diameter and facilitate cable routing and entry. The enclosure shall be cULus Listed and comply with ANSI/TIA-568-C, ANSI/TIA-570-B, and ANSI/TIA-607 standards.

### WARRANTY INFORMATION

For Leviton product warranties, go to leviton.com/ns/warranty

#### **FEATURES**

- Bottom cutout pattern accommodates AC and DC power modules
- Mounting slots on the enclosure simplify adjustment for different drywall depths (1/2 inch, 5/8 inch, and 3/4 inch)
- · Enclosures may be surface or flush mounted
- Optional Flush-Mount Cover overlaps 3/4 inch to hide possible uneven drywall cuts around the enclosure
- Ships with a cardboard insert to help prevent drywall debris or paint overspray
- Multiple knockouts on the top and bottom support conduit up to two inches in diameter and facilitate cable routing and entry
- Self-healing foam grommets protect cable bundles and prevent dust from entering the enclosure
- Available 14-inch enclosure ceiling-mount kit for installing in non-plenum drop-ceiling applications
- Mounting brackets (sold separately) can accommodate an array of devices

#### **DESIGN CONSIDERATIONS**

- · Flush mounting should precede drywall installation
- Enclosure not intended to be mounted in firewall applications
- Premium Hinged Vented Doors recommended when using active equipment inside enclosures, such as IT/AV signal extenders, routers, and switches
- For enterprise PON applications, recommended capacity of the 14-inch enclosure is one 32-leg passive optical splitter and three 12-port SC/APC adapter plates

# **STANDARDS & REGULATIONS**

cULus Listed: ANSI/UL 1863

ANSI/UL 985

ANSI/UL 1023 System Units

CAN/CSA C22.2 No. 182.4-M90 (R2010)

TIA Standards: ANSI/TIA-568-C, ANSI/TIA-570-B, and

ANSI/TIA-607

# **PHYSICAL SPECIFICATIONS**

Dimensions: See page two

Materials: Enclosure: 20-gauge, white

powder-coated steel

Covers: 18-gauge, white powder-coated steel Capacity: Maximum of two full-sized distribution


panels

# **COUNTRY OF ORIGIN**

Mexico

# PRODUCT SPECIFICATIONS 47605-14x, 47605-21x





LEVITON 14" & 21" STRUCTURED MEDIA™ ENCLOSURES, COVERS, AND DOORS Description Part No. 14" Enclosure and Flush-Mount Cover, 15.35" (389.9 mm) H x 15.62" (396.8 mm) W x 3.85" (97.8 mm) D 47605-140 14" Enclosure only, 14.0" (355.6 mm) H x 14.38" (365.3 mm) W x 3.85" (97.8 mm) D 47605-14E 14" Multi Dwelling Unit Configuration A Enclosure and Flush-Mount Cover, 15.35" (389.9 mm) 47605-1MG H x 15.62" (396.8 mm) W x 3.85" (97.8 mm) D 14" Flush-Mount Cover, 15.32" (389.1 mm) H x 15.62" (396.8 mm) W x 0.20" (5.1 mm) D 47605-14C 14" Economy Hinged Door, 15.32" (389.1 mm) H x 15.62" (396.8 mm) W x 0.25" (6.4 mm) D 47605-14D 14" Premium Vented Hinged Door, 15.32" (389.1 mm) H x 15.62" (396.8 mm) W x 0.25" (6.4 mm) D 47605-14S 14" Enclosure only, job packed, 6 per pack, 14.0" (355.6 mm) H  $\times$  14.38" (365.3 mm) W  $\times$  3.85" (97.8 mm) D 47605-14G 14" Flush-Mount Cover only, job packed, 6 per pack 15.32" (389.1 mm) H x 15.62" (396.8 mm) W x 0.20" (5.1 mm) D 47605-14B 14" Ceiling-Mount Kit, .75" (19.1 mm) H x 23.68" (601.5 mm) W x 23.68" (601.5 mm) D 47612-CMK 21" Enclosure only, 21.10" (535.9 mm) H x 14.38" (365.3 mm) W x 3.85" (97.8 mm) D 47605-21E 21" Flush-Mount Cover, 22.35" (567.7 mm) H x 15.62" (396.8 mm) W x 0.20" (5.1 mm) D 47605-21C

For further support information, visit leviton.com/ns/support

#### Page 2 of 2

Network Solutions Headquarters	
+1 (800) 722 2082	
infoUSA@leviton.com	

Leviton Berk-Tek Cable: +1 (800) 237 5835 berktek.info@leviton.com

Asia Pacific +852 3620 2602 infoAPAC@leviton.com

21" Premium Vented Hinged Door, 22.35" (567.7 mm) H x 15.62" (396.8 mm) W x 0.25" (6.4 mm) D

Canada +1 (800) 461 2002 infoCanada@leviton.com **Europe** +44 (0) 1592 772124 infoEurope@leviton.com Latin America MX: +52 (55) 2128 6286 LATAM: +52 (55) 2333 5963 infoLATAM@leviton.com Middle East & Africa +971 (4) 247 9800 infoMEA@leviton.com

47605-21S

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.