

## Grounding Vinyl Cord Outlet Sortie de cordon vinyle avec MALT

**WARNINGS AND CAUTIONS:**

- TO AVOID FIRE, SHOCK, OR DEATH; UNPLUG CORD OR TURN OFF POWER AT CIRCUIT BREAKER OR FUSE AND TEST THAT POWER IS OFF BEFORE WIRING!
- To be installed and/or used in accordance with appropriate electrical codes and regulations.

**Rated: 15A-125V**

**NOTE:** Use with Jr. Hard Service Cord, 16/3 to 12/3 AWG, 0.250" to 0.437" dia. COPPER WIRE ONLY!

**TO INSTALL:**

1. Unscrew both assembly screws.
2. Remove cord jacket and insulation as shown.

**WARNING:** Do not cut or damage jacket or insulation except as indicated below.

3. Feed cord through body.
4. Connect wires to terminal screws as follows: Black (HOT) to BRASS screw. White (NEUTRAL) to SILVER screw. Green (GROUND) to GREEN screw.  
Back out terminal screws until they stop turning (do not force past this point). Twist all copper strands of each wire tightly together. Loop wire clockwise 3/4 turn around screw shaft and tighten screw head securely over loop. Cut off any wire strands not secure under head.
5. Tighten cord clamp firmly.
6. Reassemble the cord outlet.

