### POP-UP RECEPTACLE

Cat. No. PFQP3



DI-000-PFQP3-05A

#### WARNINGS

- TO AVOID DEATH OR SERIOUS INJURY, never push objects of any kind into this product through openings, as they may touch dangerous voltages.
- TO AVOID FIRE, SHOCK OR DEATH, never touch uninsulated wires or terminals unless the wiring has been disconnected at the network interface.
- · Never install communications wiring or components during a lightning storm.
- Never install communications components in wet locations unless the components are designed specifically for use in wet locations.
- · Use caution when installing or modifying communications wiring or components.


#### **CAUTIONS**


- Install and/or use in accordance with appropriate electrical codes and regulations.
- Use only the electrical mounting box provided.
- · Use indoors only.
- For surfaces greater than 2 1/4" thick. (5.72 cm), use the overmount installation.
- If you are unsure about any part of these instructions, consult an electrician.

# **INSTALLATION INSTRUCTIONS**

**ENGLISH** 

## Includes:






Cat. No. PFQP3 Pop-Up Assembly with 3-Port QuickPort

## Before you install the pop-up receptacle

- Check under flooring to make sure there is enough clearance to accommodate the box assembly.
- Choose a mounting site where the top of the surface is smooth and free of dirt and surface irregularities.
- If there are surface irregularities, consider using a flexible sealant between mounting surface and pop-up assembly.



### Installation

# 1. Choose template and installation method


- For floors with access underneath, use undermount installation (See Template A), included.
- For surfaces greater than 2 1/4" thick. (5.72 cm), use the overmount installation (See Template B), included.

Subfloor

• For concrete installation, cut finished flooring to the size of the box.

### 2a. Undermount Installation of Box

- · Use Template A to cut opening.
- Remove the knockouts furthest from the front of the box. Pull the conductors through, leaving 6" (15.2 cm) inside of the box.
- Secure mounting brackets to underside of flooring using appropriate screws (not provided).



#### 2b. Overmount Installation of Box

- Use Template B. Rout the hatched areas 3/16" deep in the subflooring.
- Remove the knockouts furthest from the front of the box. Pull the conductors through, leaving 6" (15.2 cm) inside of the box.
- Secure mounting brackets to routed area using appropriate screws (not provided).
- Install finished flooring. NOTE: When finished flooring is installed, the box should be 1/8" to 1/4" below the surface of the finished flooring.


#### 2c. Concrete Installation of Box.

· Attach conduit and position box.

**NOTE:** The top of the floor box should extend above the poured concrete if additional flooring will be used. When finished flooring is installed, the floor box should be 1/8" to 1/4" below it.

NOTE: After conduit is connected, make sure 6" (15.2 cm) of cable is available inside box for connection.

- Attach protective plastic cover and block any open holes.
- · Pour concrete and let it cure.
- · Remove the protective cover.
- · Install finished flooring around box.




#### 3. Connect and install pop-up.

- Snap the pre-wired jack into the QuickPort frame, then route cables through electric box, ensuring that a strain relief bushing is in place. (not included).
- Mount assembly to box using the two mounting screws (26mm) provided. DO NOT
  use round head screw for mounting. They could impede full seating of the lid.
  CAUTION: To prevent overtightening of screws and deformation of assembly lid,
  use manual screwdriver only.

**NOTE:** For carpeted installation, before fastening top assembly, use sealing compound 1 in wide continuously around cutout under carpet.

· Test operation.



## Operation

- · Remove protective film.
- To open, press button. If device does not pop up when button is pushed, push down on top lid while pressing button.
- To close, press button while pushing down lid.
- $\bullet$  To clean, wipe with damp cloth. Do not use harsh cleaners.

# FOR CANADA ONLY

For warranty information and/or product returns, residents of Canada should contact Leviton in writing at Leviton Manufacturing of Canada Ltd to the attention of the Quality Assurance Department, 165 Hymus Blvd, Pointe-Claire (Quebec), Canada H9R 1E9 or by telephone at 1 800 405-5320.

#### **LIMITED 2 YEAR WARRANTY AND EXCLUSIONS**

Leviton warrants to the original consumer purchaser and not for the benefit of anyone else that this product at the time of its sale by Leviton is free of defects in materials and workmanship under normal and proper use for two years from the purchase date. Leviton's only obligation is to correct such defects by repair or replacement, at its option. For details visit www. leviton.com or call 1-800-824-3005. This warranty excludes and there is disclaimed liability for labor for removal of this product or reinstallation. This warranty is void if this product is installed improperly or in an improper environment, overloaded, misused, opened, abused, or altered in any manner, or is not used under normal operating conditions or not in accordance with any labels or instructions. There are no other or implied warranties of any kind, including merchantability and fitness for a particular purpose, but if any implied warranty is required by the applicable jurisdiction, the duration of any such implied warranty, including merchantability and fitness for a particular purpose, is limited to two years. Leviton is not liable for incidental, indirect, special, or consequential damages, including without limitation, damage to, or loss of use of, any equipment, lost sales or profits or delay or failure to perform this warranty obligation. The remedies provided herein are the exclusive remedies under this warranty, whether based on contract, tort or otherwise.