

# Power When You Need It, Concealed When You Don't




The Pop-Up Floor Box Receptacle offers a modern, practical way to attractively conceal electrical wiring devices in homes and businesses, while still providing accessibility to power when needed. Featuring a sleek low profile and stylish metal cover that recesses neatly into the floor when not in use, it takes only the press of a button to make the receptacle available.

The Pop-Up Floor Box Receptacle may be used to satisfy the appropriate code requirements for residential and commercial applications; it also offers protection from ingress of water spray when closed and meets or exceeds scrub water test for safety.

# Pop-Up Floor Box Receptacles are available in the following configurations:

- USB Charger/Tamper-Resistant Receptacle
- Self-Test Tamper-Resistant GFCI Receptacle
- Decora® Tamper-Resistant Receptacle
- 3-Port QuickPort Insert (Leviton connectors sold separately)





# Perfect for Residential and Commercial Applications

# Homes and Multifamily Units with

- Floor to ceiling windows
- Great rooms


Tile
Stone
Wood
Laminate
Carpet
Concrete
Vinyl

• Other open concept spaces

Flooring types:

## **Commercial Applications**

- Cafe/restaurants
- Hotels
- Shopping malls
- Offices, meeting rooms
- And more...



# Features

- Contoured top plate for enhanced aesthetics
- Side latch open/close mechanism prevents scratching of wiring device face
- $\bullet$  Low profile cover recesses when not in use, reducing above-floor height to only 1/4 inch
- Assembled with genuine Leviton wiring devices
- Pre-wired terminal block for easy wiring access and installation
- IP 44 Rated: protection from ingress of water spray from any direction when closed
- Meets or exceeds UL 514A requirements including scrub water test
- Tamper-resistant to comply with the latest NEC® requirements for tamper-resistant receptacles in residences and childcare facilities
- Adjustable concrete rated electrical box included
- Available in: Brushed Nickel, Black, Brass, and Bronze finishes





# **Specifications**

Description	PFUS1 15A USB Charger TR Receptacle	PFUS2 20A USB Charger TR Receptacle	PFGF1 15A Self-Test TR GFCI	PFGF2 20A Self-Test TR GFCI	PFTR1 15A TR Receptacle	PFTR2 20A TR Receptacle	PFQP3 3-Port QuickPort
Electrical Specifications							
Amperage	15A	20A	15A	20A	15A	20A	
Voltage	125V					Accepts all	
NEMA	5-15R	5-20R	5-15R	5-20R	5-15R	5-20R	QuickPort connectors
Pole	2						
Wire	3						
Material Specifications							
Pop-up face	Brass alloy						
Device face	Thermoplastic						
Mounting screws	Plated steel						
Box material	Coated steel						
Mechanical Specifications							
Box size	Standard 4"W x 4"L x 3"D						
Termination accom.	12-14 AWG n/a						n/2
Termination	Terminal block						11/ d
Standards & Certifications							
Certification/Listing	cETLus						
Applicable Standards	Conforms to UL STD 514A, Certified to CSA STD 22.2 No. 18.1, IP 44, NOM ANCE*						
Warranty							
Product Warranty	2-Year Limited						
	2-Year Limited						

\* excludes QuickPort model

# **Available Configurations**



USB Charger Tamper-Resistant Receptacles



Self-Test GFCI Tamper-Resistant Receptacles



**Tamper-Resistant Receptacles** 



3-Port QuickPort

# **Available Finishes**



Brushed Nickel (-BN)




Black (-MB)



Bronze (-BZ)

## **Dimensional Drawings**



### (Green Wire)

Cat. No.	Description	Rating	Color
PFUS1	Pop-Up Floor Box with 15A USB Charger Tamper-Resistant Receptacle	15A – 125V	BN, MB, BR, BZ
PFUS2	Pop-Up Floor Box with 20A USB Charger Tamper-Resistant Receptacle	20A - 125V	BN, MB, BR, BZ
PFGF1	Pop-Up Floor Box with 15A Self-Test GFCI Tamper-Resistant Receptacle	15A – 125V	BN, MB, BR, BZ
PFGF2	Pop-Up Floor Box with 20A Self-Test GFCI Tamper-Resistant Receptacle	20A - 125V	BN, MB, BR, BZ
PFTR1	Pop-Up Floor Box with 15A Tamper-Resistant Receptacle	15A – 125V	BN, MB, BR, BZ
PFTR2	Pop-Up Floor Box with 20A Tamper-Resistant Receptacle	20A - 125V	BN, MB, BR, BZ
PFQP3	Pop-Up Floor Box with 3-Port QuickPort	-	BN, MB, BR, BZ

To order colors, add suffix to Cat. No.: Brushed Nickel (-BN), Black (-MB), Brass (-BR), Bronze (-BZ)



**Ordering Information** 

### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747-3138 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538 Tech Line: 1-800-824-3005 Mon-Fri 8am-10pm EST, Saturday 9am-7pm EST

### Visit our Website at: www.leviton.com

 $\ensuremath{\mathbb{C}}$  2019 Leviton Manufacturing Co., Inc. All rights reserved.

