
## Product Specifications

# **ToggleTouch<sup>™</sup> Preset Toggle Dimmers**





Cat. No. TGI06-1L

### APPLICATION

The new ToggleTouch<sup>™</sup> Preset Toggle Dimmer provides a unique combination of toggle-style ON/OFF switching and digital touch-pad dimming technology. Leviton's ToggleTouch is designed for exceptional ease of operation with two fingertip-operated DIM and BRIGHT pads located alongside the toggle. ToggleTouch can be ganged with standard toggle-style switches in a wide variety of applications. The dimmer provides single-pole (one location) and 3-way (multi-location) control for incandescent and magnetic low-voltage lighting.

## FEATURES

- UL Listed (File # E-31373)
- CSA Certified (File # LR-3413)
- Universally-designed for smooth ON/OFF toggle action and fingertip-control touch dimming that's easy to operate.
- ToggleTouch dimmers available with locator light that illuminates when lights are off.
- Provides preset dimming with soft-ON feature (does not provide fade-OFF).
- Protected memory during temporary power failures ensures that ToggleTouch will retain last setting before power interruption.
- Provides single-pole and multi-location 3-way control when used with a 3-way ON/OFF switch.

- Built-in radio/TV interference filter.
- Use with Leviton DPSPE-112 Power Extender to extend load capacity to 2000W (2000VA) for incandescent, magnetic low-voltage and Advance Mark X<sup>™</sup> fluorescent dimming ballasts.
- Use with Leviton DPSPE-212 Power Extender to extend load capacity to 2000VA for Advance Mark VII<sup>™</sup> and Motorola Helios<sup>™</sup> fluorescent ballasts.
- Fits perfectly with Leviton standard toggle wallplates; gangs perfectly with all Leviton toggle switches.



ToggleTouch



#### STANDARDS SPECIFICATIONS

Controls shall be UL Listed Leviton Multi-Location Toggle Dimmer with Limited Two-Year Warranty, universal design for smooth ON/OFF toggle action, and fingertip-dimming control. Device shall feature Soft-ON feature, protected memory during temporary power failures, and a contour that fits with Leviton standard toggle wallplates. Device shall feature single-pole and 3-way control when used with a 3-way ON/OFF switch and locator light. Available in ratings and colors as scheduled on plan.

Performance Specifications		
Electrical	<ul> <li>Input 120 VAC @ 60Hz.</li> <li>Line voltage regulation.</li> <li>RFI noise suppression.</li> <li>Maximum load incandescent 1000 watts stand alone; 2000 watts with the use of a power extender.</li> <li>On/off switch provides air-gap for servicing; separate one not needed.</li> </ul>	
Mechanical	<ul> <li>Dimmer control – touch technology preset models only.</li> <li>Toggle on/off switch control.</li> <li>Two wire device plus ground wire for single pole models; and three wire device plus ground for 3 way models.</li> <li>The LED will be lighted when the load off.</li> </ul>	
Environmental	<ul> <li>Operating 0 degrees celsius to 55 degrees celsius.</li> <li>Non-operating –10 degrees celsius to 85 degrees celsius.</li> <li>Relative humidity, non-condensing 20% to 90%.</li> </ul>	

#### **ORDERING INFORMATION**

Cat. No.	Rating	Description
TGI06-1LW	600W	Incandescent, LED Locator
TGI06-10W	600W	Incandescent, no LED Locator, single-pole only
TGI10-1LW	1000W	Incandescent, LED Locator
TGM10-1LA	1000VA	Magnetic Low-Voltage Lighting, LED Locator

Available in White (-W), Ivory (-I), Almond (-A), \*Brown (- B), and Gray (-G) \* Brown 600W lighted only

#### Leviton's Limited Two-Year Warranty

This warranty gives you specific rights, and you may also have other rights, which vary in different states and countries. Leviton warrants to the original consumer purchaser that this product is free of defects in materials and workmanship for 2 years from the purchase date. Leviton's only obligation is to correct such defects by repair or replacement, at its option, if within such 2 years the product is returned prepaid, with proof of purchase date, and a description of the problem to the Leviton Manufacturing Co., Inc., ATTN: Quality Assurance Department, 59-25 Little Neck Pkwy, Little Neck, NY 11362-2591. This warranty does not cover labor for removal or reinstallation of the product and is void on any product installed improperly or in an improper environment, overloaded, misused, opened, abused, or altered in any manner. There are no implied warranties of any kind, but if implied warranties are required by the applicable jurisdiction, Leviton limits the duration of any implied warranty of fitness for use or merchantability to 2 years. Leviton is not liable for incidental or consequential damages, including without limitation, loss of equipment use and lost sales or profits for breach of any warranty on this product. Some jurisdictions may not allow exclusions or limitations may not even apply to you.



Leviton Mfg. Co., Inc. 59-25 Little Neck Pkwy • Little Neck, NY 11362 • Phone: (800) 323-8920 • Fax: (800) 832-9538