

# **Duplex Receptacles**

# Heavy-Duty Hospital Grade 15 A & 20 A, 125 V

Brass self-grounding clip is permanently staked on for secure and reliable performance

Wide receptacle face shelf provides exceptional support to the wallplate or box cover

Body and face made of impact-resistant advanced engineering polymer for extreme durability

"Universal" strap design provides ample support for electrical box installations, and includes multiple "break-off" tabs to eliminate interference with virtually any cover or wall plate

**Common Applications:** 


- Commercial Buildings
- Transportation Facilities
- Municipal Buildings
- **Educational Facilities**
- Hospitals/Medical Buildings

Ground terminal clamp allows for both back and side wiring

provide superior clamping force and

clamps allow for and provide visual verification of termination and a faster, easier

Molded in ribs prevent terminal screws from making contact with wall box



#### **Ordering Information**

Ratings		15 A/ 125 V	20 A/ 125 V	
NEMA Config		5-15R	5-20R	
Order ID	Brown	8200-H	8300-H	
	lvory	8200-HI	8300-HI	
	White	8200-HW	8300-HW	
	Gray	8200-HGY	8300-HGY	
	Red	8200-HR	8300-HR	
	Blue	8200-HBU	8300-HBU	
	Yellow	8200-HY	_	
	Light Almond	8200-HT	8300-HT	


### **Specifications**

Rating	8200-H	8300-H		
AC Horsepower Rating				
At Rated Voltage	½ HP	1 HP		
Electrical Specification	,=			
Amperage	15 A	20 A		
NEMA	5-15R	5-20R		
Voltage	125 V			
Grounding	Self-Grounding*			
Pole	2			
Wire	3			
Dielectric Voltage	Withstands 3000 V min			
Temperature Rise	Max 30 °C after 250 Cycles Overload at 200% rated current			
Environmental Specifications				
Flammability	UL94 V0			
Operating Temperature	Maximum continuous 75 °C, minimum -40 °C (w/o impact)			
Material Specifications				
Face	PBT Polyester Blend			
Body	PBT Polyester Blend			
Strap	Steel (Galvanized G60)			
Ground Contact	0.030" Brass			
Mounting Screw	Triple-Drive Plated Steel			
Ground Screw	#8 Hex Head, Triple-Drive Brass			
Line Contacts	0.030" Phosphor Bronze			
Terminal Clamp	Brass			
Terminal Screws	#8 Triple-Drive Brass			
Ground Clip	Brass			
Mechanical Specifications				
Product ID.	Ratings are permanentl	y marked on the device		
Terminal ID	Brass - Hot, Silver - Neutral, Green - Ground			
Terminal Accommodation	#14 - #10 AWG			
Wire Types	Solid or Stranded			
Termination	Back and Side Wire			
Standards & Certifications				
NEMA	WD 1 & WD 6			
ANSI	C-73			
Certification/Listing	cULus, NOM-ANCE			
Applicable Standards	UL498, Fed Spec W C 596, CSA C22.2 NO. 42			
RoHS	RoHS Compliant			
Warranty				
Product Warranty	10 Y	'ears		


## \*Self Grounding when installed in a properly grounded metallic box

#### **Dimensions**

Front View



Side View



Visit our Website at:
www.leviton.com/commercial
email: commercial@leviton.com

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

© 2018 Leviton Manufacturing Co., Inc. All rights reserved.

