

Duplex Receptacles

Heavy-Duty Industrial Specification Grade 15 A & 20 A, 125 V

Brass self-grounding clip is permanently staked on for secure and reliable performance

Wide receptacle face shelf provides exceptional support to the wallplate or box cover

Body and face made of impact-resistant advanced engineering polymer for extreme durability

"Universal" strap design provides ample support for electrical box installations, and includes multiple "break-off" tabs to eliminate interference with virtually any cover or wall plate


Common Applications:

- Commercial Buildings
- Transportation Facilities
- Municipal Buildings
- **Educational Facilities**

Molded in ribs prevent terminal screws from making contact with wall box

Ordering Information

<u> </u>				
Ratings		15 A/ 125 V	20 A/ 125 V	
NEMA Config		5-15R	5-20R	
Order ID	Brown	5252	5352	
	lvory	5252-l	5352-I	
	White	5252-W	5352-W	
	Gray	5252-GY	5352-GY	
	Red	5252-R	5352-R	
	Blue	5252-BU	5352-BU	
	Black	5252-E	5352-E	
	Light Almond	5252-T	5352-T	




Specifications

Rating	5252	5352		
3	3232	3332		
AC Horsepower Rating				
At Rated Voltage	½ HP	1 HP		
Electrical Specification	1			
Amperage	15 A	20 A		
NEMA	5-15R	5-20R		
Voltage	125 V			
Grounding	Self-Grounding*			
Pole	2			
Wire	3			
Dielectric Voltage	Withstands 3000 V min			
Temperature Rise	Max 30° C after 250 Cycles Overload at 200% rated current			
Environmental Specifications				
Flammability UL94 V0		4 V0		
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)			
Material Specifications				
Face	PBT Polyester Blend			
Body	PBT Polyester Blend			
Strap	Steel (Galvanized G60)			
Ground Contact	0.030" Brass			
Mounting Screw	Triple-Drive Plated Steel			
Ground Screw	#8 Hex Head, Triple-Drive Brass			
Line Contacts	0.030" Phosphor Bronze			
Terminal Clamp	Brass			
Terminal Screws	#8 Triple-Drive Brass			
Ground Clip	Brass			
Mechanical Specifications				
Product ID.	Ratings are permanent	y marked on the device		
Terminal ID	Brass - Hot, Silver - Neutral, Green - Ground			
Terminal Accommodation	#14 - #10 AWG			
Wire Types	Solid or Stranded			
Termination	Back and Side Wire			
Standards & Certifications				
NEMA	WD 1 & WD 6			
ANSI	C-73			
Certification/Listing	cULus, NOM-ANCE			
Applicable Standards	UL498, Fed Spec W C 596, CSA C22.2 NO. 42			
RoHS	RoHS Compliant			
Warranty				
Product Warranty	10 Y	ears		
	I			


*Self Grounding when installed in a properly grounded metallic box

Dimensions

Front View



Side View



Visit our Website at:
www.leviton.com/commercial
email: commercial@leviton.com

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005



