


SOLUTION BRIEF

IT/AV SYSTEMS FOR HUDDLE SPACES

Huddle spaces are an integral part of any business environment, and they depend on a state-of-the-art combination of IT and audiovisual systems to support seamless operations. Leviton solutions provide easy connection, switching, and extension of HDMI® and VGA signals to displays or projectors anywhere in the room, all networked over easy-to-install category-rated cable. These solutions help facilitate the smooth transition of audiovisual presentations during meetings and conference calls.

- Simple, plug-and-play solutions
- Autoswitching wallplate for two HDMI and one VGA source supports seamless content and screen switches
- VGA input is scaled to 1080p output for automatic image sizing at display
- Simple installation: only requires a single Cat 6A patch cord
- HDBaseT certification for assurance that comes from third-party verification and certification of AV signal transmission performance
- Uses Power-over-HDBaseT (PoH) to power the autoswitching wallplate from the receiver at the display – no power is required at the tabletop – freeing floor or table outlets for device power and charging



SIGNAL EXTENSION

- HDBaseT™ Class B Extender delivers 230 ft (70 m) transmission for HDMI®, bi-directional IR, RS232, and power
- Supports key features of HDMI 1.4, including 3D, 4K, 2K, CEC passthrough, and HDCP compatible
- Power supply and mounting brackets included



PART NUMBERS

HDMI® & VGA Autoswitching HDBaseT™ Extender Wallplate	41920-HRC
HDBaseT Extender Receiver, 70 m	41910-HTR

ATLAS-X1™ CAT 6A PATCH CORDS

- SlimLine boot cords feature narrow profile to reduce congestion in high-density applications
- Snagless boot design prevents tab breakage
- AXT suppression and EMI/RFI protection



PART NUMBERS

Atlas-X1 Component-Rated SlimLine Boot Patch Cord	6AS10-xx*
---	-----------

xx = Length: 3' (03), 5' (05), 7' (07), 10' (10), 15' (15), 20' (20)

* = Color: Yellow (Y), Red (R), Black (E), White (W), Blue (L), Green (G), Grey (S)

For assistance customizing your cords, please visit Leviton.com/configurator or call Tech Support at 800.824.3005.

HDMI® CABLES

- CL2 rated for in-wall installation
- Flexible commercial-grade 28-gauge construction
- Gold-plated connectors for long-lasting performance
- Cable Lock Kit secures cable to Leviton Signal Extension devices for permanent installations



PART NUMBERS

High-Speed HDMI Cable with Ethernet	41900-xxE
HDMI Cable Lock Kit	41900-LKT

xx = Length: 3' (03), 6' (06), 10' (10), 15' (15)

ATLAS-X1 CAT 6A COMPONENT-RATED CONNECTOR

- Wire manager allows fast, secure, repeatable terminations
- Tool-free design requires no specialized termination tool
- Patented Retention Force Technology (RFT) protects from time damage from 4- or 6-pin plugs
- Interchangeable icons (VOICE, DATA, AV)
- Shielded connectors provide EMI/RFI protection, signal isolation, and AXT suppression



PART NUMBERS

Atlas-X1 Cat 6A Component-Rated Connector	6AUJK-R*6
---	-----------

* = Color: White (W), Light Almond (T), Ivory (I), Yellow (Y), Orange (O), Crimson (C), Dark Red (R), Purple (P), Blue (L), Green (V), Gray (G), Black (E), Brown (B)

DECORA® DUAL-GANG STAINLESS-STEEL WALLPLATES

- Accept a variety of inserts for voice, data, and video applications
- Smooth face and rounded edges resist dust accumulation
- Stainless-steel design supports easy cleaning and enhanced durability



PART NUMBERS

Decora, Dual-Gang Standard Size, Stainless	84409-040
--	-----------

Design your Huddle Space system with the
Leviton IT/AV System Designer at Leviton.com/ITAV.