

Meeting Additional Power Needs in Health Care Facilities



Hospital Grade 4-in-1 Receptacles provide a simple transition in retrofit applications to comply with new receptacle requirements in health care facilities. These devices allow you to increase the number of receptacles in your facility without having to pull new wires.

Both the 2012 Edition of the NFPA 99 and the 2014 Edition of the National Electrical Code are applying new patient care room definitions for the minimum number of receptacles required:

NFPA 99, 2012 Edition, Section 6.3.2.2.6.2 – “The number of receptacles shall be determined by the intended use of the patient care rooms in accordance with...”

- **Receptacles for Patient Bed Locations in General Care Areas (Category 2).** Each patient bed location shall be provided with a minimum of **8** receptacles.
- **Receptacles for Patient Bed Locations in Critical Care Areas (Category 1).** Each patient bed location shall be provided with a minimum of **14** receptacles.
- **Receptacles for Operating Rooms (Category 1).** Operating rooms shall be provided with a minimum of **36** receptacles.

NEC/NFPA 70, 2014 Edition, Article 517.18(B) – “Each patient bed location shall be provided with a minimum of eight receptacles. They shall be permitted to be of the single, duplex, or **quadruplex type** or any combination of the three.

All receptacles shall be listed ‘hospital grade’ and shall be so identified.”



1254-HW

Features:

- Surge Protective and Isolated Ground versions available
- Accommodates up to 4 Fed Spec size straight or angled plugs
- Terminal Wiring Screws fit Inside a Standard Single Gang, 4” Octagon, and 4” Square Wall Box
- Adapter Plate (Cat. No. 4254) Required for 2-Gang and 4 11/16” Square Wall Box Installations
- Termination anchor holes for easy conductor wiring
- Easy-to-read voltage and amperage rating molded onto face
- Impact and chemical resistant nylon cover and base


Ordering Information

HOSPITAL GRADE			
Description		15A	20A
4-in-1 Receptacles	White	1254-HW	21254-HW
	Ivory	1254-HI	21254-HI
	Gray	-	21254-HGY
	Brown	1254-H	21254-H
	Red	1254-HR	21254-HR
4-in-1 Receptacles, Isolated Ground	Orange	1254-IG	21254-IG
	White	-	21254-IGW
	Ivory	-	21254-IGI
4-in-1 Receptacles, Surge Protective	White	8480-W	8490-W
	Ivory	8480-I	8490-I
	Red	8480-R	8490-R
4-in-1 Receptacles, Surge Protective, Isolated Ground	Orange	-	8490-IG
	White	8480-IGW	-
	Ivory	8480-IGI	8490-IGI
	Blue	8480-IGB	8490-IGB


ADAPTER PLATES		
Description		Cat. No.
4-in-1 Adapter Plates	White	3254-W
	Ivory	3254-I
	Gray	3254-GY
	Black	3254-E
	Red	3254-R
	Brown	3254
	Blue	3254-BLU
	Orange	3254-OR

Dimensions

4-in-1 Receptacles



Adapter Plates



Visit our Website at:
www.leviton.com/industrial
 email: industrial@leviton.com

Q-919

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
 Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

© 2014 Leviton Manufacturing Co., Inc. All rights reserved.

090314

