

Decora® Wireless 0-10V Low Voltage Wall Dimmer



Description

The Decora® Wireless 0-10V Low Voltage Wall Dimmer (ZS057-ALZ) is a robust, low voltage rocker manual switch with a dimming bar used to provide control of any 0-10V dimming ballast or LED driver. 24VDC is supplied by an OPP20 power pack which also switches the load ON and OFF. Requires use with Lumina™ RF Keypad Room Controller or GreenMAX® DRC Wireless Keypad Room Controller.


Features

- Use as a standalone dimmer with an OPP20 power pack or as part of a wireless system
- Compatible with multiple load types—any 0-10V controlled load, ex: LED, HID, inductive, fluorescent
- Aesthetically pleasing intuitive design—rocker switch and slender raise/lower side bar for ON/OFF, raise/ lower control
- Wireless mesh network—self-healing mesh network has no hardwired backbone and connects all products together for a more robust and reliable wireless system


Features, cont'd

- Requires a room controller to wirelessly operate within a mesh network
- Brightness Indicators
 - LEDs illuminate for 5 seconds when lighting level is changed
- Status LED
- Illuminates momentarily at button press
- Wireless 3-way switching and dimming when used with a room controller
- Standard size for seamless installation—fits in a standard single-gang wall box
- Available in White with Color Change Kit available for Ivory and Light Almond
- Complies with IEEE 802.15.4 standards—for domestic and international wireless networks
- Can be used as a component in a system to meet energy code requirements for IECC, ASHRAE 90.1, and 2022 Title 24, Part 6 space/area control, dimming, manual-ON/OFF occupancy/vacancy control and automatic shutoff requirement

Wiring Diagram




Dimensions Diagram



Leviton Manufacturing Co., Inc. Lighting & Controls



User Interface



Specifications

•	
Electrical	
Input Voltage	24VDC
Input Current	20mA
UL Impulse Voltage	800V (24V Circuit), 4000V (0-10V Circuit)
Network Connections	IEEE 802.15.4, 2.4GHz, wireless, mesh network up to 75 ft (22.86m) range between devices
Environmental	
Operating Temperature	32°F to 104°F (0°C to 40°C)
Storage Temperature	-40°F to 185°F (-40°C - 85°C)
UL Pollution Degree	2
Other	
Energy Codes	Can be used as a component in a system to meet energy code requirements for IECC, ASHRAE 90.1, and 2022 Title 24, Part 6 space/area control, dimming, manual-ON/OFF occupancy/vacancy control and automatic shutoff requirements
Listings	UL, NOM
Dimensions	4.13" x 2.12" x 1.43" (104.90mm x 53.95mm x 36.43mm)
Weight	.51lbs (.23kg)
Warranty	5-Year

Ordering Information

Decora Wireless 0-10V Low Voltage Wall Dimmer	
Cat. No.*	Description
ZS057-ALZ	Decora Wireless 0-10V Low Voltage Wall Dimmer, 2.4GHz, 24VDC, 0-10V Sinking, 20mA, Color: White, Light Almond, Ivory
DDKIT-00x	Decora Color Change Kit

^{*} Replace x to indicate color: (W) = White, (I) = Ivory, (T) = Light Almond, (G) = Gray (R) = Red, (E) = Black

Leviton Manufacturing Co., Inc. Lighting & Controls

10385 SW Avery Street, Tualatin, OR 97062 tel 800-736-6682 tech line (6:00AM-4:00PM PT Mon-Fri) 800-959-6004

Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 tel 800-323-8920 tech line (8:00AM-10:00PM ET Mon-Fri, 9:00AM-7:00PM ET Sat, 9:00AM-5:00PM ET Sun) 800-824-3005