

QuickPort® Duplex Type-106 Inserts

APPLICATION

QuickPort Duplex Type-106 Inserts accept all individual QuickPort snap-in modules (sold separately). Use to support multimedia applications where a flush-mount electrical-wallplate look is desired, or where there will be multiple devices—or a combination of electrical and voice/data devices—under a multi-gang wallplate. Available in ivory, light almond, white, grey, and black.





4-Port Insert

2-Port Insert

SPECIFICATION

The workstation connector housing shall be a fieldconfigurable NEMA-style housing that mounts flush in standard NEMA openings, and under standard duplex electrical wallplates in single or multiple gangs. It shall provide ports which are field configurable with a variety of simplex snap-in connector modules. The insert shall be constructed of high-impact, fire-retardant plastic rated UL 94V-0, and be UL Listed, and compliant with ANSI/TIA-568-C.0 specifications. Colors, configurations, and related wallplates to be specified per schedule on plan. The manufacturer shall provide a one-year limited product warranty and 15-year product performance guarantee. The manufacturer shall provide a lifetime warranty against defects in material and workmanship. and an application guarantee when installed as part of a certified system.

FEATURES

- · Fits within minimum NEMA openings
- Compatible with all individual QuickPort modules
- Brass-threaded insert for wallplate screw facilitates installation
- Narrow module width allows high port density in a small area
- The Quad 106 features a built-in termination station which stabilizes connectors during punchdown
- · Fits Decora® and duplex wallplates

DESIGN CONSIDERATIONS

- Use where a flush-mount electrical-style wallplate look is desired
- Fits most locations where NEMA duplex opening exists (including floor monuments, access floor boxes, power poles, poke-through fixtures, etc.)
- If ganged with electrical devices, a barrier box must be used
- Put blanks (41084-BxB) in unused ports for future expansion
- Specify port identification method (colored modules, designation labels, and custom silk-screening are available). To ID ports, use different colored connectors for each application, or Leviton preprinted Port Designation Labels (41080-LEB)

STANDARDS COMPLIANCE

4-Port Insert: UL Listed, CSA certified, and ANSI/TIA-568-C.0

2-Port Insert: cULus listed and ANSI/TIA-568-C.0

PHYSICAL SPECIFICATIONS

Dimensions: See page two

Materials: High-impact, fire-retardant plastic rated UL 94V-0

Capacity: Two or four ports

COUNTRY OF ORIGIN

4-Port Insert: Mexico 2-Port Insert: USA

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

Page 1 of 2

Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416

tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com

Asia / Pacific

T+33.6.8869.1380

Europe

T +1.631.812.6228 E infoasean@leviton.com

T +1.514.954.1840 E pcservice@leviton.com

Canada

India / SAARC T +971.4.886.4722 E infoindia@leviton.com Caribbean T +1.954.593.1896

T +52.55.5082.1040

E infocaribbean@leviton.com Mexico

E lsamarketing@leviton.com

Middle East & Africa T +971 4 886 4722

E infochina@leviton.com

T +852.2774.9876

China

Colombia **T** +57.1.743.6045 E infocolombia@leviton.com


South Korea T +82 2 3273 9963 E Imeinfo@leviton.com E infokorea@leviton.com


E infoeurope@leviton.com



ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.





PART NUMBERS					
Description	IVORY	LT. ALMOND	WHITE	GREY	BLACK
QuickPort® Duplex Type-106 Insert, 2 Ports	41087-2IP	41087-2TP	41087-2WP	41087-2GP	41087-2EP
QuickPort Duplex Type-106 Insert, 4 Ports	41087-QIP	41087-QTP	41087-QWP	41087-QGP	41087-QEP

Note: QuickPort snap-in connector modules and duplex electrical wallplates are sold separately. Please refer to the QuickPort connector spec sheets and the Leviton catalog for ordering information.

Page 2 of 2

F14 4961

Leviton Network Solutions Asia / Pacific Canada Caribbean China Colombia 2222 - 222nd St. SE T +1.631.812.6228 **T** +1.514.954.1840 T +1.954.593.1896 T +852.2774.9876 **T** +57.1.743.6045 Bothell, WA 98021-4416 E infoasean@leviton.com E pcservice@leviton.com E infocaribbean@leviton.com E infochina@leviton.com E infocolombia@leviton.com tel 1-800-824-3005 India / SAARC Mexico Middle East & Africa South Korea Europe tel +1-425-486-2222 T +33.6.8869.1380 T+971.4.886.4722 **T** +52.55.5082.1040 T+82.2.3273.9963 **T** +971.4.886.4722 appeng@leviton.com E infoeurope@leviton.com E infoindia@leviton.com E lsamarketing@leviton.com E Imeinfo@leviton.com E infokorea@leviton.com www.leviton.com