

## Angled Single-Gang QuickPort® Wallplates

### APPLICATION

Angled single-gang wallplates accept QuickPort snap-in modules to support multimedia applications with 2 or 4 ports. Use where an economical one-piece, single-gang flush-mount housing is desired. Available in three colors (white, light almond, and ivory) with color-matched screws.



### SPECIFICATION

The wallplate housing shall be a one-piece, single-gang flush-mount style that fits standard NEMA openings. It shall provide 2 or 4 ports and feature an angled design to facilitate optimal cable management. Must be able to accept all Leviton UTP, Fiber, or AV QuickPort modules. It must be made of high-impact, fire-retardant plastic rated UL 94V-0, and be cULus Listed and compliant with ANSI/TIA-568-C.0 specifications.

### FEATURES

- Angled ports facilitate optimal cable management, ensuring proper bend radius compliance in front and back of connector
- Recessed ports protect jack and patch cord plug
- Color-matched wallplate screws
- Fits within minimum rectangular NEMA openings
- Compatible with all individual UTP, Fiber, and AV QuickPort modules\*
- Individual port configurability allows specification flexibility
- Ideal for CAT 6A applications at the workstation

### DESIGN CONSIDERATIONS

- Fits standard NEMA single-gang backboxes
- For future expansion, install blanks (41084-B\*B) in unused ports
- Specify port identification method (colored modules, designation labels, and custom silk-screening available). To identify ports, use different colored jacks for each application, or Leviton pre-printed adhesive Port Designation Labels (41080-LEB)

### STANDARDS COMPLIANCE

- cULus Listed (UL 1863 & CAN/CSA-C22.2 No. 182.4)
- ANSI/TIA-568-C.0

### PHYSICAL SPECIFICATIONS

- Dimensions: See page two  
Capacity: Available in 2- or 4-port versions  
Materials: High-impact, fire-retardant plastic rated UL 94V-0  
Mounting: Color-matched screws

### COUNTRY OF ORIGIN

Taiwan

### WARRANTY INFORMATION


For a copy of Leviton product warranties, visit [www.leviton.com/warranty](http://www.leviton.com/warranty).

\* Due to product dimensions, shielded connectors must be installed horizontally (side-by-side). Shielded connectors installed vertically will not fit correctly into a QuickPort wallplate.

**ELECTRONIC FILES**


For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit [www.leviton.com](http://www.leviton.com).

41081-2xP



41081-xxP

41081-4xP



**PART NUMBERS**

Description	WHITE	LT. ALMOND	IVORY
Angled Single-Gang QuickPort® Wallplate, 2 Ports	41081-2WP	41081-2TP	41081-2IP
Angled Single-Gang QuickPort Wallplate, 4 Ports	41081-4WP	41081-4TP	41081-4IP

**NOTE:** QuickPort snap-in modules (connectors and bulkhead connectors and couplings) are sold separately. Please refer to the QuickPort module spec sheets for ordering information.

**Leviton Network Solutions**  
2222 - 222nd St. SE  
Bothell, WA 98021-4416

**Asia / Pacific**  
T +1.631.812.6228  
E infoasean@leviton.com

**Canada**  
T +1.514.954.1840  
E pcservice@leviton.com

**Caribbean**  
T +1.954.593.1896  
E infocaribbean@leviton.com

**China**  
T +852.2774.9876  
E infochina@leviton.com

**Colombia**  
T +57.1.743.6045  
E infocolombia@leviton.com

tel 1-800-824-3005  
tel +1-425-486-2222  
appeng@leviton.com  
[www.leviton.com](http://www.leviton.com)

**Europe**  
T +33.6.8869.1380  
E infoeurope@leviton.com

**India / SAARC**  
T +971.4.886.4722  
E infoindia@leviton.com

**Mexico**  
T +52.55.5082.1040  
E lsamarketing@leviton.com

**Middle East & Africa**  
T +971.4.886.4722  
E lmeinfo@leviton.com

**South Korea**  
T +82.2.3273.9963  
E infokorea@leviton.com