

Outdoor/All-Weather Loudspeakers Powered by JBL®

Leviton Architectural Edition®



APPLICATION

JBL Outdoor/All-Weather Loudspeakers are a high performance speaker system with weather-resistant ported bass-reflex enclosures. Use the speakers in any outdoor or utility application where the specifications call for sound quality and clarity from a durable, flexible design.

These two-way speakers can withstand direct exposure to the elements in outdoor applications because they are fully weatherized right down to their professional-grade grilles and input connectors, just like their professional counterparts. The speaker cone is polymer-coated cellulose fiber for greater resistance to the elements.

The best results are achieved and long-term performance improved by mounting any outdoor speaker in a sheltered location, such as under an eave or overhang. They are also ideal for indoor pools, atriums, and other large open spaces where enclosure speakers are desired and large-area coverage is needed.

FEATURES

- High-power amplification produces realistic bass with low distortion
- Speaker design and quality cones offer a wide range of frequencies for the perfect listening experience
- Frequency response offers a full range of sound, from deep bass to ultra high
- FreeFlow™ flared port
- Sold in pairs
- Mounting brackets included: two rotatable wall-mount brackets (including bar wrench and backup cords)

DESIGN CONSIDERATIONS

- Outdoor speakers are all-weather; however, they are not waterproof. Speakers should not be submerged or directly exposed to water, ice, snow, or sustain moisture.

PHYSICAL SPECIFICATION

- Dimensions: Height 9" (229 mm)
- Width 6.2" (157 mm)
- Depth 5.6" (142 mm)
- Weight: 4.3 lbs (2.0 kg) per speaker
- Color: White (finish and grille color)
- Driver Complement: 0.5" (12 mm) titanium-laminate tweeter
- 4" (100 mm) woofer
- Weight: 7.8 lb/3.5 kg per speaker
- Sold in pairs

PERFORMANCE SPECIFICATIONS

- Frequency Response (-3dB): 80 Hz-20 kHz
- Sensitivity (2.83V/1m): 86 dB
- Power Handling (peak/continuous): 200/50 Watts
- Impedance: Nominal 8 Ohms

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

Leviton Manufacturing Co., Inc. Global Headquarters

201 N. Service Rd. Melville, NY 11747-3138 Tech Line: 1-800-824-3005 Fax: 1-800-832-9538

Leviton Manufacturing Co., Inc. Energy Management, Controls and Automation.


4330 Michoud Blvd., New Orleans, LA, 70129 Tel: 1-504-736-9810 Fax: 1-504-253-2954

Visit our Website at: www.leviton.com/emca


©2016 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

ELECTRONIC FILES


For CAD files, typical specs, or technical drawings (.DXF, .DWG, VISIO), visit www.leviton.com.



Front



Side



Rear

ORDERING INFORMATION

DESCRIPTION	CAT. NO.
Pair of Leviton Architectural Edition® powered by JBL® Outdoor Loudspeakers	AEAWS-C1W

Leviton Manufacturing Co., Inc. Global Headquarters

201 N. Service Rd. Melville, NY 11747-3138 Tech Line: 1-800-824-3005 Fax: 1-800-832-9538

Leviton Manufacturing Co., Inc. Energy Management, Controls and Automation.

4330 Michoud Blvd., New Orleans, LA, 70129 Tel: 1-504-736-9810 Fax: 1-504-253-2954

Visit our Website at: www.leviton.com/emca

©2016 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

SAT-10087