



Vizia Lighting Controls

by Leviton

Beautiful Inside and Out





Varying the amount of light with Vizia dimmers can add beauty and drama, make a small room look open and spacious, or a large room appear intimate and inviting.



A New Vision for Residential and Commercial Lighting Control

Choosing lighting controls for every room in your home has never been simpler thanks to Vizia™ -- Leviton's most advanced statement in residential lighting control technology. Integrated into a stylish new form factor compatible with Leviton's hallmark Decora® design, Vizia lighting controls are setting a new standard among decorators, builders and homebuyers everywhere. They are ideal for new construction as well as retrofit applications. Because they are compliant with commercial grade electrical standards, they can be used in a host of commercial and light commercial applications from restaurants and medical offices to hotels and office buildings.





Elegance, Precision and Practicality


Vizia's striking good looks speak to the advanced technologies underneath the surface and the possibilities they promise. An all-digital design, coupled with an elegantly simple user interface, results in an exceptionally intuitive, easy-to-operate control.

Uncluttered and streamlined, Vizia complements a wide range of decorating styles, and delivers a performance and aesthetic return for a relatively small investment. Best of all, it is completely compatible with Decora® screwless and standard wallplates, as well as Leviton's line of Decora® wiring devices. The end result: a family of lighting controls that provides a touch of class as well as significant energy savings.

DIMMING THE LIGHTS THIS MUCH	REDUCES ENERGY CONSUMPTION BY	AND EXTENDS BULB LIFE
10%	10%	2x longer
25%	20%	4x longer
50%	40%	20x longer
75%	60%	More than 20x

Vizia lighting products make a beautiful statement in public areas such as restaurants, conference rooms, professional offices, specialty retailers and boutiques.





- When lights are OFF, you can change the light level that the lights will turn ON to by using DIM/BRIGHT bar
- When power is restored after a power outage, lights will return to last setting prior to power interruption

Vizia's patent-pending, return-to-neutral device design provides the ultimate in visual and tactile appeal. No line breaks or irregular shadow patterns ever detract from their pleasing, symmetrical appearance.

Because all Vizia dimmers use digital technology, they add touches of elegance and precise control with features such as soft fade-on/fade-off, selectable fade rates and minimum brightness levels. You can program a customized preset "on" level every time, change the dimming level without turning on the lights and, thanks to a 10-second delayed-off feature, you have ample time to leave a room or go to bed before the lights turn off.

Touch the dimmer's push pad and the lights turn on to the last set level. When a matching remote is installed, it tracks and displays the same green LED light.

Vizia Benefits

- Adjusts lighting to set a mood or perform a task
- Accents artwork, collectibles and architectural features
- Reduces glare on a computer or TV screen
- Adjustable fade rates can create smooth transitions between brightness levels
- Adjusts lights to a perfect level with a single touch of a button
- Conserves energy and extends bulb life
- Remotes available for multi-location dimming

The Vizia Collection



Dimmer
Fan Speed Control
Matching Dimmer Remote
Matching Fan Speed Control

Coordinating Dimmer Remote

Switch
Matching Switch Remote

Coordinating Switch Remote

Colors

Vizia dimmers are available in boxes with three color options: ivory, white and almond or ivory, white and light almond. Vizia is also available in an eco-friendly white only option for select models.



Vizia wiring devices are offered in a broad range of specifications to accommodate different fixture types in residential and commercial applications.

Incandescent	Magnetic Low Voltage	Electronic Low Voltage	Fluorescent, Mk10® or Tu-Wire™	Fluorescent, Mk10	Fluorescent, Hi-lume® or Eco-10™	Fan Speed Control
600w-120vac 1000w-120vac	600va-120vac 1000va-120vac	400w-120vac 600w-120vac	1000va-120vac	1200va-277vac	8a-120vac 6a-277va	1.5a-120vac

Mark 10® Powerline is a registered trademark of Advance Transformer Co. Tu-Wire™ and Eco-10™ (Eco-Series) are trademarks of Lutron Electronics, Inc. Hi-lume® is a registered trademark of Lutron Electronics, Inc.

ROOMS TO CONSIDER FOR VIZIA LIGHTING CONTROLS

- Kitchen (especially combined kitchen and living areas)
- Dining Room
- Living Room
- Family Room (Great Room)
- Entry Hall
- Home Theater
- Bedroom
- Home Office
- Bathroom
- Patio/Deck



The Vizia Collection



Lighting Controls

VZI06-1L 600W-120VAC Incandescent Dimmer for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZM06-1L 600VA-120VAC Magnetic Low-Voltage Dimmer for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZM10-1L 1000W-120VAC Incandescent or 1000VA-120VAC Magnetic Low-Voltage Dimmer for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZE04-1L 400W-120VAC Electronic Low-Voltage Dimmer for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZE06-1L 600W-120VAC Electronic Low-Voltage Dimmer for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZX10-1L 1000VA-120VAC Fluorescent Dimmer for Mark 10® Powerline or Tu-Wire™ Ballasts for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZX12-7L 1200VA-277VAC Fluorescent Dimmer for Mark 10® Powerline Ballasts for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZH08-1L 8A-120VAC Fluorescent Dimmer for Hi-Lume® or Eco-10™ (Eco-Series) Ballasts for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZH06-7L 6A-277VAC Fluorescent Dimmer for Hi-Lume® or Eco-10™ (Eco-Series) Ballasts for single-pole, 3-way or more applications, with LED Locator and Brightness Display
VZF01-1L 1.5A-120VAC Quiet Fan Speed Control for single-pole, 3-way or more applications, with LED Locator and Fan Speed Display
VZS15-1L 15A-120VAC Non-Dimming Electronic Switch for single-pole, 3-way or more applications, with LED Locator

Remotes

VZ00R-1L 120VAC Matching Dimmer Remote to 120V Dimmers/Fan Speed Control for 3-way or up to 5 location applications, with LED Locator and Brightness or Fan Speed Display
VZ00R-7L 277VAC Matching Dimmer Remote to 277V Dimmers for 3-way or up to 5 location applications, with LED Locator and Brightness Display
VZ00R-10 120VAC Coordinating Dimmer Remote to 120V Dimmers/Fan Speed Control for 3-way or up to 10 location applications (No LED)
VZ0SR-1L 120VAC Matching Switch Remote to VZS15-1L Switch for 3-way or up to 5 location applications, with LED Locator
VZ0SR-10 120VAC Coordinating Switch Remote to all 120VAC dimmers and VZS15-1L Switch for 3-way or up to 10 location applications (No LED)

Vizia products meet all applicable UL, CSA and FCC requirements and feature a five-year limited warranty.

Note: Features and specifications are subject to change.

Leviton Manufacturing Co., Inc.

59-25 Little Neck Pkwy
Little Neck, NY 11362-2591
Telephone: 1-800-323-8920
Tech Line: 1-800-824-3005 (8:30 AM – 7:30 PM E.S.T. Monday – Friday)
Fax: 1-800-832-9538

Visit Leviton's Website at www.leviton.com/vizia

© 2006 Leviton Manufacturing Co., Inc.
Patents pending

S-771/B6 sw

