

ORDER FORM

Dockhead DH1 Small Power Outlet Box

8" X 10" POWER OUTLET BOX FOR MARINE:

- Preassembled with mini straight distribution block, wiring devices with weather-resistant covers, and front and bottom LED lights
- Allows up to 2 wiring devices (see locations A & B per diagram on next page)
- Can be ordered with or without stand

CONSTRUCTION:

- Polycarbonate housing

STANDARDS:

- NEMA 3R, UL-231, CSA 22.2 No. 29, NFPA 303, NFPA 70

WARRANTY:

- Housing: 5 years
- Wiring Devices: 1 year



DATE: _____

JOB NAME: _____

DISTRIBUTOR NAME & ACCOUNT NUMBER: _____

CITY: _____

STATE: _____

ZIP: _____

PO NUMBER: _____

CONTACT NAME: _____

EMAIL: _____

PHONE: _____

LEVITON SALES PERSON: _____



Visit our Website at:
www.leviton.com/powerpedestals
email: industrial@leviton.com

Q-1490B

121523

Leviton Manufacturing Co., Inc.
201 N Service Rd, Melville, NY 11747
Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2024 Leviton Manufacturing Co., Inc. All rights reserved.

ORDERING NUMBER:

Ordering example: DH1-30-30S-B-W-ST1-W12-M0-M0-B0-B0



DH1 - - - - -
 1 2 3 4 5 6 7 8 9 10 11

1 MODEL
DH1 Dockhead 8" x 10" Base Unit
 Includes Box, Mini Straight Distribution Block, LED Clear or Amber with Front and Bottom Lens

2 RECEPTACLE/BREAKER Device Location A
R0 No Receptacle
20S 20 Amp GFI Recept. w/Std. Brkr.
30S 30A (125V) Recept. w/Std. Brkr.
30E 30A (125V) Recept. w/30mA EPD Brkr.
50S 50A (125V) Recept. w/Std. Brkr.
50E 50A (125V) Recept. w/30mA EPD Brkr. (Uses 2-Pole 50A EPD Brkr./1-Pole 50A EPD Brkr. Unavail.)
50S2 50A (125/250V) Recept. w/Std. Brkr.
50E2 50A (125/250V) Recept. w/30mA EPD Brkr.
CO Cable Only Recept. Cvr. - 1 Conn. (Only Avail. in White)
C5 CAT5 Internet Conn.

3 RECEPTACLE/BREAKER Device Location B
R0 No Receptacle
20S 20 Amp GFCI Recept. w/Std. Brkr.
30S 30A (125V) Recept. w/Std. Brkr.
30E 30A (125V) Recept. w/30mA EPD Brkr.
50S 50A (1 25V) Recept. w/Std. Brkr.
50E 50A (125V) Recept. w/30mA EPD Brkr. (Uses 2-Pole 50A EPD Brkr./1-Pole 50A EPD Brkr. Unavail.)
50S2 50A (125/250V) Recept. w/Std. Brkr.
50E2 50A (125/250V) Recept. w/30mA EPD Brkr.
CO Cable Only Recept. Cvr. - 1 Conn. (Only Avail. in White)
C5 CAT5 Internet Conn.

4 RECEPTACLE COVER COLOR
WH White
B Blue
GR Green
T Tan
GY Gray
Y Yellow

5 LED Light Color
W Clear White
A Amber

6 STAND
ST0 No Stand
ST1 4 x 4 Stand - 2 Hangers

8 KILOWATT HOUR METERS Meter Location 1
M0 No Meter
SE1 Single Element Meter - QTY 1
DE1 Dual Element Meter - QTY 1
SE2 Single Element Meter - QTY 2
DE2 Dual Element Meter - QTY 2

10 SPARE BREAKER OPTION 1**
B0 No Breaker
B1 20A 1-Pole Std. Breaker
B1GFI 20A 1-Pole GFI Breaker
B2 20A 2-Pole Std. Breaker
B2GFI 20A 2-Pole GFI Breaker
B3 30A 1-Pole Std. Breaker
B32 30A 2-Pole Std. Breaker
B32GFI 30A 2-Pole GFI Breaker
B5 50A 1-Pole Std. Breaker
B52 50A 2-Pole Std. Breaker
B52GFI 50A 2-Pole GFI Breaker

11 SPARE BREAKER OPTION 2**
B0 No Breaker
B1 20A 1-Pole Std. Breaker
B1GFI 20A 1-Pole GFI Breaker
B2 20A 2-Pole Std. Breaker
B2GFI 20A 2-Pole GFI Breaker
B3 30A 1-Pole Std. Breaker
B32 30A 2-Pole Std. Breaker
B32GFI 30A 2-Pole GFI Breaker
B5 50A 1-Pole Std. Breaker
B52 50A 2-Pole Std. Breaker
B52GFI 50A 2-Pole GFI Breaker


7 WATER HOOKUP TYPE*
W0 No Water
W11 3/4" 1/4 Turn Water Valve - QTY 1
W21 3/4" Water Valve w/Backflow Preventer - QTY 1
W31 1/2" 1/4 Turn Water Valve - QTY 1
W41 1/2" Water Valve w/Backflow Preventer - QTY 1
W12 3/4" 1/4 Turn Water Valve - QTY 2
W22 3/4" Water Valve w/Backflow Preventer - QTY 2
W32 1/2" 1/4 Turn Water Valve - QTY 2
W42 1/2" Water Valve w/Backflow Preventer - QTY 2

9 KILOWATT HOUR METERS Meter Location 2
M0 No Meter
SE1 Single Element Meter - QTY 1
DE1 Dual Element Meter - QTY 1
SE2 Single Element Meter - QTY 2
DE2 Dual Element Meter - QTY 2

NOTES: * Water Hookup Types can only be selected if Stand (ST1) is selected. If No Stand (ST0) is selected, Water Hookup Type should default to "W0" No Water.
 ** Spare breaker location will vary.

QUANTITY:

NOTES:



CUSTOMER SIGNATURE X
 (Indicates build approval)

With this signature the customer acknowledges being advised that these Made-To-Order pedestals are non-cancelable, non-refundable, and non-returnable.