


RCA 110-Termination QuickPort® Connector

APPLICATION

The Leviton RCA 110-Termination QuickPort Connector is designed to locally distribute baseband audio/video signals at distances of 10 to 40 feet over UTP cabling. Featuring standard IDC slots for quick and easy terminations, this connector is compatible with a variety of patch panels and QuickPort and MOS wallplates, including flush- and surface-mount styles.



SPECIFICATION

The connector shall snap into any housing with the QuickPort name, including flush- and surface-mount outlets, Multimedia Outlet System, patch panels, and patch blocks. The connector shall have an oversized diameter and depth to accommodate larger, high-end audio/video male plugs. The connector housing shall be available in ivory, white, light almond, grey, and black. The insert shall be available in orange, red, white, yellow, blue, and green. The connector shall be UL listed, and all plastics used in construction of the module bodies shall be fire retardant with a UL flammability rating of 94V-0.

FEATURES

- Connectors fit all QuickPort wallplate housings, patch panels, and patch blocks
- 110 termination for use with category-rated UTP cable
- Oversize connector diameter and depth readily accommodates larger, high-end audio/video plugs (male)
- Gold-plated connector for increased durability
- Connector supports connectivity for up to two pairs; use both pairs to reduce wire losses in longer cable runs
- The body is available in five colors, and the insert is available in six colors for application identification

DESIGN CONSIDERATIONS

- RCA 110-Termination QuickPort Connector snaps into any housing with the QuickPort name, including flush- and surface-mount outlets, Multimedia Outlet System, patch panels, and patch blocks
- Secure connector to cable prior to snapping into faceplate or surface-mount housing
- Use separate cables for analog and digital signals
- Use with Category 5e or better cabling
- Check clearance behind proposed location of module, to ensure space for proper bend radius of cabling media
- RCA connector inserts are available in orange (PCM audio), red (right audio), white (left audio), yellow (video), blue (video), and green (video)
- The connector housing is available in ivory, white, light almond, grey, and black to match housing or wallplates

STANDARDS COMPLIANCE

Meets or exceeds all applicable standards: cULus listed.

PHYSICAL SPECIFICATIONS

Dimensions: See page two

Materials: Snap-in connector bodies are high-impact, fire-retardant plastic rated UL 94V-0

Body Colors: Ivory, white, light almond, grey, and black

Barrel Colors: Orange, red, white, yellow, blue, and green

COUNTRY OF ORIGIN


Mexico

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



40735-Rxx

PART NUMBERS

Description	Part No.
RCA 110-Termination QuickPort® Connector, ivory	40735-RxI
RCA 110-Termination QuickPort Connector, white	40735-RxW
RCA 110-Termination QuickPort Connector, light almond	40735-RxT
RCA 110-Termination QuickPort Connector, grey	40735-RxG
RCA 110-Termination QuickPort Connector, black	40735-RxE

x = Insert Colors: orange (O), red (R), white (W), yellow (Y), blue (L), and green (V)

Leviton Network Solutions
2222 - 222nd St. SE
Bothell, WA 98021-4416

Asia / Pacific
T +1.631.812.6228
E infoasean@leviton.com

Canada
T +1.514.954.1840
E pcservice@leviton.com

Caribbean
T +1.954.593.1896
E infocaribbean@leviton.com

China
T +852.2774.9876
E infochina@leviton.com

Colombia
T +57.1.743.6045
E infocolombia@leviton.com

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Europe
T +33.6.8869.1380
E infoeurope@leviton.com

India / SAARC
T +91.80.4322.5678
E infoindia@leviton.com

Mexico
T +52.55.5082.1040
E lsamarketing@leviton.com

Middle East & Africa
T +971.4.886.4722
E lmeinfo@leviton.com

South Korea
T +82.2.3273.9963
E infokorea@leviton.com