


Cat 6 110-Style Wiring Blocks

Wall-Mount and Rack-Mount Blocks

APPLICATION

Leviton Cat 6 110-Style Wiring Blocks provide a centralized location to easily terminate 22-26 gauge solid copper wire for telephone, voice, and data applications. The wall-mount and rack-mount blocks exceed Category 6 channel requirements.



SPECIFICATION

The cross-connect shall be Category 6 110-style wiring blocks, available for wall or rack mount. They shall provide 110 terminations supporting voice, security, and Category 6 data applications, including high megabit and shared-sheath applications when used with Category 6 rated cabling. The components shall be UL listed and ANSI/TIA-568.2-D compliant. Plastic bases and blocks shall be made of fire-retardant plastic rated UL 94V-0.

FEATURES

- Available in wall-mount and rack-mount configurations
- Include labels, label holders, and Category 6 C-4 clips

DESIGN CONSIDERATIONS

- Ideal where space limitations and low cost are factors.
- Port ID options: Use the label strips and holders provided

STANDARDS COMPLIANCE

ANSI/TIA-568.2-D
cULus Listed

COUNTRY OF ORIGIN

Taiwan

PHYSICAL SPECIFICATIONS

Dimensions: See page two

Materials: 110 wiring bases are made of fire-retardant plastic rated UL 94V-0; C-4 clips are made of fire-retardant plastic rated UL 94V-0 with solder plated IDCs

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

41AB6-xF4, 41DR6-1F4

Leviton Network Solutions

2222 - 222nd St. SE
Bothell, WA 98021-4416

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Asia / Pacific

T +1.631.812.6228
E infoasean@leviton.com

Europe

T +44.0.1592.772124
E customerserviceeu@leviton.com

Canada

T +1.514.954.1840
E pcservice@leviton.com
com

India / SAARC

T +971.4.886.4722
E infoindia@leviton.com

Caribbean

T +1.954.593.1896
E infocaribbean@leviton.com

Mexico

T +52.55.5082.1040
E lsamarketing@leviton.com

China

T +852.2774.9876
E infochina@leviton.com

Middle East & Africa

T +971.4.247.9800
E lmeinfo@leviton.com

Colombia



T +57.1.743.6045
E infocolombia@leviton.com

South Korea


T +82.2.3273.9963
E infokorea@leviton.com

ELECTRONIC FILES



For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.




41AB6-1F4



69104-IDC



41AB6-3F4



41DR6-1F4

41AB6-xF4, 41DR6-1F4

PART NUMBERS

Description	Part No.
Cat 6 110-Style Wiring Block Kit, includes 96-pair block with legs, labels, and 24 C-4 clips	41AB6-1F4
Cat 6 110-Style Wiring Block Kit, includes 288-pair block with legs, labels, and 72 C-4 clips	41AB6-3F4
Cat 6 110-Style Rack-Mount Wiring Block Kit, includes 96-pair 1RU panel, labels, and 24 C-4 clips	41DR6-1F4
Wall-Mount Horizontal Cord Manager with legs	41A10-HCM
Rack-Mount Horizontal Cord Manager, 1RU	41D1R-HCM
Cat 6 110-Style C-4 Clips (bag of 10)	69104-IDC



<p>Leviton Network Solutions Asia / Pacific 2222 - 222nd St. SE Bothell, WA 98021-4416</p> <p>tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com</p>	<p>T +1.631.812.6228 E infoasean@leviton.com</p>	<p>Canada T +1.514.954.1840 E pcservice@leviton.com</p>	<p>Caribbean T +1.954.593.1896 E infocaribbean@leviton.com</p>	<p>China T +852.2774.9876 E infochina@leviton.com</p>	<p>Colombia T +57.1.743.6045 E infocolombia@leviton.com</p>
<p>Europe T +44.0.1592.772124 E customerserviceeu@leviton.com</p>	<p>India / SAARC T +971.4.886.4722 E infoindia@leviton.com</p>	<p>Mexico T +52.55.5082.1040 E lsamarketing@leviton.com</p>	<p>Middle East & Africa T +971.4.247.9800 E lmeinfo@leviton.com</p>	<p>South Korea T +82.2.3273.9963 E infokorea@leviton.com</p>	