

Banana Jack QuickPort® Couplers

APPLICATION

Banana Jack QuickPort Couplers provide audio connectivity for speaker wire. The couplers snap into any QuickPort housing: flush- and surface-mount outlets, Multimedia Outlet System (with adapter), Decora® Inserts, patch panels, and patch blocks.



SPECIFICATION

Banana Jack Coupler shall be an individual screw terminal to banana jack adapter. The coupler shall fit all other installed telecommunications wallplates, outlets, and field-configurable patch panels, and patch blocks. Couplers shall be available in ivory, white, and light almond to match the housings or wallplates. The coupler shall be UL listed. All plastics used in construction of the module bodies shall be fire retardant.

FEATURES

- Screw Terminal
- Compatible with all QuickPort wallplates, housings, and panels
- Available in a variety of colors to match housings or wallplates
- Compatible with other banana jacks

DESIGN CONSIDERATIONS

- Check clearance behind proposed location of bulkhead module to ensure space for proper bend-radius of cabling media
- Recommended wire size: 18 to 12 AWG

STANDARDS COMPLIANCE

- cULus Listed (UL 1863 , CAN/CSA-C22.2 No. 182.4-1990)

PHYSICAL SPECIFICATIONS

Dimensions: See page two

Materials: Coupler bodies are high-impact, fire-retardant plastic

Banana Jack is gold flash-plated 5-15 µm

COUNTRY OF ORIGIN


China

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



40837-Bxx

PART NUMBERS

Description	WHITE	LT. ALMOND	IVORY
Banana Jack QuickPort® Coupler black stripe	40837-BWE	40837-BTE	40837-BIE
Banana Jack QuickPort Coupler red stripe	40837-BWR	40837-BTR	40837-BIR

Leviton Network Solutions
2222 - 222nd St. SE
Bothell, WA 98021-4416

Asia / Pacific
T +1.631.812.6228
E infoasean@leviton.com

Canada
T +1.514.954.1840
E pcservice@leviton.com

Caribbean
T +1.954.593.1896
E infocaribbean@leviton.com

China
T +852.2774.9876
E infochina@leviton.com

Colombia
T +57.1.743.6045
E infocolombia@leviton.com

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Europe
T +44.0.1592.772124
E customerserviceeu@leviton.com

Mexico
T +52.55.5082.1040
E lsamarketing@leviton.com

Middle East & Africa
T +971.4.247.9800
E lmeinfo@leviton.com

South Korea
T +82.2.3273.9963
E infokorea@leviton.com