

QUICKPORT™ Modular Furniture Faceplates

APPLICATION

Leviton QUICKPORT Modular Furniture Faceplates with ID windows feature a designation window for simple, organized workstation identification. The faceplates accept QUICKPORT snap-in connectors and adapters to support a variety of voice and data applications in office environments.



SPECIFICATION

Modular Furniture Faceplate — Standard

Modular furniture connector housing shall be a field-configurable faceplate providing from one to four flush-mount ports for a variety of snap-in connectors and adapters.

Modular Furniture Faceplate — Herman Miller

Modular furniture connector housing shall be a field-configurable flush-mount faceplate compatible with Herman Miller openings, and provide from one to four flush-mount ports for a variety of snap-in connectors and adapters.

Modular Furniture Faceplate — Extended Depth

Modular furniture connector housing shall be a field configurable faceplate extending 0.75 inch from the furniture raceway to facilitate fiber or copper cable bend-radius compliance, or to compensate for shallow raceway channels, and provide from one to four flush-mount ports for a variety of snap-in connectors and adapters.

All versions shall have a rattle-free fit and a single tool free release latch; be constructed of high-impact self-extinguishing plastic rated UL 94V-0; and be cULus Listed, and compliant with ANSI/TIA 568 specifications.

FEATURES

- Faceplates accept Leviton QUICKPORT snap-in connectors
- · Provides for work area telephone and data patching
- · Compact design
- · Meets ANSI/TIA 568 bend-radius requirements
- · ID label and window kit included

DESIGN CONSIDERATIONS

- Specify 49910-Sxx (standard) or 49910-Hxx (Herman Miller) versions (dependent on furniture type)*
- Specify 49910-Exx (same opening size as 49910-Sxx) for installation into shallow raceway channels (plate has 0.5-inch added depth)
- Specify port identification method (colored connectors, adapters, and designation labels available)
- Configure 1, 2, 3, or 4 active ports; spare ports can be filled with blanks for later use

STANDARDS & REGULATIONS

- cULus Listed (UL 1863 & CAN/CSA-C22.2 No. 182.4)
- ANSI/TIA 568

MECHANICAL SPECIFICATIONS

Dimensions: See page two

Materials: UL 94V-0 Rated Thermoplastic

COUNTRY OF ORIGIN

Mexico


WARRANTY INFORMATION


For Leviton product warranties, go to leviton.com/ns/warranty


^{*} xx = various configurations and colors, see page two.


PRODUCT SPECIFICATIONS 49910-Sxx, 49910-Exx, 49910-Hxx














| PART NUMBERS | | | | | |
|--|-----------|-----------|-----------|-----------|--|
| Description | White | lvory | Gray | Black | |
| QUICKPORT™ Modular Furniture Faceplate, 2 ports | 49910-SW2 | 49910-SI2 | 49910-SG2 | 49910-SE2 | |
| QUICKPORT Modular Furniture Faceplate, 4 ports* | 49910-SW4 | 49910-SI4 | 49910-SG4 | 49910-SE4 | |
| QUICKPORT Modular Furniture Faceplate, 4 port, extended depth* | 49910-EW4 | 49910-EI4 | 49910-EG4 | 49910-EE4 | |
| QUICKPORT Modular Furniture Faceplate, 2 ports, Herman Miller* | 49910-HW2 | 49910-HI2 | 49910-HG2 | 49910-HE2 | |
| QUICKPORT Modular Furniture Faceplate, 4 ports, Herman Miller* | 49910-HW4 | 49910-HI4 | 49910-HG4 | 49910-HE4 | |

Standard and Extended Depth Modular Furniture Faceplates fit openings of approximately 1.38" x 2.68".

4-port extended depth faceplate provides 0.5-inch added depth (0.75 inch total).

Herman Miller faceplates fit openings of approximately 1.88" x 2.98".

Standard and extended depth faceplates are compatible with Herman Miller Furniture when used with Herman Miller G1189A Reducer available from Herman Miller dealers. ID label and window kit included.

*Includes one QUICKPORT blank insert.

For further support information, visit leviton.com/ns/support

Page 2 of 2

Network Solutions Headquarters

+1 (800) 722 2082

infoUSA@leviton.com

Leviton Berk-Tek Cable: +1 (800) 237 5835 berktek.info@leviton.com

Asia Pacific

+852 3620 2602 infoAPAC@leviton.com Canada +1 (800) 461 2002 infoCanada@leviton.com Europe +44 (0) 1592 772124 infoEurope@leviton.com

Latin America MX: +52 (55) 2128 6286 LATAM: +52 (55) 2333 5963 infoLATAM@leviton.com

Middle East & Africa +971 (4) 247 9800 infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.