

Rack-Mounted Rear Cable Management Bar

APPLICATION

The Rack-Mounted Rear Cable Management Bar attaches to all industry-standard 19" racks and cabinets. It is recommended to be used with QUICKPORT™ high-density flat patch panels (sold separately) and is used to support and route cables.



SPECIFICATION

The Rack-Mounted Rear Cable Management Bar shall mount to the rear side of standard 19" equipment rack rails using two included screws. The unit shall provide methods for the neat and efficient routing of cable bundles at the rear of patch panels. The Cable Management Bar shall be capable of supporting rear cable bundles for either standard density or high-density patch panels. The unit may be used with either flat or angled patch panels.

FEATURES

- Includes cable bundle tie down locations
- 48-port density in only 1RU of rack space (high-density panels sold separately: 49255-Q48, 4S255-D48, 4S255-W48, 49256-D48)

DESIGN CONSIDERATIONS

- Mounts on industry-standard 19" equipment rack use hook-and-loop (Velcro® Brand) ties to secure cable bundles to bar
- For high-density panels route cable bundles above and below bar and secure with hook-and-loop ties
- Cable bundles at the rear of angled patch panel should cross over (left to right, right to left)
- Cable Management Bar may be used in many cabinet and four post racks with the addition of a Panel Extension Kit (Part Number: E2X1F-BKT, sold separately)

MECHANICAL SPECIFICATIONS

Dimensions: See page 2
Materials: Steel | Plastic
Temperature (Storage): -40 °C to +70 °C
Temperature (Operating): -10 °C to +60 °C
Humidity (Maximum): 95% relative humidity, non-condensing

COUNTRY OF ORIGIN

Taiwan




WARRANTY INFORMATION

For Leviton product warranties, go to leviton.com/ns/warranty

49006-RMB

PRODUCT SPECIFICATIONS
49006-RMB

49006-RMB



Measurements are in inches and [mm]

PART NUMBERS

Description	Part No.
Rack-Mounted Rear Cable Management Bar	49006-RMB

For further support information, visit leviton.com/ns/support

Page 2 of 2

USA
Network Solutions Headquarters
+1 (800) 722 2082
infoUSA@leviton.com

Leviton Berk-Tek Cable: +1 (800) 237 5835
berktek.info@leviton.com

Asia Pacific
+852 3620 2602
infoAPAC@leviton.com

Canada
+1 (800) 461 2002
infoCanada@leviton.com

Europe
+44 (0) 1592 772124
infoEurope@leviton.com

Latin America
MX: +52 (55) 2128 6286
LATAM: +52 (55) 2333 5963
infoLATAM@leviton.com

Middle East & Africa
+971 (4) 247 9800
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.