

Plug-in Outlet, Zigbee® Certified

decora smart™



works with
xfinity



APPLICATIONS

Leviton's Decora Smart family of Zigbee enabled lighting controls are the perfect addition to any smart home automation system using a Zigbee hub, gateway, or controller. The DG15A Decora Smart 15A Plug-In Outlet is Zigbee 3.0 certified and includes the latest in Zigbee technology for inter-operability and network security. Zigbee uses mesh networking technology to provide quick, reliable, and secure communication to a wide variety of Zigbee certified smart products such as sensors, thermostats, locks, and more.

The DG15A provides On and Off of connected lighting via the manual control button or can be controlled wirelessly as part of a Zigbee network. The DG15A is compatible with a variety of load types such as Incandescent, LED / CFL, and Fluorescent. The DG15A is built for performance with a 15A relay and is also rated for ½ HP motor loads. When paired with a Zigbee compatible hub, gateway, or controller, the DG15A provides remote lighting control of plug-in lamps, holiday lighting, electronics, and small appliances. Typical applications include switching of floor lamps, portable fans, kitchen appliances, indoor fountains, coffee makers, and more. Using the DG15A, you can flexibly include a variety of devices in smart home schedules and other home automation activities.

The DG15A Plug-In Outlet can also be controlled via Voice or App depending on the Zigbee hub it is paired to.

Some common Smart Home hubs supporting Zigbee include the Xfinity Home Touch Screen, Amazon Echo Plus and Echo Show (2nd Gen), and Samsung SmartThings.

The DG15A Plug-In Outlet is ideal for any residential setting where remote On / Off switching of appliances and motor loads up to ½ HP or freestanding lights such as LED/CFL, incandescent, or fluorescent is needed. Leviton's Decora Smart lighting controls are engineered to function with extremely sensitive, low-wattage light sources, such as a single LED bulb or a strand of holiday lights, ensuring LEDs do not glow when off.

FEATURES AND BENEFITS

- Provides 15A, 120 VAC NEMA 5-15R grounding receptacle for use with a wide variety of lamps and appliances
- Protected memory maintains ON/OFF status of loads and during minor power fluctuations
- LED Control Button for visual feedback and manual On/Off control
- Zigbee 3.0 Certified

RATINGS

- LED / CFL - 600W - 120VAC, 60Hz
- Resistive - 1800W - 120VAC, 60Hz
- Incandescent/Halogen - 1800W - 120VAC, 60Hz
- Fluorescent - 1800VA - 120VAC, 60Hz
- Inductive - 1800W - 120VAC, 60Hz
- Motor - 1/2 HP, 9.8A

AGENCY STANDARDS AND COMPLIANCE

- Complies with UL 917
- CSA Certified
- NOM Certified
- Complies with FCC Part 15, Class B
- Zigbee 3.0 Certified

WARRANTY INFORMATION

- Five-Year Limited Warranty

Leviton Manufacturing Co., Inc. Global Headquarters

201 N. Service Rd. Melville, NY 11747-3138 Tech Line: 1-800-824-3005 Fax: 1-800-832-9538

Leviton Manufacturing Co., Inc. Residential


865 Fulton St., Suite 500, New Orleans, LA, 70130. Tel: 504 608-9001

Visit our Website at: www.leviton.com/decorasmart

©2020 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

DRAWING

DG15A



ORDERING INFORMATION

DESCRIPTION	CAT. NO.
Decora Smart Zigbee 3.0: 15A Incandescent / 5A LED/CFL Plug-In Outlet, Packed 1/Box, 10/Carton.	DG15A-1BW

Leviton Manufacturing Co., Inc. Global Headquarters
 201 N. Service Rd. Melville, NY 11747-3138 Tech Line: 1-800-824-3005 Fax: 1-800-832-9538

Leviton Manufacturing Co., Inc. Residential
 865 Fulton St., Suite 500, New Orleans, LA, 70130. Tel: 504 608-9001

Visit our Website at: www.leviton.com/decorasmart
 ©2020 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

SAT-10079
 REV JUN 2020