Features and Benefits

- New design with rocker switch and slender dimmer control slide bar
- Integrated linear full-range slide control for easy, precise operation
- Separate ON/OFF switch that preserves the selected brightness setting
- Provides single pole (one location) or 3-way (two location) lighting control when paired with a 3-way switch
- Comes packaged in White with Ivory and Light Almond color change kits (some exceptions)
- Additional color change kits available in Black, Brown, Red and Gray
- Slim, compact housing fits easily into a standard wallbox
- No fins for multi-gang installation
- Built-in radio/TV interference filter
- Five-Year Limited Product Warranty





Third party trademarks used herein are the property of their respective owners and are used for identification/reference purposes only.

Decora is a registered trademark of Leviton Manufacturing Co., Inc.



Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747-3138 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538 Tech Line (8:30AM-7:00PM E.T. Monday-Friday): 1-800-824-3005

© 2015 Leviton Manufacturing Co., Inc. All rights reserved. G-9381/K14-dp





decora® Rocker Slide Controls

New line of Dimmers and Fan Speed Control brings today's technology home.



Performance Meets Style

Creating the perfect ambiance with seamless dimming brings a new level of style and sophistication to a home. Decora Rocker Slide Dimmers, with smooth. slide-action, full-range dimming, are the perfect choice for dimming incandescent, LEDs, CFLs, halogen, magnetic low voltage, electronic low voltage and fluorescent bulbs. The line also includes a new 1.5 amp Quiet Fan Speed Control.

Decora Rocker Slide Controls feature our hallmark Decora rocker switch that provides preset ON/OFF switching and a smooth, integrated slide bar for fine adjustment of lighting levels. With a new, streamlined style, Decora dimmers and fan speed control complement any interior design and present a sleek, uniform appearance when multi-ganged with other Decora devices.





Cat. Nos. DSL06 DSM10 With Locator Light



Cat. Nos. DS710 DSE06 DSF01 DSX10 DSX12 DSH08-1 DSH06-7 No Locator Light

Decora Rocker Slide Universal Dimmers

Cat. No. DSL06	Cat. No. DSM10
120VAC-60Hz	120VAC-60Hz
300W LED/CFL	450W LED/CFL
600W Incandescent/Halogen	1000W Incandescent/MLV

- Integrated linear full-range slide control for easy, precise operation
- Separate ON/OFF switch that preserves selected brightness setting
- Single pole or 3-way when used with a 3-way switch
- No neutral required
- Locator Light

Mark 7[®] Fluorescent Ballast and **LED Power Supply 0-10V Dimmer**

Cat. No. DS710

- 120VAC-60Hz, 277VAC-60Hz 1200VA@120VAC 1500VA@277VAC 1200VA/1500VA Fluorescent
- Designed for use with LED fixtures using 0-10V power supplies
- Dual voltage 120V/277V; 50ma maximum sink current
- No power pack required for switching

Electronic Low Voltage Dimmer (Trailing Edge)

Cat. No. DSE06

120VAC-60Hz 300W LED/CFL 600VA ELV

- Integrated linear full-range slide control for easy, precise operation Separate ON/OFF switch that preserves selected brightness setting
- Single pole or 3-way when used with a 3-way switch
- Neutral required

Mark 10[®] Fluorescent Powerline Dimmer

Cat. No. DSX10	Cat. No. DSX12
120VAC-60Hz	277VAC-60Hz
1000VA Fluorescent	1200VA Fluorescent

- Integrated linear full-range slide control for easy, precise operation Separate ON/OFF switch that preserves selected brightness setting
- Single pole or 3-way when used with a 3-way switch
- No neutral required

Fluorescent Dimmer for Hi-Lume® or Eco-10® type Ballasts

Cat. No. DSH08-1	Cat. No. DSH06-7
120VAC-60Hz	277VAC-60Hz
8A@120VAC Fluorescent	6A@277VAC Fluorescent

- Integrated linear full-range slide control for easy, precise operation
- Separate ON/OFF switch that preserves selected brightness setting
- Single pole or 3-way when used with a 3-way switch
- Neutral required

1.5A Motor

Quiet Fan Speed Control

Cat. No. DSF01 120VAC-60Hz

- Combines Decora rocker ON/OFF switch with a contemporary slender slide bar for selection of low, medium or high fan speed
- Ideal for libraries, home offices, bedrooms; any area where ceiling fan noise could become distracting
- No neutral required