

# Whole Home Charging Solutions











## A Charger for Every Space

Engineered and tested for compatibility with more of the latest devices, Leviton USB In-Wall Chargers deliver fast, efficient charging to phones, tablets, laptops and more: backed by the quality you expect from the brand you trust.

From kitchens, bedrooms and home offices to bathrooms and more, our in-wall chargers can be conveniently used in any room of the home.

A weather-resistant model is available for use in outdoor locations such as patios and decks. A weatherproof cover is required for this application.









Deliver hours of enjoyment with just minutes of charging. Leviton's Power Delivery-enabled in-wall chargers support even the most demanding phones, tablets and laptops. Power Delivery, a state-ofthe-art charging technology that supplies a higher level of power for faster charging, is built-in to a variety of Leviton in-wall chargers, including the industry's highest power USB in-wall charger, the T5636 - featuring 60W of power on a single port. With built-in overcurrent protection and an internal thermoregulator to help keep valuable electronics safe, Leviton USB In-Wall Chargers are backed by the quality you expect from the leader in electrical safety.



<sup>\*</sup>Available with T5634, T5834, T5635, T5835, T5636 and T5836









## **FUTUREPROOF**

With technology evolving daily, it's important to choose a USB Charger that can keep pace.

- Type-C USB Port Accepts the newest Type-C reversible connector used on the latest smartphones, tablets, laptops and monitors
- Type A USB Port Accepts the standard Type A rectangular connector commonly found in the market today











### **SAFETY**

For over 110 years, Leviton has been at the forefront of developing electrical products with safety in mind, and our USB In-Wall Chargers continue this tradition.

- Our SmartlockPro® GFCI Combination USB offers the trusted safety of Leviton GFCI protection with the advantage of powerful USB charging
- Overcurrent protection on USB ports helps protect electronics from receiving too much power, which can damage devices
- Internal regulator on USB ports prevents electronics from overheating
- Outlets are tamper-resistant to help prevent foreign objects from being inserted



### GUSB1

SmartlockPro® Self-Test GFCI Combination Type A USB In-Wall Charger



#### GUAC1

SmartlockPro® Self-Test GFCI Combination Type A/C USB In-Wall Charger



# Choosing The Charger That's Right For You

The newest smartphones, tablets and laptops have Power Delivery built-in, allowing for faster charging speeds – but you need a Power Delivery compatible charger to take advantage. Leviton's line of PD-enabled chargers are safe, powerful and compatible with more of the newest devices.

### **Applications**

60W Dual Type-C with Power Delivery (PD)	30W Dual Type-C with Power Delivery (PD)	50W Type-C and 10W Type A with Power Delivery (PD)
<b>Cat. Nos.</b> T5636/T5836	<b>Cat. Nos.</b> T5635/T5835	<b>Cat. Nos.</b> T5634/T5834
Higher wattage supports fast charging for larger PD-enabled devices like tablets, laptops and more. Great for home offices.	Powerful charger perfect for PD-enabled phones. Perfect for everyday use.	Supports fast charging for phones, tablets, laptops and more. Great for users who require both fast charging for Type-C devices and standard charging for Type A compatible devices.





### **Product Guide**







	T5636/T5836 60W Dual Type-C with Power Delivery (PD)	T5635/T5835 30W Dual Type-C with Power Delivery (PD)	T5634/T5834 60W Type A and Type-C with Power Delivery (PD)	
USB Charger	6A	6A	4.5A+	
Total Charging Power	60W	30W	60W	
Single Port Charging Power	60W	30W	50W Type-C port 10W Type A port	
Outlet Power	15A, 20A	15A, 20A	15A, 20A	
USB Cable Compatible	3.1, 3.0, 2.0, 1.1	3.1, 3.0, 2.0, 1.1	3.1, 3.0, 2.0, 1.1	
Wiring	Wire leads	Back and side wiring	Wire leads	













<b>T5637/T5837</b> Type-C	T5633/T5833 Type A and Type-C	<b>T5632/T5832</b> Dual Type A	GUAC1/GUAC2 SmartlockPro® Self-Test GFCI Combination Type A/C	GUSB1/GUSB2 SmartlockPro® Self-Test GFCI Combination Type A	W5633/W5833 Weather-Resistant Type A and Type-C
6A	5.1A	3.6A	4.8A	4.8A	5.1A
30W	25+W	18W	24W	24W	25+W
15W	15W	12W	12W	12W	15W+
15A, 20A	15A, 20A	15A, 20A	15A, 20A	15A, 20A	15A, 20A
3.1, 3.0, 2.0, 1.1	3.1, 3.0, 2.0, 1.1	3.1, 3.0, 2.0, 1.1	3.1, 3.0, 2.0, 1.1	3.1, 3.0, 2.0, 1.1	3.1, 3.0, 2.0, 1.1
Back and side wiring	Back and side wiring	Back and side wiring	Wire leads	Wire leads	Wire leads



### Tamper-Resistant (TR) Outlets

All Leviton USB In-Wall Charger Outlets are Tamper-Resistant. Tamper-Resistant Outlets have a built-in shutter mechanism inside the receptacle that blocks access to the contacts from most foreign objects, allowing only a two- or three-prong plug to be inserted. Leviton Tamper-Resistant Outlets comply with the latest NEC® requirements for tamper-resistant receptacles in residences and childcare facilities.

### Colors available:







Light Almond (-T)







Brown (-B)

Black (-E)



Visit our Website at: www.leviton.com/usb

© 2023 Leviton Manufacturing Co., Inc. All rights reserved. All trademarks are the property of their respective owners.

