

# Berk-Tek M12 X-Coded IP67 Kit



Berk-Tek LANmark Industrial Connectors enable the expansion and integration of Ethernet into machines, sensors, PLC/DCS networks and various industrial environments. With over 50 years of cable manufacturing experience, Berk-Tek offers best-in-class Industrial Ethernet solutions that perform reliably in industrial harsh conditions, leading to maximum production uptime and efficiency.

## DESCRIPTION

This field-installable M12 X-Coded connector kit is ideal for more ruggedized industrial connectivity requiring threaded connection, 10 Gb/s Ethernet and IP67 Ingress Protection rating.

This connector is optimized for the following LANmark Industrial cables:  
LANmark-C545, -C637, -A750, -B751 (Cat 6A), -A689 and -B752 (Cat 6)



## STANDARDS

### International

EU Directive 2011/65/EU (RoHS);

EU Directive 2014/35/EU (Low Voltage)

## CHARACTERISTICS

### Construction characteristics

Connector type	M12 X-Coded (Male)
Connector Orientation	Straight
Plug Body	Zinc Alloy
Contacts	Copper Alloy with Gold Plating
Connector Shielding	Zinc Alloy
Termination Type	IDC
Pin Count	8.0
Wire Aligner	Zinc Alloy

### Dimensional characteristics

Cable diameter, range	0.217 .. 0.354 in
Jack Wire Sizes	22.0 .. 27.0 AWG

### Electrical characteristics

Rated Voltage	50 Volts
Rated current	0.5 A
Rated Impulse Voltage	800.0 V


### Mechanical characteristics

Connector Mating Cycles	100.0
-------------------------	-------

### Usage characteristics

IP Rating	IP67 (IEC 60529)
Recommended operating temperature range	-40 .. 85 °C
Application Performance	10 Gb/s Ethernet

## PRODUCT LIST

Part Number	Description
 81000752	LANmark-C545-M12X-PKB: M12, X-Coded, 8-pin IDC termination male IP67 connector

 = Make to order,  = In stock