



Choosing the right Lev-lok® module




RECEPTACLE / GFCI • SINGLE POLE SWITCH • 3-WAY SWITCH • OCCUPANCY SENSOR

RECEPTACLE / GFCI

1 Determine **Solid** or **Stranded?**
(Contractor preference or what is already in infrastructure)



2 “Do you prefer **Push Wire Connections** at the ends of the wire leads?”



- 3** Special Purpose / Application Based:
- 2-Gang Application ➔ MSTWL-WTK
 - Isolated Power Areas (NEC 517.160) ➔ MSTWL-XI
 - Low Leakage Currents ➔ MSTWL-XA or XN
 - Emergency Circuits ➔ MSTWL-R
 - Isolated Ground Circuits ➔ MSTWL-IG

For Receptacles, 20 A, 125 V Max.


Description	Module Color	Wire Type	Wire Colors	Cat. Number
Stranded Wire Leads	White	THHN	Black, White, Green	MSTWL-A
Stranded Wire Leads with Push Wire Connectors (4-Port Connector)	White	THHN	Black, White, Green	MSTWL-WST
Dual Module for 2-Gang Applications with Leads Pre-Installed in Push Wire Connectors **	White	THHN	Black, White, Green	MSTWL-WTK **
Stranded Wire Leads with Push Wire Connectors **	White	THHN	Black, White, Green	MSTWL-WT6 **
Stranded Wire Leads with Push Wire Connectors **	Red	THHN	Black, White, Green	MSTWL-RT6 **
Stranded Wire Leads for Emergency Circuits	Red	THHN	Black, White, Green	MSTWL-R
Stranded Wire Leads for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-IG
Stranded Wire Leads with Push Wire Connectors for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-WIG
Solid Wire Leads	White	THHN	Black, White, Green	MSTWL-SDA
Solid Wire Leads for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-SIG
Solid Wire Leads with Push Wire Connectors (4-Port Connector)	White	THHN	Black, White, Green	MSTWL-WSD
Solid Wire Leads with Push Wire Connectors **	White	THHN	Black, White, Green	MSTWL-WD6 **
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Orange, Brown, Green/Yellow [†]	MSTWL-XA [*]
Stranded Wire Leads for Low Leakage Circuits (For use in isolated power areas to comply with NEC 517.160)	White	XHHW-2	Brown/Yellow, Orange/Blue, Green/Yellow [†]	MSTWL-XI [*]
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Black, White, Green/Yellow	MSTWL-XN [*]

* Add suffix of 0 for 6”, 1 for 12”, 2 for 24” or 3 for 36” long leads. Please allow 4 to 6 weeks for delivery.

** 6-port connector only on ground lead. 4-port connector on the hot & neutral leads. Special order only configurations.

[†] Wire order is hot, neutral, ground.


SINGLE POLE SWITCH



1 Determine **Solid** or **Stranded**?
(Contractor preference or what is already in infrastructure)

- **IF YOU HEAR:**
"I prefer to pigtail with a wire nut"
Recommend **Stranded**


2 "Do you prefer **Push Wire Connections** at the ends of the wire leads?"

See options in chart with 

3 Remainder of qualifying questions are preference/application based:

Black, Black, Green OR
Brown, Brown, Green?

For Single Pole Switches, 20 A, 347 V Max.

Description	Module Color	Wire Type	Wire Colors	Cat. Number
Stranded Wire Leads	Yellow	THHN	Black, Black, Green	MSPSW-ST
Stranded Wire Leads with Push Wire Connectors 	Yellow	THHN	Black, Black, Green	MSPSW-WST
Solid Wire Leads	Yellow	THHN	Black, Black, Green	MSPSW-SD
Stranded Wire Leads	Yellow	THHN	Brown, Brown, Green	MSPSW-7ST
Solid Wire Leads	Yellow	THHN	Brown, Brown, Green	MSPSW-7SD

3-WAY SWITCH

1 Determine **Solid** or **Stranded**?
(Contractor preference or what is already in infrastructure)


Solid: M3WSW-SD (Only 1 option)

Stranded: Prefer **Push Wire Connections**? ➔ M3WSW-WST (Only 1 option)

Have specific 277V Lighting Application? ➔ M3WSW-7ST

Anything else? ➔ M3WSW-ST

For 3-Way Switches, 20 A, 347 V Max.

Description	Module Color	Wire Type	Wire Colors	Cat. Number
Stranded Wire Leads	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-ST
Stranded Wire Leads with Push Wire Connectors 	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-WST
Stranded Wire Leads for 277V Lighting Applications	Yellow	XHHW-2	Brown, Yellow, Yellow, Green	M3WSW-7ST
Solid Wire Leads	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-SD

OCCUPANCY SENSOR

1 Determine **Solid** or **Stranded**?
(Contractor preference or what is already in infrastructure)

For Occupancy Sensors, 20 A, 347 V Max.

Description	Module Color	Wire Type	Wire Colors	Cat. Number
Stranded Wire Leads	Yellow	THHN	Black, Blue, Green	MSPSW-XST
Solid Wire Leads	Yellow	THHN	Black, Blue, Green	MSPSW-XSD

Visit our Website at:
www.leviton.com/levlok
email: commercial@leviton.com

Q-1512

120123

Leviton Manufacturing Co., Inc.
201 N Service Rd, Melville, NY 11747
Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2024 Leviton Manufacturing Co., Inc. All rights reserved.