

VOICE Patch Panel

Datasheet: GD035404v8




APPLICATION

Leviton 19" rack-mounted Unscreened RJ45 ISDN/Telephone Patch Panels are available in 1U 25 and 50 port versions to ensure maximum utilization of cabinet space. In addition to this, all panels are supplied with a central and side cable anchor features and dual earthing points. All outlets are numerically identified. Each panel is supplied with a wiring label, cable ties, and panel mounting accessories, pair manager, earth lead and short form installation instruction.

FEATURES


- 25 and 50 port versions available
- 4 and 6 pin versions available
- Rugged construction
- 19" rack compatible
- Durable powder coat finished in black or gray



ORDER INFO

Part Number	Item Description	Color	Weight per Item (nom)	Qty per Pack
C5CPNLU254PK8M	25 way 1U UTP Telephone Panel 4 Pin (36,45)	Gray	1091g	1
C5CPNLU504PK8M	50 way 1U UTP Telephone Panel 4 Pin (36,45)	Gray	1160g	1
C5CPNLU254PK2M	25 way 1U UTP Telephone Panel 4 Pin (36,45)	Black	1091g	1
C5CPNLU504PK2M	50 way 1U UTP Telephone Panel 4 Pin (36,45)	Black	1160g	1
C5CPNLU256PK2M	25 way 1U UTP Telephone Panel 6 Pin (12,36,45)	Black	1091g	1
C5CPNLU506PK2M	50 way 1U UTP Telephone Panel 6 Pin (12,36,45)	Black	1280g	1

PHYSICAL CHARACTERISTICS



MATERIALS

- Chassis – Mild Steel

INSTALLATION

- Outlet: 8pin RJ45 Unkeyed
- IDC: LSA Style Insulation Displacement Connectors (IDC) suitable for both solid & stranded wire 26AWG (0.4mm \varnothing)– 22 AWG (0.64mm \varnothing)

STANDARDS

- Applicable Standards:
 - TIA/EIA 568C.2
 - EN 50173-1
 - ISO/IEC 11801

CONFORMANCE

- 4pin - TIA/EIA 568C.2 CAT3 (2 pair)
- 6pin - TIA/EIA 568C.2 CAT3 (3 pair)

ACCESSORY KIT

- 1x Installation instruction
- 1x 2m 1.5mm² flexible earth Lead,
- 4 x M6 Caged Nuts
- 4 x M6 x 20mm PH slotted screws
- 4 X M6 Black Cup washers

“Leviton is dedicated to designing, developing, and manufacturing sustainable high performance structured cabling and specialty cabling solutions.”

The information contained in this document is valid and correct at the time of issue. Leviton reserves the right to modify details without notice in light of subsequent standard/specification changes and ongoing technical developments.