



lev-lok® Modular Wiring Device System SELECTION GUIDE

The safer and more efficient solution for modern building electrical systems.











Install Wiring Module

All modules have a Circuit ID Label for ease of identification



Connect Wiring Device

Simply push and twist to lock connection




Finish Installation

Install device into box and finish with wallplate

The Challenge

The rapid change in technology has made it difficult for architects, engineers, and contractors to design and build structures that meet both current and future requirements, especially when it comes to the building's electrical distribution system. The pressure to compress timelines on these types of construction projects has become even greater.



The Solution

The Lev-Lok® modular wiring device system addresses the above challenges. The installation and commissioning of Lev-Lok wiring devices is significantly faster and easier than conventional wiring devices. This not only allows electrical construction projects to be completed faster, but also significantly lowers the risk of incorrect installation that results in costly rework and extended timelines.

But the benefits don't stop there. The Lev-Lok modular wiring device system makes it just as fast and easy to upgrade or replace wiring devices to meet future needs, whether it is related to reconfiguration for changing requirements, or updating to new technology as it becomes available.

A COMPLETE PORTFOLIO



Receptacles

Standard Duplex and Decora Plus™, GFCI, USB & Surge Protective



Switches

Toggle and Decora Plus™



Sensors

PIR





- Available in standard, tamper-resistant, power indication, illuminated, and isolated ground versions of both our conventional and Decora Plus™ duplex platforms
- Wiring modules available in several colors for easy circuit identification: white (normal power), red (for emergency circuits) and orange (for isolated ground circuits)
- Constructed with impact-resistant thermoplastic nylon and one-piece wraparound straps assuring maximum durability
- No exposed live parts makes changeout safer and quicker



Specification Grade Receptacles

- Available in standard, tamper-resistant, and isolated ground versions of both our conventional and Decora Plus™ duplex platforms
- Constructed with impact-resistant thermoplastic nylon and one-piece wraparound straps assuring maximum durability
- Grounding clip permanently secured to strap makes for most reliable ground connection
- Permanently marked "controlled" devices enable compliance with energy standards for buildings such as ASHRAE 90.1 and California's Title 24

CONTROLLED RECEPTACLES



Marked "Controlled" Receptacles for use with plug load control systems

4 leviton.com/levlok



Extra Heavy-Duty SmartLockPRO® GFCI Receptacles

- Patented lockout feature prevents
 RESET if the GFCI is miswired or the circuit is no longer functioning properly
- Industry exclusive wraparound strap provides greater support for receptacles, especially in physically harsh environments
- Advanced engineering polymer face provides superior chemical and impact resistance
- The only GFCI modular wiring device on the market with feed-through terminals for protecting downstream receptacles



Commercial Specification Grade and Hospital Grade USB Receptacles

- Type A/A USB Ports have a combined total of 3.6A of charging power
- Type A/C USB Ports have a combined total of 5.1 A charging power, providing faster charging and aligning with emerging standards for most mobile devices
- USB ports optimally spaced for simultaneous use, easy maneuvering and reduced USB cable stress
- Impact and chemical resistant PBT face ensures a long service life, even in punishing public spaces

INDUSTRY EXCLUSIVE

Our Lev-Lok® GFCI's feature feed-through terminals for downstream protection





Heavy-Duty Surge Protective Receptacles

- Provides for point-of-use protection of computers and other office equipment
- Indicator light provides visual indication that equipment is being protected
- Available audible alarm for hidden locations (can be silenced)
- Wide variety of color options aid in identifying different types of equipment or applications
- Tamper-resistant shutters provide an extra level of safety against electrical injury as specified by the National Electrical Code



Extra Heavy-Duty **Switches**

- Available in toggle and Decora Plus[™] platforms, in either single pole or 3-way options
- Illuminated and tamper-resistant toggle versions also available
- Heavy gauge galvanized steel mounting strap provides extra durability for use in physically abusive environments
- Toggle switches available with antimicrobial treated touch surfaces to reduce the growth of harmful bacteria on the device

AN EXTRA LAYER OF PROTECTION



MDS10-IDT







- Provide automatic lighting control for energy saving and convenience in a variety of commercial applications
- Fits in standard wallbox and replaces single pole wall switch - gangable with other units
- Available in Passive Infrared (PIR)
- Low-profile design eliminates obtrusive "scanning-device" look
- Uses Decora® and Decora Plus™ wallplates and coordinates with Leviton's popular line of Decora® wiring devices







Wiring Modules

- Wiring modules are keyed to prevent miswiring
- Available with stranded or solid wire leads
- Receptacle wiring modules available in several colors for easy "specialty" circuit identification
- Switch/sensor wiring modules have color coded leads for ease of installation
- All wiring modules have circuit ID lables for convenient marking

TESTING SIMPLIFIED

Lev-Lok® Circuit Analyzer

The Lev-Lok® Circuit Analyzer helps in testing the circuit prior to installing Lev-Lok Receptacles. Simply connect the receptacle wiring module to the circuit analyzer and you will be able to confirm that wiring is correct, or identify a wiring problem.

- Easy to read indicator lights reveal 5 common wiring issues:
 Open hot, Open ground, Open neutral, Hot/ground reverse, Hot/neutral reverse
- Compact ergonomic design includes comfort grip and built-in keyhole for lanyard attachment
- cCSAus Listed



Lev-Lok® Hospital Grade Receptacles

FED SPEC RATED

Style	Description	Rating	Default Cat. Number	Color Options	
	5.1.1.5.1	15 A	M8200	default (Brown),	
	Extra Heavy-Duty	20 A	M8300	-I, -W, -E, -B, -GY, -R, -T	
Conventional	Established Data Tananan Davistant	15 A	M8200-SG	default (Brown),	
	Extra Heavy-Duty, Tamper-Resistant	20 A	M8300-SG	I, W, E, B, G, R, T	
	Estro Hoose Duty MDI	15 A	MRI15	L W CV D T	
	Extra Heavy-Duty, MRI	20 A	MRI20	-I, -W, -GY, -R, -T	
	Howay Duty	15 A	M8200-H	default (Brown),	
	Heavy-Duty	20 A	M8300-H	I, W, E, B, GY, R, T	
	Llagury Duty Tampar Desistant	15 A	MT820	default (Brown),	
Conventional	Heavy-Duty, Tamper-Resistant	20 A	MT830	-I, -W, -E, -B, -GY, -R, -T	
Conventional	Extra Heavy-Duty, Illuminated	15 A	M8200-IL	LWCDT	
	Extra neavy-buty, illuminated	20 A	M8300-IL	I, W, G, R, T	
	Extra Heavy-Duty, Illuminated,	15 A	MT820-IL	I, W, G, R, T	
	Tamper-Resistant	20 A	MT830-IL	1, 1, 1, 1	
	Extra Heavy-Duty, Power Indication	15 A	M8200-PL	I, W, G, R, T	
	Extra neavy-buty, Power Indication	20 A	M8300-PL	1, VV, G, K, 1	
	Heavy-Duty, Isolated Ground	15 A	M8200-IG	default (Orange),	
	Heavy-Duty, Isolated Ground	20 A	M8300-IG	I, W, E, G, R, T	
	Heavy-Duty, Isolated Ground,	15 A	MT820-IG	default (Orange),	
	Tamper-Resistant	20 A	MT830-IG	I, W, E, G, R, T	
	Extra Heavy-Duty	15 A	M1626-HG	0 (Brown),	
	Lxtra rieavy-buty	20 A	M1636-HG	I, W, E, B, G, R, T	
	Extra Heavy-Duty, Tamper-Resistant	15 A	MT162-HG	I, W, G, R	
	Extra rieavy-buty, ramper-kesistant	20 A	MT163-HG	I, W, G, R, T	
	Extra Heavy-Duty, Illuminated	15 A	M1626-IL	I, W, G, R, T	
	Extra rieavy-Duty, illurriiriateu	20 A	M1636-IL	1, vv, G, K, 1	
Decora	Extra Heavy-Duty, Illuminated,	15 A	MT162-IL	I, W, G, R, T	
Plus™	Tamper-Resistant	20 A	MT163-IL	1, vv, G, K, 1	
	Extra Heavy-Duty, Power Indication	15 A	M1626-PL	I, W, G, R, T	
	Latia Heavy-Duty, Fower Indication	20 A	M1636-PL	i, vv, G, K, i	
	Heavy-Duty, Isolated Ground	15 A	MD820-IG	default (Orange),	
	Ticavy baty, isolated Ground	20 A	MD830-IG	I, W, E, G, R, T	
	Heavy-Duty, Isolated Ground,	15 A	MDT82-IG	default (Brown),	
	Tamper-Resistant	20 A	MDT83-IG	I, W, E, G, R, T	








Mating Wallplates

Leviton's wallplate selection includes multiple configurations, available in standard, midway and oversize dimensions. Materials include nylon, plastic, and metal (stainless steel, brass, and aluminum).





Must use with MSTWL series wiring modules (sold separately) - see back cover for details

COLOR LEGEND

Brown	lvory	White	Black	Blue	Gray	Red	Lt. Almond	Green
base cat no	l	W	Е	B or U or BU	GY or G	R	T	N or GN

Base color is Brown, for other colors add the appropriate color indicator to the base catalog number - Ex: M1626-HGW



Lev-Lok® Industrial Specification Grade Receptacles FED SPEC RATED

Style	Description	Rating	Default Cat. Number	Color Options	
	Extra Heavy-Duty	15 A	M5262	default (Brown),	
	LXII a Fleavy-Duty	20 A	M5362	-l, -W, -E, -B, -GY, -R, -T	
	Extra Heavy-Duty, Tamper-Resistant	15 A	M5262-SG	default (Brown),	
	Extra rieavy-buty, famper-kesistant	20 A	M5362-SG	I, W, E, B, G, R, T	
	Heavy-Duty	15 A	M5262-S	default (Brown), I, W, B,	
	ricavy bacy	20 A	M5362-S	GY (place before S), R, T	
	Heavy-Duty, Tamper-Resistant	15 A	MT562-S	default (Brown),	
	ricavy bacy, ramper resistant	20 A	MT563-S	I, W, E, B, GY, R, T	
	Heavy-Duty, Split-Circuit	15 A	M5262-SC	default (Brown),	
	ricavy bacy, Spile Circuit	20 A	M5362-SC	I, W, E, B, G, R, T	
	Heavy-Duty, Split-Circuit,	15 A	MT562-SC	default (Brown),	
Conventional	Tamper-Resistant	20 A	MT563-SC	I, W, E, B, G, R, T	
	Heavy-Duty, Isolated Ground	15 A	M5262-IG	default (Orange),	
	rieavy-buty, isolated Ground	20 A	M5362-IG	I, W, E, G, R, T	
	Heavy-Duty, Isolated Ground,	15 A	MT562-IG	default (Orange),	
	Tamper-Resistant	20 A	MT563-IG	I, W, E, G, R, T	
	Heavy-Duty, Split-Circuit, Permanently	15 A	M5262-1C	default (Brown),	
	Marked Controlled, 1 receptacle	20 A	M5362-1C	I, W, E, B, G, R, T	
	Heavy-Duty, Split-Circuit, Permanently	15 A	MT562-1C	default (Brown),	
	Marked Controlled, 1 receptacle, Tamper-Resistant	20 A	MT563-1C	I, W, E, B, G, R, T	
	Heavy-Duty, Permanently Marked	15 A	M5262-2S*	default (Brown),	
	Controlled, 2 receptacles	20 A	M5362-2S*	I, W, E, U, G, R, T, N	
	Heavy-Duty, Permanently Marked	15 A	MT562-2S*	default (Brown),	
	Controlled, 2 receptacles, Tamper-Resistant	20 A	MT563-2S*	I, W, E, U, G, R, T, N	
	Heavy-Duty	15 A	M1626	default (Brown),	
	Tieavy-Duty	20 A	M1636	-l, -W, -E, -B, -GY, -R, -T	
	Heavy-Duty, Tamper-Resistant	15 A	MT162	default (Brown),	
	Tleavy-buty, famper-kesistant	20 A	MT163	-l, -W, -E, -B, -GY, -R, -T	
	Heavy-Duty, Split-Circuit	15 A	M1626-SC	default (Brown),	
	Tieavy-buty, Spiit-Circuit	20 A	M1636-SC	I, W, E, B, G, R, T	
	Heavy-Duty, Split-Circuit,	15 A	MT162-SC	default (Brown),	
	Tamper-Resistant	20 A	MT163-SC	I, W, E, B, G, R, T	
	Heavy-Duty, Isolated Ground	15 A	M1626-IG	default (Orange),	
Decora	rieavy-buty, isolated Glourid	20 A	M1636-IG	I, W, E, G, R, T	
Plus™	Heavy-Duty, Isolated Ground,	15 A	MT162-IG	default (Orange),	
	Tamper-Resistant	20 A	MT163-IG	I, W, E, G, R, T	
	Heavy-Duty, Split-Circuit, Permanently	15 A	M1626-1C	default (Brown),	
	Marked Controlled, 1 receptacle	20 A	M1636-1C	I, W, E, B, G, R, T	
	Heavy-Duty, Split-Circuit, Permanently	15 A	MT162-1C	default (Brown),	
	Marked Controlled, 1 receptacle, Tamper- Resistant	20 A	MT163-1C	I, W, E, B, G, R, T	
	Heavy-Duty, Permanently Marked	15 A	M1626-2S*	default (Brown),	
	Controlled, 2 receptacles	20 A	M1636-2S*	I, W, E, U, G, R, T, N	
	Heavy-Duty, Permanently Marked	15 A	MT162-2*	default (Brown),	
	Controlled, 2 receptacles, Tamper-Resistant	20 A	MT163-2*	I, W, E, BU, GY, R, T, GN	









9

Must use with MSTWL series wiring modules (sold separately) - see back cover for details

COLOR LEGEND

001011 110111								
Brown	lvory	White	Black	Blue	Gray	Red	Lt. Almond	Green
base cat no	1	W	Е	B or U or BU	GY or G	R	Т	N or GN

Base color is Brown, for other colors add the appropriate color indicator to the base catalog number - Ex: MT563-2SW

^{*} Not Fed Spec Rated

Lev-Lok® SmartLockPRO® GFCI Receptacles

FED SPEC RATED

Grade	Description	Rating	Default Cat. Number	Color Options	
	Extra Heavy-Duty, Self-Test,	15 A	MGFN1	default (Brown),	
Specification Grade	Feed-Through Terminals	20 A	MGFN2	-l, -W, -E, -GY, -R, -T	
	Extra Heavy-Duty, Tamper-Resistant,	15 A	MGFT1	default (Brown), -I, -W, -E, -GY, -R, -T default (Brown), I, W, E, G, R, T default (Brown), I, W, E, G, R, T	
	Self-Test, Feed-Through Terminals	20 A	MGFT2		
	Extra Heavy-Duty, Self-Test,	15 A	MGFN1-HG		
Hospital	Feed-Through Terminals	20 A	MGFN2-HG		
Grade	Extra Heavy-Duty, Tamper-Resistant,	15 A	MGFT1-HG		
	Self-Test, Feed-Through Terminals	20 A	MGFT2-HG		



Lev-Lok® Receptacles with USB Ports

Grade	Description	Rating	Default Cat. Number	Color Options	
Specification	Heavy-Duty, Tamper-Resistant,	15 A	M56AA	default (Brown), -I,	
	Two Type A USB Ports	20 A	M58AA	-W, -E, -B*, -GY, -R*, -T, -N*, -O*	
Grade	Heavy-Duty, Tamper-Resistant,	15 A	M56AC	default (Brown), -I, -W, -E, -B*, -GY, -R*, -T, -N*, -O* default (Brown), I, W, E, G, R, T default (Brown), I, W, E, G, R, T	
	One Type A and One Type C USB Port	20 A	M58AC		
	Heavy-Duty, Tamper-Resistant,	15 A	M56AA-HG		
Hospital	Two Type A USB Ports	20 A	M58AA-HG		
Grade	Heavy-Duty, Tamper-Resistant,	15 A	M56AC-HG		
	One Type A and One Type C USB Port	20 A	M58AC-HG		



Lev-Lok® Surge Protective Receptacles

Grade	Description	Rating	Default Cat. Number	Color Options
	Hoovy Duty Tomor Posistant	15 A	MT528	default (Brown), -I, -W, -E, -B, -GY, -T
Specification Grade	Heavy-Duty, Tamper-Resistant	20 A	MT538	default (Brown), -I, -W, -E, -B, -GY
	Heavy-Duty, Tamper-Resistant, Audible Alarm Heavy-Duty, Tamper-Resistant,	15 A	MT728	-l, -W, -E, -B, -T
		20 A	MT738	-l, -W, -E, -B
Hospital Grade		15 A	MT828	-l, -W, -B, -R, -T
	Audible Alarm	20 A	MT838	-I, -W, -B, -GY, -R



Must use with MSTWL series wiring modules (sold separately) - see back cover for details

COLOR LEGEND

Brown	lvory	White	Black	Blue	Gray	Red	Lt. Almond	Green	Orange
base cat no	I	W	E	B or U or BU	GY or G	R	Т	N or GN	0

Base color is Brown, for other colors add the appropriate color indicator to the base catalog number - Ex: MGFN1-W

^{*} Special order items (minimum order quantities apply)



Lev-Lok® Industrial Specification Grade Switches and Sensors TOGGLES ARE FED SPEC RATED

Style	Description	Rating	Default	Color Options	
Style	Description	Rucing	Cat. Number	Cotor Options	
	Extra Heavy-Duty, Single Pole	15 A	M1201	default (Brown), -I, -W, -GY, -R	
	Extra neavy-buty, Single Pole	20 A	M1221	default (Brown), -I, -W, -E, -GY, -R, -T	
	Extra Llague Duty Cingle Dale Illuminated	15 A	M1201-LH	C (Clear), I, W	
	Extra Heavy-Duty, Single Pole, Illuminated	20 A	M1221-LH	C (Clear), I, W, R	
	Extra Haavy Duty Single Pole	15 A	M1201-L	default (Brown), I*	
	Extra Heavy-Duty, Single Pole, Tamper-Resistant	20 A	M1221-L	default (Brown), I*, W*, G*, R*	
Togglo	Extra Heavy-Duty, Single Pole, Antimicrobial Treated	20 A	AM120	-I, -W, -GY, -R	
Toggle	Estra Usana Data 2 anns	15 A	M1203	default (Brown), -I, -W, -GY, -R	
	Extra Heavy-Duty, 3-way	20 A	M1223	default (Brown), -I, -W, -E, -GY, -R, -T	
	Extra Haavy Duty 2 way Illuminated	15 A	M1203-LH	C (Class) I W	
	Extra Heavy-Duty, 3-way, Illuminated	20 A	M1223-LH	C (Clear), I, W	
	Extra Heavy-Duty, 3-way,	15 A	M1203-L	default (Brown), I*	
	Tamper-Resistant	20 A	M1223-L	default (Brown), I*, W*, G*, R*	
	Extra Heavy-Duty, 3-way, Antimicrobial Treated	20 A	AM320	-I, -W, -GY, -R	
		15 A	M5691	-I, -W, -GY, -T	
	Extra Heavy-Duty, Single Pole	20 A	M5621	default (Brown), -I, -W, -GY, -T, -R	
Decora	Extra Heavy-Duty, Single Pole, Illuminated	20 A	M5631	-I, -W, -T	
Plus™		15 A	M5693	-l, -W, -GY, -T	
	Extra Heavy-Duty, 3-way	20 A	M5623	default (Brown), -I, -W, -GY, -R, -T	
	Extra Heavy-Duty, 3-way, Illuminated	20 A	M5633	-l, -W, -T	







^{*} Indicator placed before "L"

Style	Description	Amp.	Default Cat. Number	Color Options
Occupancy Sensors	Passive Infrared (PIR)	Load - Incandescent/ Tungsten: 800 W @ 120 V Fluorescent: 1200 VA @ 120 V-2700 VA @ 277 V	MDS10-ID	I, W, E, G, T



11

Must use with MSPSW (single pole), M3WSW (three-way), or MSPSW-X (sensor) series wiring modules (sold separately) - see back cover for details

COLOR LEGEND

Brown	lvory	White	Black	Blue	Gray	Red	Lt. Almond	Green
base cat no	1	W	E	B or U or BU	GY or G	R	Т	N or GN

Base color is Brown, for other colors add the appropriate color indicator to the base catalog number - Ex: M1221-W

leviton.com/levlok

Lev-Lok® Modules

For Receptacles, 20 A, 125 V Max.







Description	Module Color	Wire Type	Wire Colors	Cat. Number
Stranded Wire Leads	White	THHN	Black, White, Green	MSTWL-A
Stranded Wire Leads with Push Wire Connectors (4-Port Connector)	White	THHN	Black, White, Green	MSTWL-WST
Stranded Wire Leads with Push Wire Connectors	White	THHN	Black, White, Green	MSTWL-WT6**
Stranded Wire Leads with Push Wire Connectors	Red	THHN	Black, White, Green	MSTWL-RT6**
Stranded Wire Leads for Emergency Circuits	Red	THHN	Black, White, Green	MSTWL-R
Stranded Wire Leads for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-IG
Stranded Wire Leads with Push Wire Connectors for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-WIG
Solid Wire Leads	White	THHN	Black, White, Green	MSTWL-SDA
Solid Wire Leads for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-SIG
Solid Wire Leads with Push Wire Connectors (4-Port Connector)	White	THHN	Black, White, Green	MSTWL-WSD
Solid Wire Leads with Push Wire Connectors	White	THHN	Black, White, Green	MSTWL-WD6**
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Orange, Brown, Green/Yellow‡	MSTWL-XA*
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Brown/Yellow, Orange/Blue, Green/Yellow [‡]	MSTWL-XI*
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Black, White, Green/Yellow	MSTWL-XN*

- * Add suffix of 0 for 6", 1 for 12", 2 for 24" or 3 for 36" long leads. Please allow 4 to 6 weeks for delivery.
- ** 6-port connector only on ground lead. 4-port connector on the hot & neutral leads. Special order only configurations.
- * Wire order is hot, neutral, ground.



For Single Pole Switches, 20 A, 347 V Max.

Stranded Wire Leads	Yellow	THHN	Black, Black, Green	MSPSW-ST
Stranded Wire Leads with Push Wire Connectors	Yellow	THHN	Black, Black, Green	MSPSW-WST
Solid Wire Leads	Yellow	THHN	Black, Black, Green	MSPSW-SD
Stranded Wire Leads	Yellow	THHN	Brown, Brown, Green	MSPSW-7ST
Solid Wire Leads	Yellow	THHN	Brown, Brown, Green	MSPSW-7SD



For 3-Way Switches, 20 A, 347 V Max.

Stranded Wire Leads	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-ST
Stranded Wire Leads with Push Wire Connectors	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-WST
Stranded Wire Leads for 277V Lighting Applications	Yellow	XHHW-2	Brown, Yellow, Yellow, Green	M3WSW-7ST
Solid Wire Leads	Yellow	XHHW-2	Black, Red, Red, Green	M3WSW-SD



For Occupancy Sensors, 20 A, 347 V Max.

Stranded Wire Leads	Yellow	THHN	Black, Blue, Green	MSPSW-XST
Solid Wire Leads	Yellow	THHN	Black, Blue, Green	MSPSW-XSD

Visit our Website at:

www.leviton.com/levlok

email: commercial@leviton.com

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)



