

## VERTIGO™ Zero-U Patch Panels

### APPLICATION

VERTIGO Zero U patch panels support 12 QUICKPORT™ copper or fiber connectors, enabling a wide range of copper and fiber connectivity in a single unit. Flexible mounting options allow the VERTIGO panel to be installed in a variety of cabinet, rack, underfloor and overhead applications.



### SPECIFICATION

Patch panels shall consume no horizontal rack space and offer both copper and fiber compatibility. Cable management shall route cables vertically and to the sides of the cabinet or rack, providing improved air circulation and enhanced visibility to equipment ports. Panels shall offer data ports at each rack position, allowing the use of shorter patch cords. Panels shall feature a hinged door for easy access to rear of panel for installation and maintenance.

### FEATURES & BENEFITS

- Patented innovative design for multiple applications
- Consumes no horizontal rack space
- Compatible with QUICKPORT copper and fiber connectors for maximum versatility (sold separately)
- Magnifying lens label holder for easy port label reading
- Can share mounting hardware with existing equipment (servers) if necessary
- Protective grommets guard against damage to cables
- Hinged door allows easy access to rear of panel for installation, moves, adds, and changes. Terminated connectors are hidden and protected when door is closed
- Can mount on back rail of cabinet, on a ladder tray, on the wall, or under the floor for maximum versatility
- QUICKPORT copper and fiber connectors are sold separately

### DESIGN CONSIDERATIONS

- Uses no horizontal rack space
- Mounts on back rail of cabinet on the right or left side
- Supports both fiber and copper connectors
- Routes cables vertically

### STANDARDS & REGULATIONS

- ANSI/TIA-568
- c(UL)us Listed

### MECHANICAL SPECIFICATIONS

Dimensions:	See page two
Materials:	12-gauge steel
Capacity:	12 ports
Maximum Capacity:	12 Copper, or 24 Fibers (when using LC)
Temp. (Storage):	-40 °C to +65 °C (-40 °F to +149 °F)
Temp. (Installation):	Refer to cable installation temperature
Temp. (Operating):	-10 °C to +60 °C (+14 °F to +140 °F)
Humidity (Max.):	95% relative humidity, non-condensing

### COUNTRY OF ORIGIN

China




### WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/NS/Warranty](https://www.leviton.com/NS/Warranty)

49280-QP0

**PRODUCT SPECIFICATIONS**  
**49280-QP0**

**49280-QP0**



**PART NUMBERS**

Description	Part No.
VERTIGO™ Zero-U Patch Panel, QUICKPORT™, 12-port	49280-QP0

For further support information, visit [Leviton.com/NS/Support](http://Leviton.com/NS/Support)