

THE FUTURE IS ON[®]

LEVITON[®]



LEV Series Pin & Sleeve Devices

IEC 60309-1 & IEC 60309-2


30 & 60 Amp
Mechanical Interlocks

Designed to be more durable and easier to assemble for the most efficient installation and superior performance in any environment.

Strongest handle and interlock design validated through above & beyond endurance testing for improved safety

Longer length, overmold handle provides an improved grip and features 3 lockout/tagout provisions for OSHA Compliance

Embossed ON/OFF markings




Constructed of impact-resistant, UV stable PBT
Tested to endure impact at the most extreme temperatures

Mounting feet standoff 1/4" from surface - Meets NEC[®] 300.6 air space requirement & NSF Certified

Bottom hinged cover on mechanical interlocks designed with installer in mind

Captive screws for an easier installation

Mounting feet attachment does not require drilling into the enclosure and can be adjusted for several angles



LEV Series: North American Configurations

30 A and 60 A Mechanical Interlocks | **Industrial**

INDUSTRY
BEST

5
YEAR

WARRANTY



LEV SERIES

Product Features

- Impact, UV and chemical-resistant PBT enclosure
- Pre-wired IEC receptacle accepts all manufacturer's IEC 60309-1 & 60309-2 plugs
- Fused models accept "Class J" time-delay fuses
- Watertight and dust-tight rated to IP66, IP67, IP68 and IP69K
- NSF certified sanitary design trusted for use in food & beverage facilities
- Meets North American IEC 60309-1 and 60309-2 standards
- Listed to UL 231 and 1686, CSA and NOM-ANCE requirements, CE Marked
- Backed by an industry best 5-year warranty

30 A and 60 A Mechanical Interlocks								
Amps	Wiring	Color	Voltage AC	Clock Position	Fused Mechanical Interlock	Fused Mechanical Interlock HP Rating	Non-Fused Mechanical Interlock	Non-Fused Mechanical Interlock HP Rating
30	2p3w	Blue	240	6	—	—	330MI6WLEV	5 HP
		Red	480	7	—	—	330MI7WLEV	10 HP
	3p4w	Orange	125/250	12	430MF12WLEV	2 HP @ 120 VAC 3 HP @ 208-240 VAC L-L	430MI12WLEV	2 HP @ 120 VAC 3 HP @ 208-240 VAC L-L
		Blue	3Ø240	9	430MF9WLEV	7.5 HP	430MI9WLEV*	10 HP
		Red	3Ø480	7	430MF7WLEV	15 HP	430MI7WLEV	20 HP
		Black	3Ø600	5	430MF5WLEV	20 HP	430MI5WLEV	25 HP
	4p5w	Blue	3ØY120/208	9	—	—	530MI9WLEV	10 HP
		Red	3ØY277/480	7	530MF7WLEV	15 HP	530MI7WLEV	20 HP
		Black	3ØY347/600	5	530MF5WLEV	20 HP	530MI5WLEV	25 HP
60	2p3w	Blue	240	6	360MF6WLEV	7.5 HP	360MI6WLEV	10 HP
		Red	480	7	—	—	360MI7WLEV	20 HP
	3p4w	Orange	125/250	12	460MF12WLEV	2 HP @ 120 VAC 7.5 HP @ 208-240 VAC L-L	460MI12WLEV	2 HP @ 120 VAC 10 HP @ 208-240 VAC L-L
		Blue	3Ø240	9	460MF9WLEV	15 HP	460MI9WLEV**	20 HP
		Red	3Ø480	7	460MF7WLEV	30 HP	460MI7WLEV	40 HP
		Black	3Ø600	5	460MF5WLEV	50 HP	460MI5WLEV	40 HP
	4p5w	Blue	3ØY120/208	9	560MF9WLEV	15 HP	560MI9WLEV	20 HP
		Red	3ØY277/480	7	—	—	560MI7WLEV	40 HP
		Black	3ØY347/600	5	—	—	560MI5WLEV	40 HP

*430MI9WLEVAC - Available with Factory-Installed Auxiliary Contact

**460MI9WLEVAC - Available with Factory-Installed Auxiliary Contact

Auxiliary Contacts available separately for all configurations

Accessories can be found on the back cover >

Withstands any wet and harsh location with the highest and most comprehensive ratings on the market

IP66, IP67, IP68 & IP69K



LEV Series: Mechanical Interlock Accessories



Catalog Number	Description
MOUNT-LDS	Mounting Feet
HNDLE	Replacement Handle
AUXNO	30/60/80 Amp Non-Fused Aux Contact - Normally Open
AUXNC-NF	30/60/80 Amp Non-Fused Aux Contact - Normally Closed
AUXNC-F1	30 Amp Fused Aux Contact - Normally Closed
AUXNO-F1	30 Amp Fused Aux Contact - Normally Open
AUXNO-F2	60 Amp/100 Amp Fused Aux Contact - Normally Open
AUXNO-NF1	100 Amp Non-Fused Aux Contact - Early Break
AUXNC-F2	60/100 Amp Fused Aux Contact - Normally Closed
30ASW	30 Amp Non-Fused Replacement Switch
6080A-NF	60/80 Amp Non-Fused Replacement Switch
100SW-NF	100 Amp Non-Fused Replacement Switch
30ASW-F	30 Amp Fused Replacement Switch
60ASW-F	60 Amp Fused Replacement Switch
100SW-F	100 Amp Fused Replacement Switch
HUB-34	3/4" Conduit Hub
HUB-100	1" Conduit Hub
HUB-114	1-1/4" Conduit Hub
HUB-112	1-1/2" Conduit Hub
HUB-200	2" Conduit Hub

Built for safety, performance & reliability

A Complete Offering of Mechanical Interlocks & Safety Disconnect Switches



Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line (Monday – Friday 8am to 10pm, Saturday 9am to 7pm, Sunday 9am to 5pm - E.S.T.): 1-800-824-3005

Visit our Website at: www.leviton.com/LEVseries • email: industrial@leviton.com