

lev-lok[®]

Modular Wiring Devices

Ordering and Technical Information Guide, April 2012



Table of Contents

Commercial Grade Devices

Straight Blade Receptacles

Smooth Face, Heavy Duty	3
Decora Plus™, Heavy Duty.....	4
SmartLock PRO® GFCI, Heavy Duty.....	5

Industrial Grade Devices

Straight Blade Receptacles

Smooth Face, Extra Heavy Duty	6
Isolated Ground, Extra Heavy Duty.....	7
Isolated Ground, Decora Plus™, Extra Heavy Duty	8

Toggle Switches

Single Pole, Extra Heavy Duty.....	9
------------------------------------	---

Hospital Grade Devices

Straight Blade Receptacles

Smooth Face, Heavy Duty	10
Smooth Face, Extra Heavy Duty	11
Smooth Face, Extra Heavy Duty, Illuminated.....	12
Isolated Ground, Extra Heavy Duty.....	13
Decora Plus™, Extra Heavy Duty.....	14
Decora Plus™, Extra Heavy Duty, Illuminated.....	15
Isolated Ground, Decora Plus™, Extra Heavy Duty	16
SmartLock PRO® GFCI, Heavy Duty	17

Occupancy Sensors

PIR Sensors	18
Multi-Technology Sensors.....	18

Wiring Modules 19

Smooth Face Straight Blade Receptacles

Heavy Duty Specification Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M5262-S, M5362-S, MT562-S, MT563-S, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial and institutional installations where UL Federal Specification W-C-596 and UL 498 standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498, CSA C22.2 No. 42, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Galvanized Steel with Riveted Ground Contacts
Ground Clip	Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Bushing	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism ("MT" versions)	Delrin [®] Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION



Description	Color	15A 125V 1/2HP, NEMA 5-15R 		20A 125V 1HP, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Heavy Duty Specification Grade Modular Duplex Receptacles	Brown	M5262-S	MT562-S	M5362-S	MT563-S
	Ivory	M5262-SI	MT562-SI	M5362-SI	MT563-SI
	White	M5262-SW	MT562-SW	M5362-SW	MT563-SW
	Black	—	MT562-SE	—	MT563-SE
	Blue	M5262-SB	MT562-SB	M5362-SB	MT563-SB
	Gray	M5262-GYS	MT562-SGY	M5362-GYS	MT563-SGY
	Red	M5262-SR	MT562-SR	M5362-SR	MT563-SR
	Light Almond	M5262-ST	MT562-ST	M5362-ST	MT563-ST
Description	Type				Cat. No.
Wiring Module	Stranded Wire Leads				MSTWL-A
	Solid Wire Leads				MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WSD

lev-lok[®]


M5262-S 15Amp-125 Volts

Dimensions apply to
Cat. Nos.

M5262-S, M5362-S,
MT562-S, MT563-S
& MSTWL-xxx



Standard



Tamper-Resistant

Decora Plus™ Straight Blade Receptacles



Heavy Duty Specification Grade 15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M1626, MT162, M1636, MT163, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial and institutional installations where UL Federal Specification W-C-596 and UL 498 standards of mechanical and electrical life are specified.

Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498, CSA C22.2 No. 42, NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Galvanized Steel with Riveted Ground Contacts
Ground Clip	Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism ("MT" versions)	Delrin® Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION




Description	Color	15A 125V 1/2HP, NEMA 5-15R		20A 125V 1HP, NEMA 5-20R	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Heavy Duty Specification Grade Modular Duplex Receptacles	Brown	M1626	MT162	M1636	MT163
	Ivory	M1626-I	MT162-I	M1636-I	MT163-I
	White	M1626-W	MT162-W	M1636-W	MT163-W
	Black	M1626-E	MT162-E	M1636-E	MT163-E
	Blue	M1626-B	MT162-B	M1636-B	MT163-B
	Gray	M1626-GY	MT162-GY	M1636-GY	MT163-GY
	Red	M1626-R	MT162-R	M1636-R	MT163-R
	Light Almond	M1626-T	MT162-T	M1636-T	MT163-T
Description	Type				Cat. No.
Wiring Module	Stranded Wire Leads				MSTWL-A
	Solid Wire Leads				MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WSD



M1636 20Amp-125 Volts

Dimensions apply to
Cat. Nos.

M1626, MT162, M1636,
MT163 & MSTWL-xxx



SmartLockPRO® GFCI Straight Blade Receptacles

Heavy Duty Specification Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M7599, MT759, M7899, MT789, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial and institutional installations where UL 943 Class A(GFCI) and UL 498 standards of mechanical and electrical life are specified.

Certifications and Code Compliance

NEMA WD-1&6, ANSI C-73, UL 943 Class A, UL 498, CSA C22.2 No. 42, NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Polycarbonate
Mounting Strap	Galvanized Steel with Riveted Ground Contacts
Ground Clip	Brass
Line Contacts	0.031" Thick Brass
Locking Pins	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism ("MT" versions)	Delrin® Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V, NEMA 5-15R		20A 125V, NEMA 5-20R		
		Standard	Tamper-Resistant	Standard	Tamper-Resistant	
Heavy Duty Specification Grade Modular Duplex Receptacles	Brown	M7599	MT759	M7899	MT789	
	Ivory	M7599-I	MT759-I	M7899-I	MT789-I	
	White	M7599-W	MT759-W	M7899-W	MT789-W	
	Black	M7599-E	MT759-E	M7899-E	MT789-E	
	Gray	M7599-GY	MT759-GY	M7899-GY	MT789-GY	
	Red	M7599-R	MT759-R	M7899-R	MT789-R	
	Light Almond	M7599-T	MT759-T	M7899-T	MT789-T	
Description	Type					Cat. No.
Wiring Module	Stranded Wire Leads					MSTWL-A
	Solid Wire Leads					MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads					MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads					MSTWL-WSD



M7899 20Amp-125 Volts

Dimensions apply to

Cat. Nos.

M7599, MT759,

M7899, MT789 & MSTWL-xxx



Smooth Face Straight Blade Receptacles

**Extra Heavy Duty Specification Grade
15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding**

Cat. Nos.
M5262, M5362, M5262-SG, M5362-SG, MSTWL-A, -SDA, -WST, -WSD



Application
In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial, industrial and institutional installations where UL Federal Specification W-C-596 and UL498 standards of mechanical and electrical life are specified.

Certifications and Code Compliance
NEMA WD-1&6, Fed. Spec. W-C-596, UL 498, CSA C22.2 No. 42, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Brass with Integral Ground Contacts
Ground Clip	Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Bushing	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism ("SG" versions)	Delrin [®] Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION




Description	Color	15A 125V 1/2HP, NEMA 5-15R 		20A 125V 1HP, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Extra Heavy Duty Specification Grade Modular Duplex Receptacles	Brown	M5262	M5262-SG	M5362	M5362-SG
	Ivory	M5262-I	M5262-SGI	M5362-I	M5362-SGI
	White	M5262-W	M5262-SGW	M5362-W	M5362-SGW
	Black	M5262-E	M5262-SGE	M5362-E	M5362-SGE
	Blue	M5262-B	M5262-SGB	M5362-B	M5362-SGB
	Gray	M5262-GY	M5262-SGG	M5362-GY	M5362-SGG
	Red	M5262-R	M5262-SGR	M5362-R	M5362-SGR
	Light Almond	M5262-T	M5262-SGT	M5362-T	M5362-SGT
Description	Type				Cat. No.
Wiring Module	Stranded Wire Leads				MSTWL-A
	Solid Wire Leads				MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WSD

lev-lok[®]

M5262 15Amp-125 Volts

**Dimensions apply to
Cat. Nos.**

M5262, M5362, M5262-SG,
M5362-SG & MSTWL-xxx



Isolated Ground Straight Blade Receptacles

Extra Heavy Duty Specification Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Isolated Ground

Cat. Nos.

M5262-IG, M5362-IG, MT562-IG, MT563-IG, MSTWL-IG, -SIG, -WIG

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial, industrial and institutional installations where UL Federal Specification W-C-596 and UL 498 standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498, CSA C22.2 No. 42, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Galvanized Steel
Ground Clip	Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Isolated Ground System	Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism	Delrin [®] Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V 1/2HP, NEMA 5-15R 		20A 125V 1HP, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Extra Heavy Duty Specification Grade Modular Duplex Receptacles	Orange	M5262-IG	MT562-IG	M5362-IG	MT563-IG
	Ivory	M5262-IGI	MT562-IGI	M5362-IGI	MT563-IGI
	White	M5262-IGW	MT562-IGW	M5362-IGW	MT563-IGW
	Black	M5262-IGE*	MT562-IGE*	M5362-IGE*	MT563-IGE*
	Gray	M5262-IGG	MT562-IGG*	M5362-IGG	MT563-IGG*
	Red	M5262-IGR	MT562-IGR	M5362-IGR*	MT563-IGR*
	Light Almond	M5262-IGT*	MT562-IGT*	M5362-IGT*	MT563-IGT*
Description	Type				Cat. No.
Orange Wiring Module	Stranded Wire Leads				MSTWL-IG
	Solid Wire Leads				MSTWL-SIG
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WIG


*These colors are special order items - consult customer service for availability

lev-lok[®]

M5362-IG 20Amp-125 Volts

Dimensions apply to
Cat. Nos.

M5262-IG, M5362-IG,
MT562-IG, MT563-IG,
MSTWL-xIG



Isolated Ground, Decora Plus™ Straight Blade Receptacles

Extra Heavy Duty Specification Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Isolated Ground

Cat. Nos.

M1626-IG, M1636-IG, MT162-IG, MT163-IG, MSTWL-IG, -SIG, -WIG

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial, industrial and institutional installations where UL Federal Specification W-C-596 and UL 498 standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498, CSA C22.2 No. 42, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Galvanized Steel
Ground Clip	Brass
Line Contacts	0.040" Thick Brass
Isolated Ground System	Brass
Locking Pins	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism	Delrin® Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V 1/2HP, NEMA 5-15R 		20A 125V 1HP, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Extra Heavy Duty Specification Grade Modular Duplex Receptacles	Orange	M1626-IG*	MT162-IG*	M1636-IG*	MT163-IG*
	Ivory	M1626-IGI*	MT162-IGI*	M1636-IGI*	MT163-IGI*
	White	M1626-IGW*	MT162-IGW*	M1636-IGW*	MT163-IGW*
	Black	M1626-IGE*	MT162-IGE*	M1636-IGE*	MT163-IGE*
	Gray	M1626-IGG*	MT162-IGG*	M1636-IGG*	MT163-IGG*
	Red	M1626-IGR*	MT162-IGR*	M1636-IGR*	MT163-IGR*
	Light Almond	M1626-IGT*	MT162-IGT*	M1636-IGT*	MT163-IGT*
Description	Type				Cat. No.
Orange Wiring Module	Stranded Wire Leads				MSTWL-IG
	Solid Wire Leads				MSTWL-SIG
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WIG


*These colors are special order items - consult customer service for availability

lev-lok®

M1636-IG 20Amp-125 Volts

Dimensions apply to
Cat. Nos.

M1626-IG, M1636-IG,
MT162-IG, MT163-IG,
MSTWL-xIG



Single Pole Toggle Switches

Extra Heavy Duty Specification Grade 15 & 20 Amp, 120/277 Volt

Cat. Nos.

M1201, M1221, M1201-LH, M1221-LH, M1201-L, M1221-L, MSPSW-ST, -WST, -SD, -7ST, -7SD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 120/277 Volts in commercial, industrial, and institutional installations where UL Federal Specification W-S-896 and UL 20 standards of mechanical and electrical life are specified.

Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-S-896, UL 20, CSA C22.2 No. 111, ANCE NOM 057

MATERIALS


Component	Material
Cover	Nylon
Base	PBT Polyester
Mounting Strap	0.50" Thick Galvanized Steel
Ground Clip	Brass
Contacts	Silver Alloy
Toggle	Polycarbonate
Mounting Screws	Triple Combination Head, Steel
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Line Lead (Black or Brown), 1 Load Lead (Black or Brown), 1 Ground Lead (Green)
Contacts	Copper Alloy
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 120V 1/2HP, 15A 240V 2HP		15A 120V 1/2HP	20A 120V 1HP, 20A 240V 2HP		20A 120V 1HP
		Standard Toggle	Tamper-Resistant Key Toggle	Illuminated Toggle	Standard Toggle	Tamper-Resistant Key Toggle	Illuminated Toggle
Extra Heavy Duty Specification Grade Single Pole Switches	Brown	M1201	M1201-L	M1201-LHC (Clear)	M1221	M1221-L	M1221-LHC (Clear)
	Ivory	M1201-I	M1201-IL	M1201-LHI	M1221-I	M1221-IL	M1221-LHI
	White	M1201-W	—	M1201-LHW	M1221-W	M1221-WL	M1221-LHW
	Black	—	—	—	M1221-E	—	—
	Gray	M1201-GY	—	—	M1221-GY	M1221-GL	—
	Red	M1201-R	—	—	M1221-R	M1221-RL	—
	Light Almond	—	—	—	M1221-T	—	—
Description	Type						Cat. No.
Wiring Module	Stranded Wire Leads (Black)						MSPSW-ST
	Stranded Wire Leads (Black) with Push Wire Connector						MSPSW-WST
	Solid Wire Leads (Black)						MSPSW-SD
	Stranded Wire Leads (Brown) to identify 277V applications						MSPSW-7ST
	Solid Wire Leads (Brown) to identify 277V applications						MSPSW-7SD



Dimensions apply to
Cat. Nos.
M1201, M1221,
M1201-LH, M1221-LH,
M1201-L, M1221-L,
MSPSW-xxx



Standard

Tamper-Resistant

Smooth Face Straight Blade Receptacles

Heavy Duty Hospital Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M8200-H, MT820, M8300-H, MT830, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial, industrial and institutional installations where UL Federal Specification W-C-596 and UL 498 HG standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498 HG, CSA C22.2 No. 42 HG, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Galvanized Steel with Riveted Ground Contacts
Ground Clip	Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Bushing	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism ("MT" versions)	Delrin® Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V 1/2HP, NEMA 5-15R 		20A 125V 1HP, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Heavy Duty Hospital Grade Modular Duplex Receptacles	Brown	M8200-H	MT820	M8300-H	MT830
	Ivory	M8200-HI	MT820-I	M8300-HI	MT830-I
	White	M8200-HW	MT820-W	M8300-HW	MT830-W
	Black	M8200-HE	MT820-E	M8300-HE	MT830-E
	Blue	M8200-HB	MT820-B	M8300-HB	MT830-B
	Gray	M8200-HGY	MT820-GY	M8300-HGY	MT830-GY
	Red	M8200-HR	MT820-R	M8300-HR	MT830-R
	Light Almond	M8200-HT	MT820-T	M8300-HT	MT830-T
Description	Type				Cat. No.
Wiring Module	Stranded Wire Leads				MSTWL-A
	Solid Wire Leads				MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WSD

lev-lok®

M8300-H 20Amp-125 Volts



Dimensions apply to

Cat. Nos.


M8200-H, MT820,

M8300-H, MT830

& MSTWL-xxx



Standard



Tamper-Resistant

Smooth Face Straight Blade Receptacles

Extra Heavy Duty Hospital Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M8200, M8200-SG, MRI15, M8300, M8300-SG, MRI20, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial, industrial and institutional installations where UL Federal Specification W-C-596 and UL 498 HG standards of mechanical and electrical life is specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498 HG, CSA C22.2 No. 42 HG, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Single Piece Nickel-Plated Brass with Integral Ground Contact (Brass for MRI series)
Ground Clip	Nickel-Plated Brass (Brass for MRI series)
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Bushing	Solid Brass
Mounting Screws	Triple Combination Head, Steel (Brass for MRI Series)
Shutter Mechanism ("SG" versions)	Delrin [®] Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V 1/2HP, NEMA 5-15R 			20A 125V 1HP, NEMA 5-20R 		
		Standard	Tamper-Resistant	MRI*	Standard	Tamper-Resistant	MRI*
Extra Heavy Duty Hospital Grade Modular Duplex Receptacles	Brown	M8200	M8200-SG	—	M8300	M8300-SG	—
	Ivory	M8200-I	M8200-SGI	MRI15-I	M8300-I	M8300-SGI	MRI20-I
	White	M8200-W	M8200-SGW	MRI15-W	M8300-W	M8300-SGW	MRI20-W
	Black	M8200-E	M8200-SGE	—	M8300-E	M8300-SGE	—
	Blue	M8200-B	M8200-SGB	—	M8300-B	M8300-SGB	—
	Gray	M8200-GY	M8200-SGG	MRI15-GY	M8300-GY	M8300-SGG	MRI20-GY
	Red	M8200-R	M8200-SGR	MRI15-R	M8300-R	M8300-SGR	MRI20-R
	Light Almond	M8200-T	M8200-SGT	MRI15-T	M8300-T	M8300-SGT	MRI20-T
Description	Type						Cat. No.
Wiring Module	Stranded Wire Leads						MSTWL-A
	Solid Wire Leads						MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads						MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads						MSTWL-WSD



*MRI Series receptacles feature components made of non-ferrous metals that are safe for use in high magnetic field environments.

lev-lok[®]


M8300 20Amp-125 Volts

Dimensions apply to
Cat. Nos.

M8200, M8200-SG,
MRI15, M8300,
M8300-SG, MRI20
& MSTWL-xxx



Standard, MRI



Tamper-Resistant

Smooth Face, Illuminated Straight Blade Receptacles

Extra Heavy Duty Hospital Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M8200-IL, MT820-IL, M8200-PLI, M8300-IL, MT830-IL, M8300-PL, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial, industrial and institutional installations where UL Federal Specification W-C-596 and UL 498 HG standards of mechanical and electrical life is specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498 HG, CSA C22.2 No. 42 HG, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Single Piece Nickel-Plated Brass with Integral Ground Contact (Brass for MRI series)
Ground Clip	Nickel-Plated Brass (Brass for MRI series)
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Bushing	Solid Brass
Mounting Screws	Triple Combination Head, Steel (Brass for MRI Series)
Shutter Mechanism ("SG" versions)	Delrin® Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION


Description	Color	15A 125V 1/2HP, NEMA 5-15R 			20A 125V 1HP, NEMA 5-20R 		
		Illuminated	Illuminated, Tamper Resistant	Power-Indication	Illuminated	Illuminated, Tamper Resistant	Power-Indication
Extra Heavy Duty Hospital Grade Modular Duplex Receptacles	Ivory	M8200-ILI	MT820-ILI	M8200-PLI	M8300-ILI	MT830-ILI	M8300-PLI
	White	M8200-ILW	MT820-ILW	M8200-PLW	M8300-ILW	MT830-ILW	M8300-PLW
	Gray	M8200-ILG	MT820-ILG	M8200-PLG	M8300-ILG	MT830-ILG	M8300-PLG
	Red	M8200-ILR	MT820-ILR	M8200-PLR	M8300-ILR	MT830-ILR	M8300-PLR
	Light Almond	M8200-ILT	MT820-ILT	M8200-PLT	M8300-ILT	MT830-ILT	M8300-PLT
Description	Type						Cat. No.
Wiring Module	Stranded Wire Leads						MSTWL-A
	Solid Wire Leads						MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads						MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads						MSTWL-WSD

lev-lok®

M8300-IL 20Amp-125 Volts

Dimensions apply to
Cat. Nos.

M8200-PL, M8200-IL,
MT820-IL, M8300-PL,
M8300-IL, MT830-IL
& MSTWL-xxx



Power-Indication

Illuminated

Isolated Ground Straight Blade Receptacles

Extra Heavy Duty Hospital Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Isolated Ground

Cat. Nos.

M8200-IG, M8300-IG, MT820-IG, MT830-IG, MSTWL-IG, -SIG, -WIG

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial and institutional installations where UL Federal Specification W-C-596 and UL 498 HG standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498 HG, CSA C22.2 No. 42 HG, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Plated Steel
Ground Clip	Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism	Delrin [®] Acetal
Isolated Ground System	Brass
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V 1/2HP, NEMA 5-15R 		20A 125V 1HP, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Extra Heavy Duty Hospital Grade Modular Duplex Receptacles	Orange	M8200-IG	MT820-IG	M8300-IG	MT830-IG
	Ivory	M8200-IGI	MT820-IGI	M8300-IGI	MT830-IGI
	White	M8200-IGW	MT820-IGW	M8300-IGW	MT830-IGW
	Black	M8200-IGE*	MT820-IGE*	M8300-IGE*	MT830-IGE*
	Gray	M8200-IGG*	MT820-IGG*	M8300-IGG*	MT830-IGG*
	Red	M8200-IGR	MT820-IGR	M8300-IGR	MT830-IGR
	Light Almond	M8200-IGT*	MT820-IGT*	M8300-IGT*	MT830-IGT*
Description	Type				Cat. No.
Wiring Module	Stranded Wire Leads				MSTWL-IG
	Solid Wire Leads				MSTWL-SIG
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WIG





*These colors are special order - contact customer service for availability

lev-lok[®]

M8300-IG 20Amp-125 Volts

Dimensions apply to
Cat. Nos.

M8200-IG, M8300-IG,
MT820-IG, MT830-IG,
MSTWL-xIG



Standard

Tamper-Resistant

Decora Plus™ Straight Blade Receptacles

Extra Heavy Duty Hospital Grade 15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M1626-HG, MT162-HG, M1636-HG, MT163-HG, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial and institutional installations where UL Federal Specification W-C-596 and UL 498 HG standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498 HG, CSA C22.2 No. 42 HG, ANCE NOM 057

MATERIALS




Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Single Piece Nickel-Plated Brass with Integral Ground Contact
Ground Clip	Nickel-Plated Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism ("MT" versions)	Delrin® Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V 1/2HP, NEMA 5-15R 		20A 125V 1HP, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Extra Heavy Duty Hospital Grade Modular Duplex Receptacles	Brown	M1626-HG0	—	M1636-HG0	—
	Ivory	M1626-HGI	MT162-HGI	M1636-HGI	MT163-HGI
	White	M1626-HGW	MT162-HGW	M1636-HGW	MT163-HGW
	Black	M1626-HGE	—	M1636-HGE	—
	Blue	M1626-HGB	—	M1636-HGB	—
	Gray	M1626-HGG	MT162-HGG	M1636-HGG	MT163-HGG
	Red	M1626-HGR	MT162-HGR	M1636-HGR	MT163-HGR
	Light Almond	M1626-HGT	—	M1636-HGT	MT163-HGT
Description	Type				Cat. No.
Wiring Module	Stranded Wire Leads				MSTWL-A
	Solid Wire Leads				MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WSD

lev-lok®
M1636-HG 20Amp-125 Volts
**Dimensions apply to
Cat. Nos.**

M1626-HG, MT162-HG,
M1636-HG, MT163-HG,
& MSTWL-xxx



Decora Plus™ Illuminated Straight Blade Receptacles

Extra Heavy Duty Hospital Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M1626-IL, MT162-IL, M1626-PL, M1636-PL, MT163-PL, M1636-PL, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial and institutional installations where UL Federal Specification W-C-596 and UL 498 HG standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498 HG, CSA C22.2 No. 42 HG, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Single Piece Nickel-Pated Brass with Integral Ground Contact
Ground Clip	Nickel-Plated Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism ("MT" versions)	Delrin® Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V 1/2HP, NEMA 5-15R 			20A 125V 1HP, NEMA 5-20R 		
		Illuminated#	Illuminated, Tamper-Resistant#	Power Indication	Illuminated#	Illuminated, Tamper-Resistant#	Power Indication
Extra Heavy Duty Hospital Grade Modular Duplex Receptacles	Ivory	M1626-ILI*	MT162-ILI*	M1626-PLI	M1636-ILI*	MT163-ILI*	M1636-PLI
	White	M1626-ILW	MT162-ILW	M1626-PLW	M1636-ILW	MT163-ILW	M1636-PLW
	Gray	M1626-ILG*	MT162-ILG*	M1626-PLG	M1636-ILG*	MT163-ILG*	M1636-PLG
	Red	M1626-ILR	MT162-ILR	M1626-PLR	M1636-ILR	MT163-ILR	M1636-PLR
	Light Almond	M1626-ILT*	MT162-ILT*	M1626-PLT	M1636-ILT*	MT163-ILT*	M1636-PLT
Description	Type						Cat. No.
Wiring Module	Stranded Wire Leads						MSTWL-A
	Solid Wire Leads						MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads						MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads						MSTWL-WSD

#Available Q2 2012



*These colors are special order - contact customer service for availability



M1636-IL 20Amp-125 Volts

Dimensions apply to Cat. Nos.

M1626-IL, MT162-IL, M1626-PL, M1636-PL, MT163-PL, M1636-PL & MSTWL-xxx



Isolated Ground, Decora Plus™ Straight Blade Receptacles

Extra Heavy Duty Hospital Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Isolated Ground

Cat. Nos.

MD820-IG, MD830-IG, MDT82-IG, MDT83-IG, MSTWL-IG, -SIG, -WIG

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial and institutional installations where UL Federal Specification W-C-596 and UL 498 HG standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, Fed. Spec. W-C-596, UL 498 HG, CSA C22.2 No. 42 HG, ANCE NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Nylon
Mounting Strap	Plated Steel
Ground Clip	Brass
Line Contacts	0.040" Thick Brass
Locking Pins	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism	Delrin® Acetal
Isolated Ground System	Brass
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION

Description	Color	15A 125V 1/2HP, NEMA 5-15R 		20A 125V 1HP, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Extra Heavy Duty Hospital Grade Modular Duplex Receptacles	Orange	MD820-IG	MDT82-IG	MD830-IG	MDT83-IG
	Ivory	MD820-IGI	MDT82-IGI	MD830-IGI*	MDT83-IGI
	White	MD820-IGW	MDT82-IGW	MD830-IGW	MDT83-IGW
	Black	MD820-IGE*	MDT82-IGE	MD830-IGE*	MDT83-IGE
	Gray	MD820-IGG*	MDT82-IGG	MD830-IGG*	MDT83-IGG*
	Red	MD820-IGR	MDT82-IGR	MD830-IGR	MDT83-IGR*
	Light Almond	MD820-IGT*	MDT82-IGT	MD830-IGT*	MDT83-IGT
Description	Type				Cat. No.
Wiring Module	Stranded Wire Leads				MSTWL-IG
	Solid Wire Leads				MSTWL-SIG
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WIG


*These colors are special order - contact customer service for availability

lev-lok®

MD830-IG 20Amp-125 Volts

Dimensions apply to
Cat. Nos.

MD820-IG, MD830-IG,
MDT82-IG, MDT83-IG,
MSTWL-xIG



Standard

Tamper-Resistant

SmartLockPRO® GFCI Straight Blade Receptacles

Heavy Duty Hospital Grade

15 & 20 Amp, 125 Volt, Duplex, 2-Pole, 3-Wire, Self-Grounding

Cat. Nos.

M7599-HG, MT759-HG, M7899-HG, MT789-HG, MSTWL-A, -SDA, -WST, -WSD

Application

In accordance with the NEC, these devices are suitable for use in all 15 or 20 ampere branch circuits of 125 Volts in commercial, industrial and institutional installations where UL 943 Class A(GFCI) and UL 498 HG standards of mechanical and electrical life are specified.



Certifications and Code Compliance

NEMA WD-1&6, ANSI C-73, UL 943 Class A, UL 498, CSA C22.2 No. 42, NOM 057

MATERIALS

Component	Material
Cover	Nylon
Base	Polycarbonate
Mounting Strap	Galvanized steel with Riveted Ground Contact
Ground Clip	Brass
Line Contacts	0.031" Thick Brass
Locking Pins	Solid Brass
Mounting Screws	Triple Combination Head, Steel
Shutter Mechanism ("MT" versions)	Delrin® Acetal
Wiring Module	Material
Wire Leads	6", #12 AWG THHN 1 Hot Lead (Black), 1 Neutral Lead (White), 1 Ground Lead (Green)
Contacts	Brass
Housing	Polycarbonate

ORDERING INFORMATION



Description	Color	15A 125V, NEMA 5-15R 		20A 125V, NEMA 5-20R 	
		Standard	Tamper-Resistant	Standard	Tamper-Resistant
Heavy Duty Hospital Grade Duplex Receptacles	Brown	M7599-HG0	MT759-HG0	M7899-HG0	MT789-HG0
	Ivory	M7599-HGI	MT759-HGI	M7899-HGI	MT789-HGI
	White	M7599-HGW	MT759-HGW	M7899-HGW	MT789-HGW
	Black	M7599-HGE	MT759-HGE	M7899-HGE	MT789-HGE
	Gray	M7599-HGY	MT759-HGY	M7899-HGY	MT789-HGY
	Red	M7599-HGR	MT759-HGR	M7899-HGR	MT789-HGR
	Light Almond	M7599-HGT	MT759-HGT	M7899-HGT	MT789-HGT
Description	Type				Cat. No.
Wiring Module	Stranded Wire Leads				MSTWL-A
	Solid Wire Leads				MSTWL-SDA
	Stranded Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WST
	Solid Wire with 4-Port Push Wire Connectors Attached to All 3 Leads				MSTWL-WSD

lev-lok®

M7899-HG 20Amp-125 Volts

Dimensions apply to
Cat. Nos.

M7599-HG, MT759-HG,
M7899-HG, MT789-HG & MSTWL-xxx



Box Mount Occupancy Sensors

120/277 Volt


Cat. Nos.

MDS10-ID, MDS15-ID, MSSMT-GD, MSPSW-XS

Certifications and Code Compliance

UL Listed/CSA Certified, complies with CEC Title 24, complies with FCC Regulations, NOM

FIELD OF VIEW




ORDERING INFORMATION

Description	Color	PIR	PIR with Self-Adaptive Technology	Multi-Technology
Occupancy Sensors	Ivory	MDS10-IDI	MDS15-IDI	MSSMT-GDI
	White	MDS10-IDW	MDS15-IDW	MSSMT-GDW
	Black	MDS10-IDE	MDS15-IDE	MSSMT-GDE
	Gray	MDS10-IDG	MDS15-IDG	MSSMT-GDG
	Light Almond	MDS10-IDT	MDS15-IDT	MSSMT-GDT
Description	Type			Cat. No.
Wiring Module	Stranded Wire Leads			MSPSW-XST
	Solid Wire Leads			MSPSW-XSD


lev-lok[®]

Dimensions apply to
Cat. Nos.

MDS10, MDS15, MSSMT,
MSPSW-XS



PIR & PIR with Self-Adaptive Technology



Multi-Technology

Wiring Modules




MSTWL-A



MSTWL-IG




MSTWL-WST



MSTWL-ST

lev-lok[®]
Modular Wiring Devices



Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747
Phone: 1-800-323-8920 ■ Fax: 1-800-832-9538
Tech Line (8:30AM-7:00PM E.S.T. Mon-Fri): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9
Phone: 1-800-469-7890 ■ Fax: 1-800-563-1853

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290
Phone: (+52) 55-5082-1040 ■ www.leviton.com.mx

Visit us on the web at: www.leviton.com/lev-lok ■ email: industrial@leviton.com

Q-347C