



LEVITON®

In these times,
**we are here to
support you.**

We have increased
our inventory to respond
quickly to your needs.



**Full Line of Health Care
Wiring Devices**

- Switches, receptacles, wallplates, medical grade power strips, plugs & connectors

**Antimicrobial Treated
Switches and Wallplates**

- Antimicrobial additive inhibits 99.9% of bacterial growth when cleaned regularly

**Temporary Power Devices
for Quick Power Needs**

- Portable outlet boxes, power distribution boxes
- Single pole cam-type connectors
- Pin & Sleeve IEC 60309 devices

HOSPITAL GRADE CERTIFIED DEVICES

OVER 115 YEARS IN THE INDUSTRY

CONTACT YOUR APPLICATION SPECIALIST

Electrical wiring devices for any health care application



Receptacles

- Offering includes: Standard, Decora Plus™, Tamper-Resistant, Power Indication, MRI, Isolated Ground, Illuminated, 4-in-1, AFCI, GFCI, AFCI/GFCI combo, Weather Resistant and USB configurations



Switches

- AC Toggle and Decora Plus™ Switches
 - Pilot Light, Illuminated, Tamper-Resistant and Antimicrobial Treated Versions
 - Single Pole, Double Pole, 3-Way and 4-Way
- Key-Locking
- Safety Disconnect Switches (Non-Metallic and Stainless Steel)



Lev-Lok

- Modular system allows for 3x faster installation and 5x faster device swap outs than traditional wiring
- Lev-Lok® Hospital Grade Receptacles
 - Standard, Decora, Illuminated, Power Indication, GFCI, Tamper-Resistant, MRI, Isolated Ground, USB and Surge Protective versions
- Lev-Lok® Switches
 - Standard, Tamper-Resistant, Antimicrobial and Illuminated versions
- Lev-Lok® Occupancy Sensors
 - Available in Passive Infrared (PIR) and Multi-Technology (Ultrasonic and PIR) versions



Wallplates & Covers

- Metallic Wallplates
 - Available in Type 302 and 430 Stainless Steel, Aluminum and Brass; Antimicrobial Treated version available
- Special Purpose Wallplates
 - Pre-marked with “EMERGENCY” for Easy Identification
- Weatherproof Covers
 - Comply with NEC® Article 406.9 for Weatherproof Enclosures in Wet and Damp Locations



Antimicrobial Treated Devices

- Antimicrobial treated devices inhibit 99.9% of bacterial growth in between normal cleanings
- Combat the spread of germs in public facilities
 - Tough – Made durable in order to withstand harsh chemical cleaning products, stringent washings, and UV lights with minimal wear and tear
 - Clean – Inhibit 99.9% of bacterial growth on frequently touched switches and wallplates in between normal cleanings
- Offering includes devices that get touched the most
 - Standard toggle and Decora Plus™ switches and wallplates

Medical Grade Power Strips

- Designed explicitly for use in health care facilities, including all types of Patient Care Rooms, both within and beyond the Patient Care Vicinity, as defined by NEC Article 517
- Satisfy electrical safety requirements specified in NFPA 99: Health Care Facilities Code, allowing facility managers to ensure code compliance and safety
- Offering includes standard med-strips, surge protected med-strips, and med-strips with Inform™ Technology
 - Devices with Inform Technology feature an LED that activates when the NFPA 99 load limit (75%) has been exceeded
 - Inform™ monitors the load of connected devices so you don't have to, eliminating the need for manual calculations



Providing power when and where you need it



Cams

- Up to 1135 A, 600 V
- Insulators molded of high-performance TPV
- Slit and cam male contact design compensates for wear
- Color-coded insulators for easy phase identification
- UL Listed and CSA Certified



Portable Boxes & Covers

- Single- and two-gang, feed-thru and pendant style boxes
- Many cover configurations; flip-lid versions are rated NEMA Type 3R
- Resistant to heat, harsh chemicals and impacts



Industrial Grade Plugs and Connectors

- Black & White® Extra Heavy Duty (15-50 A, 125-600 V)
- Wetguard® Watertight (15-30 A, 125-600 V)
- Rhino-Hide® Rough Service (15-20 A, 125-250 V)
- NEMA and Non-NEMA Configurations
- UL/Fed.Spec./CSA/NOM
- Industry leading limited lifetime warranty



Power Distribution Box

- 50 A, 125/250 V
- UL and CSA Listed
- Sturdy metal housing and legs withstand heavy abuse
- Weatherproof covers prevent nuisance tripping



IEC 60309 Pin & Sleeve Devices

- LEV Series
 - 30 & 60 A Plugs, Connectors, Receptacles, Inlets, & Mechanical Interlocks
 - Superior Watertight Ratings: IP66, IP67, IP68, & IP69K Rated, NSF Certified
 - Simplify Installation and Improve Safety & Productivity
- Standard Series North American IP69K Configurations in 20, 30, 60, & 100 A
- International Splashproof & Watertight Configurations in 16, 32, 63, & 125 A

 inform™



**CONTACT YOUR
APPLICATION SPECIALIST**