Ultrasonic Ceiling Mounted Occupancy Sensor

Cat. No. OSC05-U, OSC10-U, OSC20-U

To be used with 24VDC OSPxx Series and CN100 Power Pack Class II Low-Voltage Wiring

INSTALLATION INSTRUCTIONS CATALOG ITEMS

Current

30m/

40mA

onsumption

Description

1-Way Ultrasonic

WARNINGS AND CAUTIONS

- TO AVOID FIRE, SHOCK, OR DEATH: TURN OFF POWER at circuit breaker or fuse and test that power is off before wiring!
- · To be installed and/or used in accordance with appropriate electrical codes and regulations.
- · If you are unsure about any part of these instructions, consult an electrician
- · Sensors must be mounted on a vibration free surface.
- · All sensors must be mounted at least 6 feet away from air vents.
- Do not mount sensors closer than 10 feet from each other.

Tools needed to install your Sensor

Slotted/Phillips Screwdriver Electrical Tape Pliers Pencil Cutters

Parts Included List

Sensor (1) #8-32 x 1/2" Screw (2) #8-32 x 1-1/2" Screw (2) #8-32 Washer and Nut (2) Threaded Rod (1) and Hex Nut (1) Plastic Washer (1)

DESCRIPTION

The Occupancy Sensor is a low-voltage ultrasonic sensor that works with the OSPxx Series and CN100 power pack to automatically control lighting. The sensor turns the lights on and keeps them on whenever occupancy is detected and will turn them off after the 'delayed-off time' has expired.


The sensor continually analyzes and adjusts to changing conditions. The sensor uses the latest microprocessor-based technology which permits it to continually adjust and optimize its performance

Ultrasonic (doppler shift) motion detection gives maximum sensitivity that yields a sensor vith excellent performance.

INSTALLING YOUR OCCUPANCY SENSOR


NOTE: Use check boxes |V| when Steps are completed.


Step 1 WARNING: TO AVOID FIRE, SHOCK, OR DEATH; TURN OFF POWER at circuit breaker or fuse and test that power is off before wiring!





Step 2 Preparing and connecting wires:





Step 3 Typical Installations:

Listed are 3 typical installation options (A, B, and C). Choose one that best suits your needs. Other methods of installation may be possible but they have not been described here

A. Drop Ceiling Installation (Mounting Option A):

NOTE: Use the threaded rod included.

- 1. Select location for mounting of sensor for your application (refer to Mounting Location Diagram).
- 2. Use the supplied threaded rod or other methods to make a hole (1/2" to 1") in the ceiling tile just large enough to pass the body of the threaded rod through.
- 3. Insert the sensor wires through the flared end of the threaded rod. Position the threaded rod to the base of the sensor.
- 4. Insert the flared end of the threaded rod into the opening in the bottom of the sensor and twist to lock into place.

Step 3 cont'd	
---------------	--


5. Push the wires into the hole in the ceiling tile and insert the threaded rod until the sensor is flush with the tile.

Catalog No

OSC05-U0W

DSC10-U0V

- 6. Insert wires through the hole in the included washer, then place the included washer over the rod and screw on the included hex nut.
- 7. Class II Wiring: Connect low-Voltage wires from Power Pack to Sensor per WIRING DIAGRAM as follows: Twist strands of each lead tightly and, with circuit conductors, push firmly into appropriate wire connector. Screw connectors on clockwise making sure that no bare conductor shows below the wire connectors. Secure each connector with electrical tape.
- 8. Rotate the sensor to the desired orientation. Note that the sensor base and back cover are keyed. To lock the device in place, ensure that the arrows are not aligned.
- 9. Restore power at circuit breaker or fuse to Power Pack. INSTALLATION IS COMPLETE.
- Mounting Option Diagram A Occupancy Sensor Mounted to Drop Ceiling Using Threaded Rod



B. Wallboard or Drop Ceiling Installation (Mounting Option B):

- NOTE: You may use the mounting screws, nuts and washers included, or screws in combination with commercially available wall anchors.
- 1. Select location for mounting of sensor for your application (refer to Mounting Location Diagram)
- 2. Make a hole in the ceiling tile or wallboard large enough to pass the wire connections and wire nuts through (approximately 1" diameter)
- 3. Remove the back cover of the sensor. Hold the back cover and body of the sensor and rotate until the two arrows line up and pull apart.
- 4. Install back cover of the ceiling sensor to the wallboard or drop ceiling using the included screws, nuts and washers, or screws in combination with commercially available wall anchors.
- 5. Class II Wiring: Connect low-Voltage wires from Power Pack to Sensor per WIRING DIAGRAM as follows: Twist strands of each lead tightly and, with circuit conductors, push firmly into appropriate wire connector. Screw connectors on clockwise making sure that no bare conductor shows below the wire connectors. Secure each connector with electrical tape.
- 6. Push wire connections through the center hole of the back cover and into the ceiling.
- 7. Secure the sensor body to the back cover by aligning the arrows. Lock it by turning the sensor such that the arrows do not line up.
- 8. Rotate the sensor to the desired orientation.

(2 places)


190

Keylock Arrow

-Sensor Front Cover

-Sensor Base

9. Restore power at circuit breaker or fuse to Power Pack. INSTALLATION IS COMPLETE.



Operating

requency

40KHz

40KHz

Coverage

500 sq. ft

Suggested


ounting Locati Mount in corn


over doorway

Mount in cente


NOTE: Listed below are suggested JUNCTION BOX installation applications which require mounting to conduit in one of the following three ways:


Occupancy Sensor Mounted to Octagon Box Installed Flush to Wallboard Ceiling





OSPxx Series Power Pack






Back Cover shown mounted

on ceiling with screws



FCC COMPLIANCE STATEMENT:

This device complies with part 15 and part 18 of the FCC rules. Operation is subject to the following two conditions: (1) This device must not cause harmful interference, and (2) This device must accept any interference received, including interference that may cause undesired operation.



OPERATION

Motion detection by the ultrasonic sensor will turn on the lights as well as keeping them on. When motion is not detected, the lights will turn off after the delayed-off time.

- Delayed-Off time The sensor is designed to turn the lights off if no motion is detected after a specified time. This length of time is called the delayed-off time and is set using the timer (Black) knob on the sensor. The adapting patterns will modify the delayed-off time to fit the parameters of each installation based on environmental conditions and occupancy patterns.
- Walk-through Mode The walk-through feature is useful when a room is momentarily occupied. With this feature, the sensor will turn the lights off shortly after the person leaves the room.

The walk-through feature works as follows: When a person enters the room, the lights will turn on. If the person leaves the room before the default walk-through timeout of 2.5 minutes, the sensor will turn the lights off. If the person stays in the room for longer than 2.5 minutes, the sensor will proceed to the standard operation.

LED Operation - There are two LED indicators that will flash when motion is detected. The LED flash can be disabled using the LED disable switch setting. Green flash indicates motion detection by ultrasonic technology.

ADAPTIVE FUNCTIONS

The Sensor continually analyzes the parameters of the motion detection signal and adjusts its internal operation to maximize detection of motion while minimizing the effects of noise (electrical noise, air currents, temperature changes, etc...).

Operation:

When the lights turn on, the sensor initially enters the "walk-through" mode. Once the room is occupied for longer than 2.5 minutes, the sensor exits the "walk-through" mode and enters the "Occupied" mode. When the sensor is first installed, the delayed-off time for the occupied mode is based on the Time adjustment settings. While the sensor is in use, the delayed-off time will change, based on how the sensor adapts to the room conditions. Whenever the sensor subsequently turns on, the value of the delayed-off time will be the adapted value (refer to Occupancy Pattern Learning For Delayed Off Time).

The adapted settings can be reset using the DIP switch.

Occupancy Pattern Learning For Delayed Off Time:

The sensor will automatically change the delayed off time in response to the occupancy and environmental conditions of the space it is installed in. The sensor analyzes the motion signal properties and will minimize the delayed off time duration when there is frequent motion detection, and lengthen the delayed off time duration when there is weak and infrequent motion detection.

In the case of a false-off condition (lights turn off when the room is occupied), the delayed off time duration will immediately be lengthened to prevent further false turn offs

Occupancy Pattern Learning for Ultrasonic Technology:

The sensor learns the occupancy patterns of a space during the course of a day, for a seven day period. At any given time, the sensor will look at the collected data and adjust its ultrasonic sensitivity. The sensor will adjust the sensitivity to make it less likely to turn on during a period of non-occupancy and more likely to turn on during a period of occupancy.

SETTINGS

Default Settings:

Adjustment knob settings as per "recommended manual settings," (refer to Table 3 and Figure 1).

All switches in the off position (refer to Table 4)

TABLE 3: ADJUSTMENT KNOB SETTINGS						
Knob Color	Symbol	Function	Knob Setting	Factory Default Setting		
Green	31	Sets the ultrasonic range	Range setting Full CCW = min. (OFF) Full CW = max.	50%		
Black	\bigcirc	Delayed- Off Time	Full CCW = min. (30 sec.) Full CW = max. (30 min.)	50% (10 min)		
Blue	THE .	Ambient Light Override (Gray wire only)	Full CCW – Lights stay OFF Full CW – Lights always turn ON (NO ambient light override) Range – 100-3000 LUX	100%		

TABLE 4: SWITCH SETTINGS						
SWITCH	SWITCH FUNCTIONS	SWITCH SETTINGS				
	Bank A	OFF	ON			
A1	N/A	N/A	N/A			
A2	N/A	N/A	N/A			
A3	Manual Mode	Auto Adapting Enabled	Auto Adapting Disabled			
A4	Walk-Through Disable	Walk-Through Enabled	Walk-Through Disabled			
	Bank B					
B1	Override to ON	Auto Mode	Lights Forced ON			
B2	Override to OFF	Auto Mode	Lights Forced OFF			
B3	Test Mode	OFF→ ON → OFF = Enter/Exit Test Mode				
B4	LEDs Disable	LEDs Enabled	LEDs Disabled			

Test Mode: To set the delayed-off time to 6 seconds for performing a walk test. While the sensor is in test mode, the LED's will flash amber once a second.

1. ENSURE POWER IS ON.

2. Remove front cover.

- 3. Locate Dip Switch 3 in Bank B (B3) (refer to Figure 1). B3 will be in the OFF position from the factory.
- 4. To enter Test Mode, move switch to ON and back to OFF. The test mode has now been entered with a 6 second time-out. NOTE: If B3 is already in the ON position, then test mode can be entered by just moving it to the OFF position

NOTES:

- 1. The timer will remain in the 6 second test mode for 15 minutes, then automatically exit test mode and reset to the delayed-off time setting as defined by the black timer knob.
- 2. To manually take the timer out of the 6 second test mode, simply toggle the switch B3 from OFF to ON and back to OFF.


Photocell (Ambient Light Override) adjustment:


In order to use the Ambient Light Override functionality of the sensor, the sensor must be wired to the power pack (OSPXX) using the gray wire instead of the blue wire. This feature allows the user to conserve energy by keeping the controlled lights off when not necessary. The sensor does this by measuring the amount of ambient light in the installed area and keeping the controlled lights off if there is enough ambient light available. To use this feature, the Photocell adjustment (blue) knob must be adjusted from the default position. Once this adjustment is made, the controlled lights will only turn on if the ambient light present is less than the setting.


To set the Photocell level (used with the gray wire connection):


NOTE: This setting must be performed when the natural light is low enough to require artificial light.


- 1. Remove the cover from the sensor.
- 2. Make note of the position of the Green knob. Rotate the Green knob full CCW and enter the sensor's Test mode as described above
- 3. Rotate the Blue knob full CCW.
- 4. Wait for the lights to turn OFF.
- 5. Rotate the Green knob full CW.
- 6. Slowly rotate the blue knob clockwise until the lights turn ON. This is the correct setting
- 7. Return the Green knob to its original position.
- 8. Replace cover. Setting is complete.











FOR CANADA ONLY:

For warranty information and/or product returns, residents of Canada should contact Leviton in writing at Leviton Manufacturing of Canada Ltd to the attention of the Quality Assurance Department, 165 Hymus Blvd, Pointe-Claire (Quebec), Canada H9R 1E9 or by telephone at 1 800 405-5320

LIMITED 5 YEAR WARRANTY AND EXCLUSIONS

Leviton warrants to the original consumer purchaser and not for the benefit of anyone else that this product at the time of its sale by Leviton is free of defects by repair or replacement, at its option. For details visit www.leviton.com or call 1-800-824-3005. This warranty excludes and there is disclaimed liability for labor for removal of this product or reinstallation. This warranty is void if this product is installed improperly or in an improper environment, overloaded, misused, opened, abused, or altered in any manner, or is not used under normal operating conditions or not in accordance with any labels or instructions. of any such implied warranty, including merchantability and fitness for a particular purpose, is limited to five years. Leviton is not liable for incidental, indirect, special, or consequential damages to, or loss of use of, any equipment, lost sales or profits or delay or failure to perform this warranty obligation. The remedies provided herein are the exclusive remedies provided herein are the exclusive remedies under this warranty, whether based on contract, tort or otherwise

Figure 4 (Cat. No. OSC20) Field-of-View Ranges

