

Color Pro Strip LED Fixture



DESCRIPTION

The Color Pro Strip is a wash LED lighting fixture perfect for near-wall wash applications and other wash applications where linear fixtures are appropriate. For continuous washes, strips should be mounted end-to-end.

- 35° Field Angle*
- (264) .22W 10mm LEDs
- LED Package
 - RGB - Red (96), Green (72), Blue (96)
- Digital Display
- Flicker-free 400Hz refresh rate
- Control Options
 - DMX512
 - Audio-Trigger built-in microphone
- DMX Operating Modes
 - Mode P - 12 channels; 4 x Red, Green, Blue
 - Mode A - 16 Channels; Red, Green, Blue, Dimmer/Strobe
 - Mode F - 6 Channels; Dimmer, Red, Green, Blue, Strobe, Macros
 - Mode H - 24 Channels; 8 x Red, Green, Blue
 - Mode L - 40 Channels; 8 x Red, Green, Blue, Dimmer, Strobe
- Operating Mode
 - Master/Slave
 - Stand-Alone
- Center mounting yoke and dual-end mounting points

INTERNAL PROGRAMS

- Macro
 - No Function
 - Color Fade
 - Color Fade RGB
 - Color Fade Chase
 - Color Snap
 - Color Pulse
 - Random Macro
- Flash - Strobes the LEDs on the whole strip in White color
- Fade Scroll - Fades the LEDs on the whole strip from one color to another
- Flash Scroll - Changes the LEDs on the whole strip from one color to another
- Chase Effect - Select different chase patterns on the whole strip
- Chase Speed - Selects the speed of the selected chase
- Sound Chase - Selects the chase pattern that is triggered via audio
- Sound Flash - Selects the flash pattern that is triggered via audio
- Sound Sensor - Selects the sensitivity of the audio sensor

* Field angles can vary +/- 5°

SPECIFICATIONS

PHYSICAL	
Size	40.25" x 6.75" x 3.5" (102.24cm x 17.15cm x 8.89cm)
Weight	10 lbs (4.5 kg)
ELECTRICAL	
DMX Connectors	3-Pin XLR
Voltage	110V-230V, 50/60Hz
Max Wattage	27 Watts/0.36 Amps
LED Lifetime	60,000-100,000 hours
ENVIRONMENTAL	
Ambient Temperature	0-40°C/104° F
Maximum Surface Temperature	60°C/140° F

NOTE: Included accessories: NEMA 5-15P, Parallel Blade & Ground Plug, 15A

ORDERING INFORMATION

CAT. NO.*	DESCRIPTION
LW135-0PB	Color Pro Strip, 3W RGB LED, 35°, 5-15 Plug, Black Finish
TAoCC-000	C-Clamp
TAoSC-000	Safety Cable

LEVITON SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:
JOB NUMBER:	

Leviton Manufacturing Co., Inc. Lighting & Energy Solutions

20497 SW Teton Avenue, Tualatin, OR 97062 • Tel: 1-800-736-6682 • Fax: 503-404-5594 • Tech Line (6:00AM-4:00PM P.S.T. Mon-Fri): 1-800-959-6004

Leviton Manufacturing Co., Inc. Global Headquarters

201 N. Service Rd. Melville, NY 11747-3138 • Tech Line: 1-800-824-3005 • Fax: 1-800-832-9538

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 • Telephone: 1-800-469-7890 • FAX: 1-800-563-1853

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 • Tel. (+52) 55-5082-1040 • FAX: (+52) 5386-1797 • www.leviton.com.mx

Visit our Website at: www.leviton.com/les

© 2012 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.