

Photocells



DEFINITION

Leviton's photocell sensors precisely monitor either task or ambient light levels. As part of a Leviton lighting and energy solution, photocells work with other components in the system to automatically adjust light levels to a userdefined level. Photocells are most suitable for installation in rooms with windows and open spaces receiving substantial ambient light.

Photocells must be hardwired to a compatible Leviton lighting control system. The photocell measures ambient light in a specific area and sends this data to a dimmer or relay that, in turn, adjusts fixtures to a constant lighting level as measured in that specific area. Daylight harvesting is achieved as lights in a room (with windows or significant, artificial ambient light) automatically brighten or dim depending on how much light the photocell detects.

BENEFITS

- Constant lighting at the optimal level for greater visual comfort and acuity, which contributes to improved productivity
- Provides convenient, automatic hands-free daylight harvesting when integrated with Leviton lighting control products
- Lowers electric bills by reducing usage of lighting where ambient natural light is also present
- Lumen maintenance opportunity compatible

DAYLIGHT HARVESTING


With daylight harvesting, ambient (often natural) light supplements in-room, artificial light in order to keep a constant lighting level while simultaneously saving energy. This ensures unnecessary overhead lighting remains dimmed or OFF. This constant level is programmed into a compatible control device. Once hardwired to the photocell, the dimmer or relay receives the photocell's real-time light measurement and maintains a steady level within the photocell's area of detection.

RULES OF OPERATION

Measured light level = Light Maintain Level Action: Output to lights remains constant

Measured light level < Light Maintain Level Action: Lights are brightened

Measured light level > Light Maintain Level Action: Lights are dimmed




Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 **tech line** 800-824-3005 **fax** 800-832-9538 ©2019 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.


FEATURES


- Indoor photocells designed with a flat Fresnel lens looks downward in a 60° cone of reference to measure actual light on the work surface and reduce the influence of stray light striking the photocell from nearby windows or incidental side lighting
- Outdoor photocells are IP54 rated to guarantee ultimate protection from dirt, dust, oil and other non-corrosive material
- Measures light from any source in the visible spectrum within a 60° cone or 180° angle of response depending on the model
- **ODCOP-00W photocell** with 60° clear lens operates between 1-1,600FC. ODCOP should be surface mounted or direct to ceiling box
- **ODCOP-SOW switching photocell** with 60° clear lens operates between 1-1,600FC. ODCOP should be surface mounted or direct to ceiling box
- ODCOP-DOW dimming photocell with 60° clear lens operates between 1-1,600FC. ODCOP should be surface mounted or direct to ceiling box
- PCCxD-00W, PCCxS-00W, PCCSD-00W line voltage photocells with 60° clear lens for applications where zone control switching, dimming, and demand response are required. Operates between 1-1,600FC. PCC photocells should be mounted to the ceiling in standard 4"x4" square or octagon electrical boxes
- **PCIND-000 indoor photocell** with 60° clear Fresnel lens is default setting = 75-800FC sensing range; can be field adjusted to 800FC max sensing range. PCIND should be mounted to the ceiling, facing down
- PCIND-0SV side view photocell for applications where ceiling mounting is required yet the view should be of the lighting entering the space through a window; or, for installation to the wall of skylights where the view should be up into the skylight. Default setting = 0-30FC sensing range; can be field configured with a jumper for a 3FC, 30FC, 300FC, or 600FC max sensing range
- **PCOUT-000 outdoor photocell** is enclosed in a weatherproof housing with a visor for shading and lens protection. Default setting = 50-750FC sensing range
- **PCOUT-0SV side view photocell** for applications where wall mounting is required yet the view should be of the lighting entering the space through a top/side and/or face of the photocell. Reference placement diagrams. Default setting = 0-30FC sensing range; can be field configured with a jumper for a 3FC, 30FC, 300FC, or 600FC max sensing range
- **PCATR-000 atrium photocell** with opaque dome lens filters 33% of light level in upper atrium. Default setting = 215-2,690FC sensing range; can be field adjusted to 2,690FC max sensing range
- **PCSKY-000 skylight photocell** with dark dome lens filters 90% of light level in skylight. Default setting = 1,076-8,072FC sensing range; can be field adjusted to 8,072FC max sensing range






PHOTOCELL (PCCxD, PCCxS, PCCSD)






SIDE VIEW PHOTOCELL (PCIND-0SV/PCOUT-0SV)




Diameter: 2.04"

ATRIUM/SKYLIGHT (PCATR/PCSKY)






PHOTOCELL PLACEMENT



Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 **tech line** 800-824-3005 **fax** 800-832-9538 ©2019 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

WIRING DIAGRAMS





INSTALLATION

• Low Voltage Class 2 Wiring - Connect directly to dimmer or relay panel

SPECIFICATIONS

	ODCOP- 00W	ODC0P- S0W	ODC0P- D0W		PCCxD- 00W	PCCxS- 00W	PCCSD- 00W
Input Voltage	24VD	12-24VDC		120-277VAC			
Input Current		10mA			30mA		
IP Rating		32			30		
Default Range	1-1,600 FC (10-16,000 LUX)						
Output Voltage	12-24V	Switched: 12-24VD Dimmed: 1-10V Sinking	Dimmed: 1-10V N/A				
Operating Temperature Range	32-131°F (0 -55°C)			32-104°F (0-40°C)			
Storage Temperature Range	14-185°F (-10-85℃)			14-160°F (-26-71°C)			
Listings	Can be used to comply with IECC, ASHRAE 90.1, and 2016 Title 24, Part 6 daylight harvesting requirement	Can be used to comply with IECC, ASHRAE 90.1, and 2016 Title 24, Part 6 daylight harvesting requirements, UL listed, NOM compliant, FCC certified	Can be used to comply with IECC, ASHRAE 90.1, and 2016 Title 24, Part 6 daylight harvesting requirements and NYC LL48, UL 916 listed, FCC certified	90 ha Sta cU	n be used to comply with IECC, ASHRAE).1, and 2016 Title 24, Part 6 daylight arvesting requirements, UL 773A (Occupancy andard), UL 924 (Emergency Equipment), JL Listed, NOM Certified, RoHS Compliant, NY C48 Compliant		ight (Occupancy ipment),
Warranty	Limited 5-Year Warranty						

	PCIND- 000	PCIND- 0SV	PCOUT- 000	PCOUT- 0SV	PCATR- 000	PCSKY- 000
Input Voltage				24VDC		
Input Current				10mA		
IP Rating	20		54	54	65	
Default Range	75-800 FC (807- 8,611 LUX)		0-30 FC (0-322 LUX)		215-2,690FC (2,314-2,8954 LUX)	1,076-8,072 FC (11,581- 8,6886 LUX)
Output Voltage	10VDC full output		0-1	10VDC	10VDC full output	
Operating Temperature Range	12-140°F (-11-60°C))-122°F)-50°C)	12-140°F (-11-60°C)	
Storage Temperature Range	14-185°F (-10-85°C)					
Listings	Can be used to comply with IECC, ASHRAE 90.1, and 2016 Title 24, Part 6 daylight harvesting and demand response and requirements					
Warranty	Limited 2-Year Warranty					

Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 tech line 800-824-3005 fax 800-832-9538 ©2019 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

SELECTION

DEELOTION					
PHOTOCELL	LENS	MOUNTING	ORIENTATION	HEIGHT	DIAMETER
ODCOP-00W		Ceiling		0.99" (25.14mm)	2.51" (63.75mm)
ODCOP-SOW]				
ODCOP-DOW					
PCCxD-00W	Clear		Down	1.09" (27.91mm)	1.09" (27.91mm)
PCCxS-00W]				
PCCSD-00W					
PCIND-000	Fresnel			2.00" (50.8mm)	1.00" (25.4mm)
PCIND-0SV	Diffuse	Ceiling/Wall	Up/Down	1.36" (34.54mm)	2.04" (51.81mm)
PCOUT-000	Clear Hood	1/2" IPT	Horizontal	1.85" (46.99mm)	1.28" (32.51mm)
PCOUT-0SV	Diffuse	Ceiling/Wall	Up/Down	1.36" (34.54mm)	2.04" (51.81mm)
PCATR-000	Dama (Fraat	1 (0" IDT	Horizontal		1.28" (32.51mm)
PCSKY-000	Dome/Frost	1/2" IPT	Up	2.25" (57.15mm)	

ADJUSTABLE CORRESPONDING FC RANGES

SENSOR	MAXIMUM			
ODCOP-00W				
ODCOP-SOW				
ODCOP-DOW	1 1 600 50			
PCCxD-00W	1-1,600 FC			
PCCxS-00W				
PCCSD-00W				
PCIND-000	75-800 FC			
PCIND-0SV	3, 30, 300 or 600 FC			
PCOUT-000	50-750 FC			
PCOUT-0SV	3, 30, 300 or 600 FC			
PCATR-000	215-2,690 FC			
PCSKY-000	1,076-8,072 FC			

ORDERING INFORMATION

CAT. NO.	DESCRIPTION	COLOR	
ODCOP-00W	Photocell		
ODCOP-SOW	Switching Photocell		
ODCOP-DOW	Dimming Photocell		
PCCxD-00W	Line Voltage Dimming Photocell		
PCCxS-00W	Line Voltage Switching Photocell		
PCCSD-00W	Line Voltage Dimming/Switching Photocell	White	
PCIND-000	Indoor Photocell		
PCIND-0SV	Indoor Side View Photocell		
PCOUT-000	Outdoor Photocell		
PCOUT-0SV	Outdoor Side View Photocell		
PCATR-000	Atrium Photocell]	
PCSKY-000	Skylight Photocell		

LEVIT

Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 tel 800-323-8920 fax 800-832-9538 tech line (8:30AM-7:00PM ET Mon-Fri) 800-824-3005

Leviton Manufacturing Co., Inc. Energy Management, Controls and Automation 20497 SW Teton Avenue, Tualatin, OR 97062 tel 800-736-6682 fax 503-404-5594 tech line (6:00AM-4:00PM PT Mon-Fri) 800-959-6004

Visit our Website at: www.leviton.com/photocells

©2019 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.