

RCA Component Video 110-Termination MOS Modules

APPLICATION

Leviton RCA Component Video 110-Termination Multimedia Outlet System (MOS) Modules provide a point-to-point connection for component video signals over twisted-pair cabling. Connect DVD players, Blu-Ray players, and other media sources to televisions and other displays using industry standard RCA connectors. The IDC termination allows for quick termination and customization of cable lengths in the field.

The RCA modules require a Leviton MOS wallplate. The modules are manufactured from durable ABS plastic and are available in white, ivory, or light almond.



SPECIFICATION

AV modules shall have the ability to transmit component video signals over twisted-pair cabling in a point-to-point connection. Products shall be compatible with UTP or shielded cabling that is rated for CAT 5e or higher. Twisted-pair cabling shall be terminated to product using IDC connections. Products shall be capable of transmitting video at resolutions of 1080i for distances up to 100 feet. RCA connections shall have barrel colors of red, blue, and green. Products shall be available in white, ivory, and light almond colors, and shall be compatible with Leviton Multimedia Outlet System wallplates.

FEATURES

- Provides a point-to-point RCA connection for component video signals over twisted-pair cabling (UTP or shielded)
- Twisted-pair cabling can be cut to length in field
- Twisted-pair cabling provides a migration path for future digital signals
- Fast and easy cable termination using color-coded 110-termination IDC connectors

DESIGN CONSIDERATIONS

- Modules must be installed in a Leviton MOS wallplates
- RCA Component modules can be mixed with other MOS modules in the same wallplate
- One twisted-pair cable required (CAT 5e or higher, UTP or shielded)
- Component RCA modules designed to support video resolutions of 1080i for distances up to 100 feet
- RCA connectors have a 13mm (center-to-center) spacing to accommodate cords with larger plugs
- Modules are 1 unit high
- Modules are not compatible with MOS Surface-Mount Boxes

MECHANICAL SPECIFICATIONS

Dimensions: 0.96" H x 1.85"W x 1.65" D
Housing Material: ABS plastic

ELECTRICAL SPECIFICATIONS

Cable Type: UTP and shielded twisted-pair (CAT 5e or higher)
Cable length: Up to 100 feet (1080i)
Impedance: RCA – 75 Ω unbalanced
IDC – 100 Ω balanced

ELECTRICAL SPECIFICATIONS

Operating Temperature: 0° C to 50° C (32° F to 122° F)
Storage Temperature: -10° C to 70° C (14° F to 158° F)
Relative Humidity: 0% to 90%, non-condensing

STANDARDS COMPLIANCE

cULus Listed (UL 1863, CAN/CSA C22.2 No. 182.4-M90)

COUNTRY OF ORIGIN


Taiwan

WARRANTY INFORMATION

One-year limited warranty. For a copy of Leviton warranties, visit www.leviton.com/warranty.


ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



CONNECTOR PIN-OUT

Signal	IDC/Wire
n/a	brown
n/a	w/brown
Red RCA center	green
Red RCA ground	w/green
Blue RCA center	orange
Blue RCA ground	w/orange
Green RCA center	blue
Green RCA ground	w/blue



WIRING DIAGRAM



PART NUMBERS

Description	Part No.
RCA Component Video 110-Termination MOS Module, white	41292-DEW
RCA Component Video 110-Termination MOS Module, ivory	41292-DEI
RCA Component Video 110-Termination MOS Module, light almond	41292-DET