

# ENGLISH

## TO INSTALL:

**WARNING:** TO BE INSTALLED AND/OR USED IN ACCORDANCE WITH APPROPRIATE ELECTRICAL CODES AND REGULATIONS.

**WARNING:** IF YOU ARE NOT SURE ABOUT ANY PART OF THESE INSTRUCTIONS, CONSULT AN ELECTRICIAN.

**CAUTION:** OUTLET MUST BE WIRED TO A SEPARATE 3-WIRE CIRCUIT OF UP TO #4 AWG SIZE CONDUCTORS.

**NOTE:** This device may be used with copper, copper-clad, or aluminum wire.

1. **WARNING:** TO AVOID FIRE, SHOCK, OR DEATH; **TURN OFF POWER** AT CIRCUIT BREAKER OR FUSE AND TEST THAT the POWER IS OFF BEFORE WIRING!
  2. Remove insulation from wire per strip gage as shown on back of device, approximately 1/2 inch (1.3 cm).
  3. Determine appropriate terminal for each wire per **wiring diagram**.
  4. Insert wires into proper terminals (**refer to wiring diagram**). Tighten terminal screws to 25 in.-lbs. of torque. **CAUTION:** Terminal screws must tighten onto conductor only, not insulation.
  5. Mount device using long mounting screws. Attach wallplate (sold separately).
  6. Restore power to circuit breaker or fuse.
- Installation is complete.**