


OPT-X™ SDX Fiber Adapter Plates — Precision Molded

APPLICATION

Leviton SDX Fiber Adapter Plates are used in conjunction with SDX panels or enclosures (rack- or wall-mount) to provide a means to connect backbone to backbone or backbone to horizontal fiber cabling. The SDX Fiber Adapter Plates are offered in LC, SC, and ST versions.



SPECIFICATION

5F100-PLT

The SDX adapter plate shall be modular and functional for use in an SDX panel or enclosure (rack- or wall-mount). The adapter plate shall be offered in LC, SC, and ST styles in 6-, 12-, or 24-fiber configurations. The adapter plate shall be compliant to ANSI/TIA-568.3-E (for performance) and respective ANSI/TIA-604-X (for intermateability) standards. Adapter plates shall use zirconia ceramic sleeves and be offered in standard fiber type colors pursuant to ANSI/TIA-568.3-E standards. The LC and SC adapters and plate shall be integrated to eliminate "rattle" and loose fit. Adapter plates shall be TAA compliant.

5F100-8MT

FEATURES & BENEFITS

- Integrated LC and SC plates (two pieces) eliminates rattling and loose fit
- Adapter plates use zirconia ceramic sleeves for optimal performance in 1 Gbps and higher transmission speeds
- LC and SC plates offered in standard fiber type colors
- · Adapter plates offered in LC, SC, ST, and blank styles
- · Captive push-lock pins allow for quick, tool-less installation
- Compatible with all SDX panels and enclosures (rack- or wall-mount)

DESIGN CONSIDERATIONS

- Arrange adapter plates within panel or enclosure to allow for future growth
- · Colored plate or fiber adapters will identify fiber type used
- Visible sequential numbering to identify ports (for Tx & Rv)
- 4RU rack-mount enclosure accommodates up to 15 adapter plates for highest density per RU
- Zirconia ceramic sleeve typically used on laser optimized multimode and single-mode applications (OM3, OM4, OS2)
- Dust plugs or caps are installed in adapters on final assembly

STANDARDS & REGULATIONS

- Meets ANSI/TIA-568.3-E for performance requirements
- Meets ANSI/TIA-604-2B (ST), -3B (SC), -10C (LC) for connector intermateability

MECHANICAL SPECIFICATIONS

Dimensions: See page two

Materials: Adapter plate: constructed of engineered

polymer, various pantone colors

Temp. (Installation): -10 °C to +60 °C (-50 °F to +140 °F) Temp. (Operating): -10 °C to +60 °C (-50 °F to +140 °F)

COUNTRY OF ORIGIN


LC, SC, blank plates: USA ST plates: Taiwan


WARRANTY INFORMATION


For Leviton product warranties, go to Leviton.com/NS/Warranty


PRODUCT SPECIFICATIONS 5F100-xxx (precision molded)











PART NUMBERS	
Description	Part No.
Plate (beige), 62.5 μm MM (OM1), Duplex LC, 12-fiber, zirconia ceramic sleeve	5F100-2IL
Plate (aqua), 50 µm LOMM (OM3 & OM4), Duplex LC, 12-fiber, zirconia ceramic sleeve	5F100-2QL
Plate (blue), SM (OS2), Duplex LC, 12-fiber, zirconia ceramic sleeve	5F100-2LL
Plate (green), SM (OS2), Duplex LC/APC, 12-fiber, zirconia ceramic sleeve	5F100-2VL
Plate (beige), 62.5 μm MM (OM1), Quad LC, 24-fiber, zirconia ceramic sleeve	5F100-4IL
Plate (aqua), 50 µm LOMM (OM3 & OM4), Quad LC, 24-fiber, zirconia ceramic sleeve	5F100-4QL
Plate (blue), SM (OS2), Quad LC, 24-fiber, zirconia ceramic sleeve	5F100-4LL
Plate (green), SM (OS2), Quad LC/APC, 24-fiber, zirconia ceramic sleeve	5F100-4VL
Plates (beige), 62.5 µm MM (OM1), Duplex SC, 6-fiber, zirconia ceramic sleeve	5F100-6IC
Plates (aqua), 50 µm MM (OM3 & OM4), Duplex SC, 6-fiber, zirconia ceramic sleeve	5F100-6QC
Plates (blue), SM (OS2), Duplex SC, 6-fiber, zirconia ceramic sleeve	5F100-6LC
Plates (green), SM (OS2), Duplex SC/APC, 6-fiber, zirconia ceramic sleeve	5F100-6VC
Plate (beige), 62.5 μm MM (OM1), Duplex SC, 12-fiber, zirconia ceramic sleeve	5F100-2IC
Plate (aqua), 50 µm LOMM (OM3 & OM4), Duplex SC, 12-fiber, zirconia ceramic sleeve	5F100-2QC
Plate (blue), SM (OS2), Duplex SC, 12-fiber, zirconia ceramic sleeve	5F100-2LC
Plate (green), SM (OS2), Duplex SC/APC, 12-fiber, zirconia ceramic sleeve	5F100-2VC
Plate (black), ST MM/SM, 6-fiber, zirconia ceramic sleeve	5F100-6MT
Plate (black), ST MM/SM, 8-fiber, zirconia ceramic sleeve	5F100-8MT
Plate (black), blank	5F100-PLT

For further support information, visit Leviton.com/NS/Support

Page 2 of 2

USA Network Solutions Headquarters +1 (800) 722 2082

infoUSA@leviton.com

Leviton Cable (formerly Berk-Tek) +1 (800) 237 5835 | infoUSA@leviton.com **Asia Pacific**

+852 3620 2602 infoAPAC@leviton.com

Canada +1 (800) 461 2002 infoCanada@leviton.com

Europe +44 (0) 1592 772124 infoEurope@leviton.com

Latin America MX: +52 (55) 2128 6286 LATAM: +52 (55) 2333 5963 infoLATAM@leviton.com

Middle East & Africa +971 (4) 247 9800 infoMEA@leviton.com

Revised December 2023

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.