5G108-xx5

PRODUCT SPECIFICATIONS 5G108-xx5

GIGAMAX™ Cat 5e UTP QUICKPORT™ Jack

APPLICATION

The GIGAMAX Cat 5e UTP QUICKPORT Jack is designed to be used with any Category 5e UTP structured cabling system. The modular connector features a one-piece narrow design that supports high port density in a small area, and is ideal for use in residential, MDU, and high-megabit applications.





SPECIFICATION

The jack shall meet or exceed the requirements for channellevel electrical transmission performance as described in ANSI/TIA-568.2-D (Cat 5e), ISO/IEC 11801-1 (Class D), and EN 50173-1 (Class D). The jack shall be compliant with ANSI/TIA-1096-A, c(UL)us Listed, and be independently verified for electrical transmission performance. In addition to Category 5e compliance, the jack shall have the ability to support high megabit and shared-sheath applications. All plastics used in construction of the connector bodies shall be fire-retardant with a UL flammability rating of 94V-0. Termination of all jacks shall be 110-type IDC with solderplated phosphor bronze contacts. The jack shall provide a ledge directly adjacent to the 110-style termination against which the wires can be directly terminated and cut in one action by the installer. Jack wiring label shall provide installation color codes for both T568A and T568B wiring schemes. The modular hardware shall fit all other installed telecommunications wallplates, outlets and field-configurable patch panels and patch blocks.

DESIGN CONSIDERATIONS

- Use in any QUICKPORT housing to support GIGAMAX Cat 5e UTP connectivity in surface-mount, flush-mount, or modular furniture outlets, or patch panels and patch blocks
- Can be used in conjunction with other QUICKPORT snap-in modules for voice/data and video applications over UTP, coax, and fiber
- To ID ports, use different colored modules for each application

FEATURES & BENEFITS

- · Available in 13 colors
- Dual wiring code label allows connector to be wired to either T568A or T568B
- · Individual port configurability allows specification flexibility
- Robust one-piece lead-frame design increases power-carrying capacity and efficiency while providing improved durability
- · Narrow connector allows high port density in a small area
- Will exceed IEEE 802.3 standard up to 0.7 amps per conductor continuously
- Supports high-megabit and shared-sheath applications
- Available individually, in bulk packages of 25, and in bulk packages of 150 with a JackRapid[™] Punchdown Tool

STANDARDS & REGULATIONS

- ANSI/TIA-568.2-D (Cat 5e)
- ISO/IEC 11801-1 (Cat 5e)
- EN 50173-1 (Cat 5e)
- ANSI/TIA-1096-A (formerly FCC Part 68)
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE. UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)
- c(UL)us Listed (UL 1863)
- · UL 2043 Plenum Certified
- RoHS 3

COUNTRY OF ORIGIN

USA

WARRANTY INFORMATION

For Leviton product warranties, go to Leviton.com/NS/Warranty

PRODUCT SPECIFICATIONS 5G108-xx5




MECHANICAL SPECIFICATIONS


Dimensions: See below

Materials: Jack Body: High-impact, fire retardant

plastic rated UL 94V-0

Temp. (Storage): -40 °C to +70 °C (-40 °F to +158 °F)
Temp. (Installation): Refer to cable installation temperature
Temp. (Operating): -10 °C to +60 °C (+14 °F to +140 °F)
Humidity (Max.): 95% relative humidity, non-condensing





Standard Jack	QuickPack™ 25/Bag	150/Bag with JackRapid™ Tool
5G108-RW5	5G108-BW5	5G108-JW5
5G108-RI5	5G108-BI5	5G108-JI5
5G108-RO5	5G108-BO5	5G108-JO5
5G108-RL5	5G108-BL5	5G108-JL5
5G108-RE5	5G108-BE5	5G108-JE5
5G108-RT5	5G108-BT5	5G108-JT5
5G108-RG5	5G108-BG5	5G108-JG5
5G108-RC5	5G108-BC5	5G108-JC5
5G108-RY5	5G108-BY5	5G108-JY5
5G108-RV5	5G108-BV5	5G108-JV5
5G108-RP5	5G108-BP5	5G108-JP5
5G108-RB5	5G108-BB5	5G108-JB5
5G108-RR5	5G108-BR5	5G108-JR5
	Jack 5G108-RW5 5G108-RI5 5G108-RC5 5G108-RE5 5G108-RE5 5G108-RC5 5G108-RC5 5G108-RV5 5G108-RV5 5G108-RV5 5G108-RV5 5G108-RP5 5G108-RP5 5G108-RP5	Jack 25/Bag 5G108-RW5 5G108-BW5 5G108-RI5 5G108-BI5 5G108-RO5 5G108-BO5 5G108-RL5 5G108-BL5 5G108-RE5 5G108-BE5 5G108-RE5 5G108-BT5 5G108-RG5 5G108-BG5 5G108-RC5 5G108-BC5 5G108-RY5 5G108-BY5 5G108-RV5 5G108-BV5 5G108-RP5 5G108-BP5 5G108-RB5 5G108-BB5

For further support information, visit Leviton.com/NS/Support

Page 2 of 2

USA

Network Solutions Headquarters

+1 (800) 722 2082 infoUSA@leviton.com

Leviton Cable (formerly Berk-Tek) +1 (800) 237 5835 | infoUSA@leviton.com Asia Pacific

+852 3620 2602 infoAPAC@leviton.com Canada +1 (800) 461 2002 infoCanada@leviton.com **Europe** +44 (0) 1592 772124 infoEurope@leviton.com

MX: +52 (55) 2128 6286 LATAM: +52 (55) 2333 5963 infoLATAM@leviton.com

Latin America

Middle East & Africa +971 (4) 247 9800 infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.