

# **Passive Infrared Ceiling Occupancy Sensor**



# Description

The OSCxx-IOW is a Passive Infrared (PIR) ceiling mount, low voltage occupancy sensor that works in conjunction with the Leviton OSPxx Power Pack to control lighting. The sensor's main function is to turn the lights ON or maintain the lights ON while movement is detected within the sensor's range and to turn the lights OFF when the space is left unoccupied.

The sensor uses a dual element PIR heat detector that resides behind a multi-zone optical lens. This Fresnel lens establishes dozens of zones of detection. The sensor is sensitive to the heat emitted by the human body. In order to trigger the sensor, the source of heat must move from one zone of sensing to another. Non-moving hot objects will not cause the lights to turn ON (like incandescent lights).

### Applications

- Classrooms Utility closets
  - ets Conference rooms • Small offices
- Copy rooms
  Hallways
  Small offices
  Open areas
  Private restrooms
  Storage rooms
- Vending rooms
   Open warehouses
   Work spaces

### Features

- Fast, simple installation: easy base mount, three wire connection (low voltage) and twist-and-lock
- Self-adjusting: internal microprocessor continually analyzes, evaluates and adjusts the infrared sensitivity and time delay. Performance is kept at a maximum and user complaints are eliminated.
- Flexible base mounting: supplied twist-and-lock base mount permits fast alignment. Supplied cover hides mounting hardware and wires. Can be used with raceways for hard surface installations.
- Range & coverage: 450 sq. feet and 1,500 sq. feet models available
- Maximum reliability, low cost: all digital circuitry uses a minimum of components
- Power base (OPB15) available for line voltage applications
- Ambient light recognition: a light sensor prevents lights from turning on when the room is adequately lit by natural light
- Non-volatile memory: learned and adjusted settings saved in protected memory are not lost during power outages
- Timer setting feature: automatic—30sec-30min. Test mode—6sec with auto exit programming.
- PIR masking: pre-scored masking disks are provided with the device for fine tuning the field-of-view
- Walk-through: provides increased energy savings by decreasing the time delay to 2.5min when someone momentarily walks through the monitored space
- High motion sensitivity: large lens area and multi-element lens design gives excellent range and sensitivity
- Custom off-white color matched for shaded ceilings and most common ceiling tiles
- Device: rugged, high-impact, injection molded plastic. Color coded leads are 6" long (16.24 cm).

Condition	Example	Adaptive Reaction
Timer left in text mode—the sensor remains in a 6 sec. test mode	An installer accidently leaves the sensor in the 6 sec. timer text mode and the lights may go on or off every 6 seconds	The sensor automatically resets the timer to 10 minutes after 15 minutes of test mode
False ON—the sensor incorrectly turns the lights ON	The sensor detects movement in the corridor hallway and the room lights turn ON	After an initial movement is sensed, if another movement is not sensed within the timer setting, then the delayed OFF time setting is automatically reduced
False OFF—the sensor incorrectly turns the lights OFF	The sensor does not detect movement because an occupant sits virtually motionless at a desk and the lights turn OFF	If motion is sensed within a short period after the lights go OFF, then the current delayed OFF time setting is increased

### Leviton Manufacturing Co., Inc. Global Headquarters


201 North Service Road, Melville, NY 11747-3138 **tel** 800-323-8920 **tech line** (8:30AM-7:00PM ET Mon-Fri) 800-824-3005 ©2023 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

# **DIP Switch Settings**


Switch		Switch Functions	Switch Settings
	Bank A	OFF	ON
A1	N/A		
A2	N/A		
A3	Manual Mode	Auto Adapting Enabled	Auto Adapting Disabled
A4	Walk-Thru Disabled	Walk-Thru Enabled	Walk-Thru Disabled
	Bank B		
B1	Override to ON	Auto Mode	Lights forced ON
B2	Override to OFF	Auto Mode	Lights forced OFF
B3	Test Mode	OFF ON OFF	Enter/Exit Test Mode
B4	LED Disabled	LEDs Enabled	LEDs Disabled

\*Bold items are factory defaults


# **Dimensions Diagrams**




# Wiring Diagram



## **Field-Of-View Diagrams**







# Product Data OSCxx-I0W



# Specifications

Electrical		
Power Requirements	24 VDC, 10mA from OSPxx Power Pack or OPB15 Power Base	
Power Consumption	10mA	
Output	24 VDC active high logic control signal with short circuit protection	
Controls		
Infrared Sensitivity	0 to 100%; red knob (factory setting: 75%)	
Light Sensor	20 to 3,000 Lux; blue knob factory set at 100% (grey wire required)	
Time Delay	30sec-30min; black knob (factory setting: 10min)	
Indicators		
Red LED Lamp	Passive infrared motion technology	
Environmental		
Operating Temperature Range	32-104°F (0-40°C)	
Relative Humidity	0-95% non-condensing, for indoor use only	
Other		
Mounting Height	8-10 feet	
Energy Codes	Can be used to comply with IECc, ASHRAE 90.1 and 2022 Title 24, Part 6 occupancy sensing requirements	
Listings	IP42 Rated, CUL/US Certified	
Warranty	Limited 5-Year	

# **Ordering Information**

Passive Infrared Ceiling Sensors		
Cat. No.	Description	
OSC04-IOW	Passive Infrared Ceiling Sensor, 450 sq. feet of coverage	
OSC04-IAW	Passive Infrared Ceiling Sensor, 1500 sq feet of coverage, made in USA with globally sourced components	
OSC15-IOW	Passive Infrared Ceiling Sensor, 1500 sq. feet of coverage	
OSC15-IAW	Passive Infrared Ceiling Sensor, 1500 sq. feet of coverage, made in USA with globally sourced components	

**Product Data** OSCxx-I0W



Leviton Manufacturing Co., Inc. Lighting & Controls 10385 SW Avery Street, Tualatin, OR 97062 tel 800-736-6682 tech line (6:00AM-4:00PM PT Mon-Fri) 800-959-6004

Leviton Manufacturing Co., Inc. Global Headquarters 201 North Service Road, Melville, NY 11747-3138 tel 800-323-8920 tech line (8:30AM-7:00PM ET Mon-Fri) 800-824-3005

#### Visit our Website at: www.leviton.com/sensors

©2023 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.