


Smart PIR 0-10V Dimming Wallbox Sensor





Description

The Leviton Smart Dimming Wallbox Sensor (ODD10-IDx) is designed for use with 0-10V ballasts and uses Passive Infrared (PIR) detection technology to monitor a room for occupancy using a segmented, tamper resistant lens. A specialized lens divides the field-of-view into sensor zones. When a person passes in or out of a sensor zone the sensor detects motion and switches the lights ON. The lights will remain ON as long as an occupant moves through the sensor zones and after the timeout expires. The ODD10-IDx features a vacancy mode for Manual-ON/Auto-OFF operation, ideal for installations where manual-ON switching is required for energy code applications. Lighting levels can be adjusted using the dimming bar next to the switch.

A "minor motion" zone detects small body movements. This detection allows the lights to remain ON when individuals in the space are more stationary. The "major motion" zone exhibits a lesser degree of sensitivity requiring larger movements.

Configuration of ODD10-IDx is made using the Leviton Smart Sensor App from a smartphone or other Bluetooth® enabled Android or iOS device. Simple configuration can also be applied using pushbutton setup for several common pre-configured options. The ODD10-IDx integrates a photocell for daylighting hold-OFF which can be programmed using the Leviton Smart Sensor App.

Leviton Smart Wallbox Sensors feature antimicrobial treated plastic to help keep its surfaces cleaner and prevent microorganisms from degrading the product. This product contains an antimicrobial agent to inhibit the growth of mold, mildew, fungus and odor-causing bacteria that cause discoloration, staining, deterioration or corrosion on the surface of the device in between normal cleanings.

Applications

- Office
- Small Lobbies
- Meeting Rooms

Features

- Can be used to comply with ASHRAE 90.1, IECC and 2019
 Title 24, Part 6 occupancy/vacancy sensing, dimming, and
 manual-ON/auto-OFF requirements
- Fits in a standard wallbox and gangable with other units
- Controls LED lighting loads up to 8A
- One relay module for single-level switching
- 180° field-of-view provides approximately 1,100 square feet of coverage Maximum sensing distance in front of the sensor is 30-40 feet and 15-20 feet on either side
- Latest PIR technology accurately detects minor motion up to 400sq ft and major motion up to 1,100 sq ft
- · Integrated photocell for daylighting hold-OFF
- Add a Power Pack and Controlled Receptacles for plug load control
- Use the Leviton Push to Pair (P2P) process to create a multiway system for up to 5 devices
- Antimicrobial treated plastic helps keep the device clean
- Advanced configuration can be performed using the Leviton Smart Sensor App on any Bluetooth enabled Android or iOS device:
 - Set operating mode to Occupancy (auto-ON/auto-OFF) or Vacancy (manual-ON/auto-OFF)
 - Adjust sensitivity and timeouts
 - Set up partial-ON and partial-OFF levels and partial-OFF timeouts
 - Enable the integrated photocell for daylighting hold-OFF and select target daylighting hold-OFF levels
 - Activate the nightlight and select nightlight colors
 - Set a security code to lock configuration settings
- Out-of-the-box configuration default mode:
 - Auto-ON/auto-OFF with 20-minute time out
 - Sensitivity set to 75%
 - Nightlight and daylighting disabled

Product Data ODD10-IDx


Features (continued)

• Convenient pushbutton hold configuration for installers without a smart device*:

Pushbutton Hold Configuration			
Button (#)	Operating Mode	Sensitivity (%)	Time Out (mins)
1		75	10
2	Auto-ON/		20
3	Auto-OFF	100	10
4			20
5		75	10
6	Manual-ON/		20
7	Auto-OFF	100	10
8			20

^{*}Requires removal of front face cover


Wiring Diagrams




^{*}Depending on manufacture date, pink wire may be gray

For Lighting Loads

Dimensions Diagrams





Top View





Field of View Diagram





Specifications

Electrical		
Input Voltage/Frequency	120-277VAC, 50/60Hz	
Input Current		
120V	Standby: 0.2W Max: 0.5W+Load Current	
277V	Standby: 0.3W Max: 0.6W+Load Current	
Load Ratings		
General Purpose @ 120V	10A	
General Purpose @ 277V	10A	
LED/Electronic Ballast @ 120V	8A	
LED/Electronic Ballast @ 277V	5A	
Standard Ballast @ 120V	104	
Standard Ballast @ 277V	10A	
Tungsten @ 120V	6.67A	
Tungsten6f7276@ 277V	0.07A	
Motor @ 120V	1/4HP (FLA 5.8A)	
Motor @ 277V	1/3HP (FLA 3.0A)	
IP Rating	IP10	
Network Connections	BLE 4.2, BLE 5.0	
Environmental		
Operating Temperature	32 to 104°F (0 to 40°C)	
Storage Temperature	-40 to 185°F (-40 to 85°C)	
Physical		
Dimensions	4.13" x 2.12" x 1.86" (104.90mm x 53.95mm x 47.25mm)	
Other		
Energy Codes	Can be used to comply with ASHRAE 90.1, IECC and 2019 Title 24, Part 6 occupancy/vacancy sensing, dimming, and manual-ON/auto-OFF requirements	
Listings	IECC, UL and cUL listed; JIS Z 2801:2000	
Certifications	FCC, ICC	
Warranty	Limited five-year warranty	

Leviton Manufacturing Co., Inc. Lighting & Controls

201 North Service Road, Melville, NY 11747-3138 **tel** 800-323-8920 **tech line** (8:00AM-10:00PM ET Mon-Fri, 9:00AM-7:00PM ET Sat, 9:00AM-5:00PM ET Sun 800-824-3005 ©2022 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Product Data ODD10-IDx



Ordering Information

Smart Wallbox Sensors			
Cat. No.	Description		
ODD10-IDW	Smart PIR 0-10V Dimming Wallbox Sensor, App configurable; Auto-ON/Auto-OFF or Manual-ON/Auto-OFF, neutral wire required, 120/208/220/230/240/277VAC, 50/60Hz; White		
ODD10-IDI	Smart PIR 0-10V Dimming Wallbox Sensor, App configurable; Auto-ON/Auto-OFF or Manual-ON/Auto-OFF, neutral wire required, 120/208/220/230/240/277VAC, 50/60Hz; Ivory		
011-ODD10-IDW	Smart PIR 0-10V Dimming Wallbox Sensor, Antimicrobial, App configurable; Auto-ON/Auto-OFF or Manual-ON/Auto-OFF, neutral wire required, 120/208/220/230/240/277VAC, 50/60Hz; White		
ODDKT-00E	Smart Dimming Wallbox Sensor Color Change Kit, Black		
ODDKT-00R	Smart Dimming Wallbox Sensor Color Change Kit, Red		
ODDKT-00G	Smart Dimming Wallbox Sensor Color Change Kit, Gray		
ODDKT-00I	Smart Dimming Wallbox Sensor Color Change Kit, Ivory		
ODDKT-00T	Smart Dimming Wallbox Sensor Color Change Kit, Light Almond		
ODDKT-00W	Smart Dimming Wallbox Sensor Color Change Kit, White		

Note: Wallplate sold separately. Order 80401-2AW, 1-Gang Decora Wallplate, antimicrobial treated.

Leviton Manufacturing Co., Inc. Lighting & Controls

10385 SW Avery Street, Tualatin, OR 97062 tel 800-736-6682 tech line (6:00AM-4:00PM PT Mon-Fri) 800-959-6004

Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 tel 800-323-8920 tech line (8:00AM-10:00PM ET Mon-Fri, 9:00AM-7:00PM ET Sat, 9:00AM-5:00PM ET Sun) 800-824-3005